


### Description

The GBL05C-A is a 5V bi-directional TVS diode, utilizing leading monolithic silicon technology to provide fast response time and low ESD clamping voltage, making this device an ideal solution for protecting voltage sensitive high-speed data lines. The GBL05C-A has a low capacitance with a typical value at 1pF, and complies with the IEC 61000-4-2 (ESD) with  $\pm 30\text{kV}$  air and  $\pm 30\text{kV}$  contact discharge. It is assembled into a lead-free SOD-323 package. The small size, low capacitance and high ESD surge protection make GBL05C-A an ideal choice to protect cell phone, wireless systems, and communication equipment.

### Features

- 360W peak pulse power (8/20 $\mu\text{s}$ )
- Ultra low capacitance: 1pF typical
- Ultra low leakage: nA level
- Operating voltage: 5V
- Low clamping voltage
- Protects one power line or data line
- Complies with following standards:
  - IEC 61000-4-2 (ESD) immunity test  
 Air discharge:  $\pm 30\text{kV}$   
 Contact discharge:  $\pm 30\text{kV}$
  - IEC61000-4-5 (Lightning) 18A (8/20 $\mu\text{s}$ )
- RoHS Compliant

### Dimensions and Pin Configuration



Circuit and Pin Schematic


### Mechanical Characteristics

- Package: SOD-323
- Lead Finish: Matte Tin
- Case Material: “Green” Molding Compound.
- Moisture Sensitivity: Level 3 per J-STD-020
- Terminal Connections: See Diagram Below
- Marking Information: See Below

### Applications

- USB Ports
- Smart Phones
- Wireless Systems
- Ethernet 10/100/1000 Base T

### Marking Information



### Ordering Information

| Part Number | Packaging        | Reel Size |
|-------------|------------------|-----------|
| GBL05C-A    | 3000/Tape & Reel | 7 inch    |


**Absolute Maximum Ratings ( $T_A=25^{\circ}\text{C}$  unless otherwise specified)**

| Parameter                                | Symbol           | Value       | Unit               |
|--|------------------|-------------|--------------------|
| Peak Pulse Power (8/20 $\mu\text{s}$ )   | Ppk              | 360         | W                  |
| Peak Pulse Current (8/20 $\mu\text{s}$ ) | I <sub>PP</sub>  | 18          | A                  |
| ESD per IEC 61000-4-2 (Air)              | V <sub>ESD</sub> | $\pm 30$    | kV                 |
| ESD per IEC 61000-4-2 (Contact)          |                  | $\pm 30$    |                    |
| Operating Temperature Range              | T <sub>J</sub>   | -55 to +125 | $^{\circ}\text{C}$ |
| Storage Temperature Range                | T <sub>stg</sub> | -55 to +150 | $^{\circ}\text{C}$ |


**Electrical Characteristics ( $T_A=25^{\circ}\text{C}$  unless otherwise specified)**

| Parameter               | Symbol           | Min | Typ | Max | Unit          | Test Condition                                     |
|-------------------------|------------------|-----|-----|-----|---------------|--|
| Reverse Working Voltage | V <sub>RWM</sub> |     |     | 5   | V             |  |
| Breakdown Voltage       | V <sub>BR</sub>  | 6   |     |     | V             | I <sub>T</sub> = 1mA                               |
| Reverse Leakage Current | I <sub>R</sub>   |     |     | 0.2 | $\mu\text{A}$ | V <sub>RWM</sub> = 5V                              |
| Clamping Voltage        | V <sub>C</sub>   |     |     | 10  | V             | I <sub>PP</sub> = 1A (8 x 20 $\mu\text{s}$ pulse)  |
| Clamping Voltage        | V <sub>C</sub>   |     |     | 20  | V             | I <sub>PP</sub> = 18A (8 x 20 $\mu\text{s}$ pulse) |
| Junction Capacitance    | C <sub>J</sub>   |     | 1   |     | pF            | V <sub>R</sub> = 0V, f = 1MHz                      |


**Typical Performance Characteristics (TA=25°C unless otherwise Specified)**




**Junction Capacitance vs. Reverse Voltage**




**Peak Pulse Power vs. Pulse Time**




**Clamping Voltage vs. Peak Pulse Current**



**Power Derating Curve**




**8 X 20μs Pulse Waveform**



Note: Data is taken with a 10x attenuator

**ESD Clamping Voltage**  
**8 kV Contact per IEC61000-4-2**

### SOD-323 Package Outline Drawing



| SYM      | MILLIMETERS |       |       |
|----------|-------------|-------|-------|
|          | MIN         | NOM   | MAX   |
| A        | 0.800       | --    | 1.100 |
| A1       | 0.800       | --    | 0.900 |
| A2       | 0.000       | --    | 0.100 |
| b        | 0.250       | --    | 0.400 |
| c        | 0.080       | --    | 0.177 |
| D1       | 1.600       | 1.700 | 1.800 |
| D        | 2.300       | --    | 2.800 |
| E        | 1.150       | --    | 1.400 |
| L        | 0.475REF    |       |       |
| L1       | 0.100       | --    | 0.500 |
| $\Theta$ | 0°          | --    | 8°    |

### Suggested Land Pattern



**Unit: mm**

### Contact Information

Applied Power Microelectronics Co., Ltd.

Website: <http://www.appliedpowermicro.com>

Email: [sales@appliedpowermicro.com](mailto:sales@appliedpowermicro.com)

Phone: +86 (0519) 8399 3606