

437A Series – 1206 Fast-Acting Ceramic Fuse

Agency Approvals	

Agency	Agency File Number	Ampere Range
c FN ° us	E10480	0.500A – 8A
SP.	29862	0.500A – 8A

Electrical Characteristics for Series

% of Ampere Rating	Ampere Rating	Opening Time at 25°C
100%	0.500A – 8A	4 hours, Minimum
250%	0.750A – 8A	5 seconds, Maximum
350%	0.750A – 8A	1 second, Maximum
330 %	0.500A	5 seconds, Maximum

Electrical Specifications by Item

Ampere Max. Deting Amp Voltage	late martine Detine 1		Nominal		Nominal Power	Agency Approvals			
Rating (A)	Code	Rating (V)	Interrupting Rating ¹	Resistance (Ohms) ²	Melting I ² t (A ² Sec.) ³	Drop At Rated Current (V) ⁴	Dissipation At Rated Current (W)	c N [°] us	۹.
0.500	.500	63	50A @ 63VAC/DC	0.908	0.018	0.52	0.260	х	х
0.750	.750	63	50A @ 63VAC/DC 100A @ 63VDC	0.600	0.064	0.45	0.338	х	х
1.00	001.	63		0.420	0.100	0.41	0.410	х	х
1.25	1.25	63		0.318	0.256	0.40	0.500	х	х
1.50	01.5	63	50A @ 63VAC/DC	0.209	0.324	0.39	0.585	х	х
1.75	1.75	63		0.071	0.075	0.27	0.473	х	х
2.00	002.	63		0.062	0.144	0.20	0.400	х	х
2.50	02.5	32		0.043	0.441	0.15	0.375	х	х
3.00	003.	32		0.035	0.506	0.14	0.420	х	х
3.50	03.5	32		0.027	0.777	0.13	0.455	х	х
4.00	004.	32	50A @ 32VAC/35VDC	0.022	1.024	0.13	0.520	х	х
5.00	005.	32		0.0159	2.30	0.13	0.650	х	х
7.00	007.	32		0.0100	5.02	0.13	0.910	х	х
8.00	008.	32		0.008	7.23	0.13	1.040	х	х

Notes:

1. AC Interrupting Rating tested at rated voltage with unity power factor. DC Interrupting Rating tested at rated voltage with time constant < 0.8 msec.

2. Nominal Resistance measured with < 10% rated current.

3. Nominal Melting I²t measured at 1 msec. opening time.

4. Nominal Voltage Drop measured at rated current after temperature has stabilized.

© 2019 Littelfuse, Inc.

Specifications are subject to change without notice. Application testing is strongly recommended. . Revised: 02/07/19

Description

The 437A Series AECQ-Compliant fuses are specifically tested to cater to secondary circuit protection needs of compact auto-electronics applications.

The general design ensures excellent temperature stability and performance reliability. In addition to this, the high I²t values typical of the Littelfuse Ceramic Fuse family ensure high inrush current withstand capability.

Features

- Operating Temperature from -55°C to +150°C
- 100% Lead-free, Halogen-Free and RoHS compliant
- Meets Littelfuse's automotive qualifications*
- * Largely based on Littelfuse internal AEC-Q200 test plan.

Applications

System

- Li-ion Battery
- LED Lighting
- TFT Display
- Battery Management System (BMS)

Fast response to faulty

sensitive electronic

components

current to ensure overcurrent protection for

ROHS 🕫 HF c 🔊 us 🚯

 Automotive Navigation • Clusters

Additional Information







Datasheet

Resources




Devices designed to carry rated current for 4 hours minimum. It is recommended that devices be operated continuously at no more than 80% rated current. See "Temperature Re-rating Curve" for additional re-rating information. Devices designed to be mounted with marking code facing up



Surface Mount Fuses

Ceramic Fuse > 437A Series




 Re-rating depicted in this curve is in addition to the standard re-rating of 20% for continuous operation.

continuous operation. Example:

For continuous operation at 75 degrees celsius, the fuse should be rerated as follows: I = (0.80)(0.85)|_{RAT} = (0.68)|_{RAT}

Part Numbering System




Average Time Current Curves



Soldering Parameters

Reflow Condition		Pb-free assembly	
	- Temperature Min (T _{s(min)})	150°C	
Pre Heat	- Temperature Max (T _{s(max)})	200°C	
	-Time (Min to Max) (t _s)	60 – 180 seconds	
Average Ramp-up Rate (Liquidus Temp (T _L) to peak)		5°C/second max.	
T _{S(max)} to T _L - Ramp-up Rate		5°C/second max.	
Reflow	- Temperature (T _L) (Liquidus)	217°C	
	- Temperature (t _L)	60 – 150 seconds	
Peak Tempe	rature (T _P)	260+0/-5 °C	
Time within Temperatur	n 5°C of actual peak e (t _p)	20 – 40 seconds	
Ramp-down Rate 5°C/second max.		5°C/second max.	
Time 25°C t	Time 25°C to peak Temperature (Tp)8 minutes max.		
Do not exceed 260°C		260°C	
Wave Soldering		260°C, 10 seconds max.	






Surface Mount Fuses

Ceramic Fuse > 437A Series

Product Characteristics

	Body: Advanced Ceramic		
Materials	Terminations: Ag/Ni/Sn (100% Lead-free)		
	Element Cover Coating: Lead-free Glass		
Moisture Sensitivity Level	IPC/JEDEC J-STD-020, Level 1		
Solderability	IPC/EIC/JEDEC J-STD-002, Condition B		
Humidity Test	MIL-STD-202, Method 103, Conditions D		
Resistance to Solder Heat	MIL-STD-202, Method 210, Condition B		
Moisture Resistance	MILSTD-202, Method 106		
Thermal Shock MIL-STD-202, Method 107, Condition B			
Mechanical Shock	MIL-STD-202, Method 213, Condition A		
Vibration	MIL-STD-202, Method 201		
Vibration, High Frequency	MIL-STD-202, Method 204, Condition D		
Dissolution of Metallization	IPC/EIC/JEDEC J-STD-002, Condition D		
Terminal Strength	IEC 60127-4		

High Temperature Storage	MIL-STD-202 Method 108 with exemptions		
Thermal Shock Test	JESD22 Method JA-104, Test Conditions B and N		
Biased Humidity MILSTD-202 Method 103, 85°C/85% RH wi 10% operating power for 1000 hrs			
Operational Life	MIL-STD-202 Method 108, Test Condition D		
Resistance To Solvents	MIL-STD-202 Method 215		
Mechanical Shock	MIL-STD-202 Method 213, Test Condition C		
High Frequency Vibration	MIL-STD-202, Method 204		
Resistance To Soldering Heat	MIL-STD-202 Method 210, Test Condition B		
Solderability	JESD22-B102E Method 1		
Terminal Strength For SMD	AEC Q200-006		
Board Flex	AEC Q200-005		
Electrical Characterization	3 Temperature Electrical Characterization		



Part Marking System

Amp Code	Marking Code
.500	F
.750	G
001.	Н
1.25	J
01.5	К
1.75	L
002.	N
02.5	<u>o</u>
003.	Р
3.500	R
004.	S
005.	Т
007.	W
008.	X

Packaging

Packaging Option Packaging Specification		Quantity	Quantity and Packaging Code		
8mm Tape and Reel	EIA-481, IEC 60286, Part 3	3000	WRA		

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littlefuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <u>www.littlefuse.com/disclaimer-electronics</u>.