

Please visit our website for more information: www.upi-semi.com

The contents of this document are provided in connection with uPI Semiconductor Corp. ("uPI") products. uPI makes no representations or warranties with respect to the accuracy or completeness of the contents of this publication and reserves the right to make changes to specifications and product descriptions at any time without notice.

No license, whether express, implied, arising by estoppel or otherwise, to any intellectual property rights, is granted by this publication. Except as provided in uPI' s terms and conditions of sale for such products, uPI assumes no liability whatsoever, and uPI disclaims any express or implied warranty relating to sale and/or use of uPI products, including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright or other intellectual property right. uPI products are not designed, intended, authorized or warranted for use as components in systems intended for medical, life-saving, or life sustaining applications. uPI reserves the right to discontinue or make changes to its products at any time without notice.

uPI, uPI design logo, and combinations thereof, are trademarks or registered trademarks of uPI Semiconductor Corp. Other product names used in this publication are for identification purposes only and may be trademarks of their respective companies.

uPI SEMI

QN4101M6N

N-Channel 40V Fast Switching MOSFET

General Description

The QN4101M6N is a high performance trench N-channel MOSFET which utilizes extremely high cell density to provide low Rdson and gate charge characteristics. It is ideally suited to support synchronous buck converter applications.

The QN4101M6N meets RoHS and Green Product requirements while supporting full function reliability.

Features

- ✓ Advanced high cell density Trench technology
- ✓ Green Device Available

Product Summary

V_{DS}	$R_{DS(ON)}$ max (V_{GS}=10V)	I_D (T_C=25 °C)
40V	2.3mΩ	136A

Applications

- ✓ Synchronous rectifier for Consumer/Computing /Industry Power Supply
- ✓ Motor
- ✓ Load Switch

Pin Configuration





Ordering Information

Order Number	Package Type	Top Marking
QN4101M6N	PRPAK5X6	

QN4101M6N

Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	40	V
V_{GS}	Gate-Source Voltage	±20	V
I_D@T_C=25°C	Continuous Drain Current, V_{GS} @ 10V[1]	136	A
I_D@T_C=100°C	Continuous Drain Current, V_{GS} @ 10V[1]	86	A
I_D@T_A=25°C	Continuous Drain Current, V_{GS} @ 10V[1]	23	A
I_D@T_A=70°C	Continuous Drain Current, V_{GS} @ 10V[1]	18	A
I_{DM}	Pulsed Drain Current[2]	272	A
EAS	Single Pulse Avalanche Energy[3]	526.7	mJ
I_{AS}	Avalanche Current	45.9	A
P_D@T_C=25°C	Total Power Dissipation[4]	69	W
P_D@T_A=25°C	Total Power Dissipation[4]	2	W
T_{STG}	Storage Temperature Range	-55 to 150	°C
T_J	Operating Junction Temperature Range	-55 to 150	°C

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance (> 10S)Junction-Ambient[1]	13	17	°C/W
$R_{\theta JA}$	Thermal Resistance Junction-Ambient[1]	45	59	°C/W
$R_{\theta JC}$	Thermal Resistance Junction-Case[1]	1.8	2.3	°C/W

QN4101M6N

N-Channel Electrical Characteristics

N-Channel Electrical Characteristics: (T_J=25 ℃, unless otherwise noted)						
Symbol	**Parameter**	**Conditions**	**Min**	**Typ**	**Max**	**Unit**
BV_{DSS}	Drain-Source Breakdown Voltage	V_{GS}=0V, I_D=250uA	40	--	--	V
$\triangle BV_{DSS}/\triangle T_J$	BVDSS Temperature Coefficient	Reference to 25°C, I_D=1mA	--	0.019	--	V/°C
$R_{DS(ON)}$	Static Drain-Source On-Resistance[2]	V_{GS}=10V, I_D=30A	--	1.8	2.3	mΩ
		V_{GS}=4.5V, I_D=20A	--	2.4	3.1	
$V_{GS(th)}$	Gate Threshold Voltage	V_{GS}=V_{DS}, I_D =250uA	1.2	--	2.5	V
$\triangle V_{GS(th)}$	$V_{GS(th)}$ Temperature Coefficient		--	-4.8	--	mV/°C
I_{DSS}	Drain-Source Leakage Current	V_{DS}=32V, V_{GS}=0V,T_J=25°C	--	--	1	uA
		V_{DS}=32V, V_{GS}=0V,T_J=55°C	--	--	5	
I_{GSS}	Gate-Source Leakage Current	V_{GS}=±20V, V_{DS}=0V	--	--	±100	nA
gfs	Forward Transconductance	V_{DS}=5V, I_D=20A	--	53	--	S
R_g	Gate Resistance	V_{DS}=0V, V_{GS}=0V, f=1MHz	--	1.0	--	Ω
Q_g	Total Gate Charge (10V)	V_{DS}=20V, V_{GS}=10V, I_D=20A	--	54.0	--	nC
Q_g	Total Gate Charge (4.5V)	V_{DS}=20V, V_{GS}=4.5V, I_D=20A	--	24.4	--	
Q_{gs}	Gate-Source Charge		--	12.3	--	
Q_{gd}	Gate-Drain Charge		--	5.8	--	
$t_{d(on)}$	Turn-On Delay Time	V_{DS}=20V, V_{GS}=10V, R_G=3.3Ω, I_D=20A	--	12.4	--	ns
t_r	Rise Time		--	43.3	--	
$t_{d(off)}$	Turn-Off Delay Time		--	42.4	--	
t_f	Fall Time		--	7.2	--	
C_{iss}	Input Capacitance	V_{DS}=20V, V_{GS}=0V, f=1MHz	--	3844	--	pF
C_{oss}	Output Capacitance		--	706	--	
C_{rss}	Reverse Transfer Capacitance		--	38	--	

QN4101M6N

Guaranteed Avalanche Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
EAS	Single Pulse Avalanche Energy[5]	V_{DD}=25V , L=0.5mH , I_{AS}=33A	272.25	--	--	mJ

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current [1,6]	V_G=V_D=0V, Force Current	--	136	--	A
I_{SM}	Pulsed Source Current[2,6]		--	272	--	A
V_{SD}	Diode Forward Voltage[2]	V_{GS}=0V, I_S=1A, T_J=25℃	--	0.7	1.2	V
t_{rr}	Reverse Recovery Time	I_F=20A, di/dt=100A/μs, T_J=25℃	--	36	--	nS
Q_{rr}	Reverse Recovery Charge		--	32	--	nC

Note:

1. Test data conducted with surface mount attachment to 1 inch^2, FR-4 board utilizing 2oz copper
2. Pulse Test. Pulse width ≦ 300uS, duty cycle ≦ 2%
3. EAS data is a maximum rating. The test condition is V_{DD}=25V, V_{GS}=10V, L=0.5mH
4. The power dissipation is limited by a 150°C maximum junction temperature
5. The Min. value is 100% EAS tested guarantee
6. The data is theoretically the same as I_D and I_{DM}. In real applications, it will be limited by total power

QN4101M6N

Typical Characteristics



Fig.1: Typical Output Characteristics



Fig.2: On-Resistance vs. Gate-Source



Fig.3: Forward Characteristics of Reverse



Fig.4: Gate-Charge Characteristics



Fig.5: Normalized $V_{GS(th)}$ vs. T_J



Fig.6: Normalized R_{DSON} vs. T_J

QN4101M6N



Fig.7: Drain-Source On-State Resistance



Fig.8: Transfer Characteristics



Fig.9: Capacitance



Fig.10: Safe Operating Area



Fig.11: Transient Thermal Impedance

Legal Notice

The contents of this document are provided in connection with uPI Semiconductor Corp. (“uPI”) products. uPI makes no representations or warranties with respect to the accuracy or completeness of the contents of this publication and reserves the right to make changes to specifications and product descriptions at any time without notice.

No license, whether express, implied, arising by estoppel or otherwise, to any intellectual property rights, is granted by this publication. Except as provided in uPI’s terms and conditions of sale for such products, uPI assumes no liability whatsoever, and uPI disclaims any express or implied warranty relating to sale and/or use of uPI products, including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright or other intellectual property right. uPI products are not designed, intended, authorized or warranted for use as components in systems intended for medical, life-saving, or life sustaining applications. uPI reserves the right to discontinue or make changes to its products at any time without notice.

Other product names used in this publication are for identification purposes only and may be trademarks of their respective companies.

uPI Semiconductor Corp.

9F.,No.5, Taiyuan 1st St. Zhubei City, Hsinchu, Taiwan, R.O.C.

TEL : 886.3.560.1666 FAX : 886.3.560.1888