

Features

- 5.1 Thru 200 Volt Voltage Range
- Glass Passivated Junction
- Available On Tape and Reel
- Halogen Free Available Upon Request By Adding Suffix "-HF"
- Moisture Sensitivity Level 1
- Epoxy Meets UL 94 V-0 Flammability Rating
- Lead Free Finish/RoHS Compliant (Note1) ("P" Suffix Designates RoHS Compliant. See Ordering Information)

Maximum Ratings

- Operating Junction Temperature Range: -65°C to +150°C
- Storage Temperature Range: -65°C to +150°C
- Thermal Resistance : 226°C/W Junction to Ambient
- Thermal Resistance : 20°C/W Junction to Lead
- Thermal Resistance : 22°C/W Junction to Case

Parameter	Symbol	Rating	Conditions
Steady State Power Dissipation	P_D	3.0W	Note 2
Maximum Forward Voltage	V_F	1.5V	$I_F=200mA$


Note: 1.High Temperature Solder Exemption Applied, see EU Directive Annex 7a.

2.Mounted on 5.0mm² (1oz thick) land areas.

Lead temperature at $T_L=75^\circ C$

3.0 Watt Surface Mount Silicon Zener Diodes 5.1V to 200V


SMB (DO-214AA) (LEAD FRAME)



DIMENSIONS

DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.079	0.103	2.00	2.62	
B	0.075	0.087	1.91	2.21	
C	0.002	0.008	0.05	0.20	
D	0.006	0.012	0.15	0.31	
E	0.030	0.060	0.76	1.52	
F	0.065	0.091	1.65	2.32	
G	0.200	0.220	5.08	5.59	
H	0.160	0.191	4.06	4.85	
J	0.130	0.155	3.30	3.94	

Suggested Solder Pad Layout



Electrical Characteristics @ 25°C Unless Otherwise Specified

MCC Part Number	Zener Voltage ⁽³⁾	Test Current	Maximum Dynamic Impedance	Knee Current	Knee Impedance	Maximum Reverse Current	Reverse Voltage	Maximum DC Zener Current	Marking Code
	V _Z	I _{ZT}	Z _{ZT} @ I _{ZT}	I _{ZK}	Z _{ZK}	I _R	V _R	I _{ZM}	
	V	mA	Ω	mA	Ω	μA	V	mA	
3SMBJ5918B	5.1	73.5	4	1	350	5	2	588	H18B
3SMBJ5919B	5.6	66.9	2	1	250	5	3	534	H19B
3SMBJ5920B	6.2	60.5	2	1	200	5	4	482	H20B
3SMBJ5921B	6.8	55.1	2.5	1	200	5	5.2	440	H21B
3SMBJ5922B	7.5	50	3	0.5	400	5	6	400	H22B
3SMBJ5923B	8.2	45.7	3.5	0.5	400	5	6.5	364	H23B
3SMBJ5924B	9.1	41.2	4	0.5	500	5	7	328	H24B
3SMBJ5925B	10	37.5	4.5	0.25	500	5	8	300	H25B
3SMBJ5926B	11	34.1	5.5	0.25	550	1	8.4	272	H26B
3SMBJ5927B	12	31.2	6.5	0.25	550	1	9.1	250	H27B
3SMBJ5928B	13	28.8	7	0.25	550	1	9.9	230	H28B
3SMBJ5929B	15	25	9	0.25	600	1	11.4	200	H29B
3SMBJ5930B	16	23.4	10	0.25	600	1	12.2	186	H30B
3SMBJ5931B	18	20.8	12	0.25	650	1	13.7	166	H31B
3SMBJ5932B	20	18.7	14	0.25	650	1	15.2	150	H32B
3SMBJ5933B	22	17	17.5	0.25	650	1	16.7	136	H33B
3SMBJ5934B	24	15.6	19	0.25	700	1	18.2	124	H34B
3SMBJ5935B	27	13.9	23	0.25	700	1	20.6	110	H35B
3SMBJ5936B	30	12.5	28	0.25	750	1	22.8	100	H36B
3SMBJ5937B	33	11.4	33	0.25	800	1	25.1	90	H37B
3SMBJ5938B	36	10.4	38	0.25	850	1	27.4	82	H38B
3SMBJ5939B	39	9.6	45	0.25	900	1	29.7	76	H39B
3SMBJ5940B	43	8.7	53	0.25	950	1	32.7	68	H40B
3SMBJ5941B	47	8	67	0.25	1000	1	35.8	62	H41B
3SMBJ5942B	51	7.3	70	0.25	1100	1	38.8	58	H42B
3SMBJ5943B	56	6.7	86	0.25	1300	1	42.6	52	H43B
3SMBJ5944B	62	6	100	0.25	1500	1	47.1	48	H44B
3SMBJ5945B	68	5.5	120	0.25	1700	1	51.7	44	H45B
3SMBJ5946B	75	5	140	0.25	2000	1	56	40	H46B
3SMBJ5947B	82	4.6	160	0.25	2500	1	62.2	36	H47B
3SMBJ5948B	91	4.1	200	0.25	3000	1	69.2	32	H48B
3SMBJ5949B	100	3.7	250	0.25	3100	1	76	30	H49B
3SMBJ5950B	110	3.4	300	0.25	4000	1	83.6	26	H50B
3SMBJ5951B	120	3.1	380	0.25	4500	1	91.2	24	H51B
3SMBJ5952B	130	2.9	450	0.25	5000	1	98.8	22	H52B
3SMBJ5953B	150	2.5	600	0.25	6000	1	114	20	H53B
3SMBJ5954B	160	2.3	700	0.25	6500	1	121.6	18	H54B
3SMBJ5955B	180	2.1	900	0.25	7000	1	136.8	16	H55B
3SMBJ5956B	200	1.9	1200	0.25	8000	1	152	14	H56B

Note : 3. TOLERANCE AND VOLTAGE DESIGNATION - The type numbers listed indicate a tolerance of +/-5%

Curve Characteristics

Fig. 1 - Power Derating Curve




Fig. 2 - Typical Zener Breakdown Characteristics




Fig. 3 - Typical Zener Breakdown Characteristics





Fig. 4 - Peak Pulse Power Rating Curve



Ordering Information

Device	Packing
Part Number-TP	Tape&Reel:3Kpcs/Reel

Note : Adding "-HF" Suffix For Halogen Free, eg. Part Number-TP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp** . does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp** . and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.