

C41

Water Cooled Resonant Capacitor

Water Cooled Resonant Capacitor C41-BB1



Characteristics

- Conduction water-cooled
- Polypropylene dielectric
- Low dissipation factor($\text{tg}\delta$), low ESL and low ESR
- High voltage, high frequency and high dv/dt
- High current resistance, excellent heat dissipation


Application

- Widely used in high power and high frequency resonant devices

Technical Data

● Reference standards	GB/T 3984-2004 IEC 60110.1
● Operating temperature range	-40°C~+85°C
● Capacitance range	0.1µF~85µF
● Rated capacitance	100kVar-1500 kVar
● Rated voltage	400VAC-1100VAC
● Tolerance	±5% ±10%
● Test voltage between terminals	1.5 U_{NAC} 10s
	3.5 U_{NDC} 10s at 25°C±5°C
● Dissipation factor	$\text{tg}\delta \leq 5 \times 10^{-4}$ at 25°C±5°C, 1kHz
● Insulation resistance	$R \cdot C \geq 3000\text{s}$, at 100VDC, 25°C±5°C, 60s
● Life expectancy	100000h at U_{N} and 70°C, 30000h at U_{rms}

Typical Circuit




C7 is the water-cooled capacitor in the series resonant capacitor


C41

Water Cooled Resonant Capacitor

Construction Diagram




Product Coding



C41

Water Cooled Resonant Capacitor

C41—BB1



Article Table

Part Number	Rated Voltage Vrms	Nominal Capacitance μF at 1Khz	Max Irms A	Max Power kVar	Freq Range @Full Power (kHz)	ESR mΩ	Dimension (mm)			Case Code
							L	H	T	
C41701334KBB1201***	700	0.33	300	200	196-216	1.0	50	50	36	BB1
C41601664KBB1201***	600	0.66	350	200	135-149	0.8	50	50	36	BB1
C41501125KBB1201***	500	1.20	400	200	105-105	0.5	50	50	36	BB1
C41501155KBB1201***	500	1.50	400	200	85-108	0.3	50	50	36	BB1
C41401265KBB1201***	400	2.60	550	200	80-96	0.2	50	50	36	BB1






Part Number	Rated Voltage Vrms	Nominal Capacitance μF at 1Khz	Max Irms A	Max Power kVar	Freq Range @Full Power (kHz)	ESR mΩ	Dimension (mm)			Case Code
							L	H	T	
C41102104KBB1301...	1000	0.10	350	300	476-649	1.2	50	50	36	BB1
C41102204KBB1301...	1000	0.20	400	300	238-423	1.2	50	50	36	BB1
C41701254KBB1301...	700	0.25	500	300	390-530	1.2	50	50	36	BB1
C41701334KBB1301...	700	0.33	500	300	295-401	1.0	50	50	36	BB1
C41701664KBB1301...	700	0.66	500	300	147-200	0.8	50	50	36	BB1
C41601105KBB1301...	600	1.00	650	300	132-223	0.5	50	50	36	BB1
C41601125KBB1301...	600	1.20	650	300	111-187	0.5	50	50	36	BB1
C41601135KBB1301...	600	1.32	650	300	100-170	0.3	50	50	36	BB1
C41501245KBB1301...	500	2.40	650	300	80-97	0.2	50	50	36	BB1
C41102104KBB1301...	1000	0.10	350	300	476-649	1.2	50	50	36	BB1

C41

Water Cooled Resonant Capacitor

Temperature Characteristics

—◆— Voltage —■— Current —▲— Power









C41

Water Cooled Resonant Capacitor

Temperature Characteristics

—●— Voltage —■— Current —▲— Power



C41

Water Cooled Resonant Capacitor

Temperature Characteristics

—●— Voltage —■— Current —▲— Power

