



Circuit Diagram

NO.2	
PART NO	vigor
1	90±30
2	130±30
3	180±30
4	250±30
5	350±50

NO.3	
PART NO	MATERIAL/QT
S	SUS/1PC
C	C5210/1PC
D	SUS/2PCS
F	C5210/2PCS

NO.4	
PART NO	L
A	8 10
B	8.5 11
C	9 11
D	9.5 12
E	10 12

NO.5-NO.6	
PART NO	NOTE
01~99	SERIAL NUMBER

NO.1			
PART NO	H	PART NO	H
A	4.3	0	11
B	4.5	P	11.5
C	5	Q	12
D	5.5	R	12.5
E	6	S	13
F	6.5	T	13.5
G	7	U	14
H	7.5	V	15
I	8	W	16
J	8.5	X	17
K	9	Y	18
L	9.5	Z	19
M	10		15.5
N	10.5		

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	4	Brass(0.30)	Plating silver	
④	Contact	—	1	F.Ag/SUS	—	
③	Base	—	1	Nylon	Black	
②	Cover	—	1	SPCC	Plating Nickel	
①	Keystoke	—	1	Nylon	Black	

APPROVALS

DRAWN xu qi feng 2014.11.10

TITLE: TACT SWITCHS

ELECTRONICS CO.,LTD

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

CHECKED	APPROVALS	TOLERANCES ARE	30°±0.1°	±0.30	ANGLE	PART NO.	UNIT:	SCALE:	PROJ.	SHEET
		10~30	±0.20	±2°	mm	K2-1102SP	mm	1:1		1 of 1