

650V N-Channel Silicon Carbide Power MOSFET

FEATURES


- Low On-Resistance
- Low Capacitance
- Avalanche Ruggedness
- Halogen Free, RoHS Compliant

BENEFITS

- Higher System Efficiency
- Parallel Device Convenience
- High Temperature Application
- High Frequency Operation







APPLICATIONS

- Switch Mode Power Supply (SMPS)
- Power Factor Correction (PFC)
- Uninterruptible Power Supply (UPS)
- EV Charging station & Motor Drives
- Solar/ Wind Renewable Energy
- Power Inverters & DC/DC Converters

Device Marking and Package Information				
Device	Package Marking			
C2M065W200	TO-247-3L	C2M065W200		

Absolute Maximum Ratings $T_C = 25^{\circ}C$, unless otherwise noted					
Parameter	Symbol	Test Conditions	Value	Unit	
Drain-Source Voltage	V _{DSS}	VGS=0V, IDS=100μA	650	V	
Continuous Drain Current	I _D	VGS=20V, Tc=25° C	10	_	
Pulsed Drain Current	I _{DM}	t _{PW} limitation per Fig.17	40	A	
Power Dissipation	P _D	Tc=25° C	338	W	
Recommend Gate Source Voltage	VGS, op	Static	-5/+20	V	
Maximum Gate Source Voltage	Vgs, max	AC (f > 1Hz)	-10/+25	V	
Soldering Temperature	T∟		260		
Operating Junction and Storage Temperature Range	T _J , T _{stg}		-55/+150	°C	

Thermal Resistance				
Parameter	Symbol	Value	Unit	
Thermal Resistance, Junction-to-Case	R _{thJC}	0.37	K/W	



-			Value			
rameter Symbol Test Conditions		Min.	Тур.	Max.	Unit	
Static						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	$V_{GS} = 0V, I_{D} = 100\mu A$	650			V
		$V_{DS} = 650V, V_{GS} = 0V, T_{J} = 25^{\circ}C$		<1	100	
Zero Gate Voltage Drain Current	I _{DSS}	$V_{DS} = 650V, V_{GS} = 0V, T_{J} = 150^{\circ}C$		10	500	μA
Gate-Source Leakage	I _{GSS}	$V_{GS} = 20V, V_{DS} = 0V$			200	nA
Gate-Source Threshold Voltage	V _{GS(th)}	$V_{DS} = 10V, I_{D} = 5mA$	2		3.5	V
Drain-Source On-Resistance	R _{DS(on)}	$V_{GS} = 20V, I_{D} = 5A$		230	275	mΩ
Dynamic						
Input Capacitance	C _{iss}	V _{GS} = 0V		308		pF
Output Capacitance	C _{oss}	$V_{DS} = 400V$ f = 1.0MHz		42		
Reverse Transfer Capacitance	C _{rss}	V _{AC} =25mV		11		
Effective Output Capacitance, Energy Related	Co(er)	VGS=0V V _{DS} =0 to 450V		187		
Effective Output Capacitance, Time Related	Co(tr)	I _D =const., VGS=0V V _{DS} =0 to 450V		253		
Total Gate Charge	Q_g			25.5		nC
Gate-Source Charge	Q_{gs}	V _{DS} =300V, VGS=0/+15V,		4.5		
Gate-Drain Charge	Q_{gd}	I _D =10A		14		
Gate plateau voltage	Vpl			12.5		V
Turn-on Delay Time	t _{d(on)}			36		
Turn-on Rise Time	t _r	V _{DS} =300V V _{GS} =0/15V		36.5		
Turn-off Delay Time	t _{d(off)}	$I_D=10A$ $RG(ext)=2.5\Omega$		40		ns
Turn-off Fall Time	t _f			7		
Coss Stored Energy	Eoss	V_{GS} =0V, V_{DS} =650V f =1MHz, V_{AC} =25mV		119		
Turn-on Switching Energy	Eon	V _{DS} =650V,		194*		μJ
Turn-off Switching Energy	Eoff	V_{GS} =0/15V, I_{D} =10A, $RG(ext)$ = 2.5 Ω		326*		
Internal Gate Resistance	RG(int.)	f =1MHz, Vac=25mV		26		Ω

^{*}Base on the results of calculation, note that the energy loss caused by the reverse recovery of FWD is not included in E on .



Built-in SiC Diode Characteristics						
Continuous Diode Forward Current	I _S	$V_{GS} = 0V$		10	-	А
Inverse Diode Forward Voltage	V _{SD}	$I_{SD} = 3A$, $V_{GS} = -5V$			6	V
Reverse Recovery Time	t _{rr}			12.5		ns
Reverse Recovery Charge	Q _{rr}	$I_F = 10A, V_{DS} = 105V,$ $di_F/dt = 500A/\mu s$		14.5	-	nC
Peak Reverse Recovery Current	IRM	333, 17 po	-	1.7	-	А




Fig. 1 Forward Output Characteristics at $T_j = 25$ °C




Fig. 3 On-Resistance vs. Drain Current for Various T_j




Fig. 2 Forward Output Characteristics at $T_j = 150$ °C




Fig. 4 Transfer Characteristics for Various \boldsymbol{T}_{j}






Fig. 5 On-Resistance vs. Gate Voltage for Various T_i




Fig. 7 Normalized On-Resistance vs.

Temperature




Fig. 9 Reverse Output Characteristics at $T_i = 25$ °C




Fig. 6 On-Resistance vs. Temperature for Various Gate Voltage




Fig. 8 Threshold Voltage vs. Temperature




Fig. 10 Reverse Output Characteristics at $T_i = 150$ °C






Fig. 11 Capacitances vs. Drain to Source Voltage (0 - 200V)




Fig. 13 Output Capacitor Stored Energy




Fig. 15 Drain Current Derating vs. Case Temperature




Fig. 12 Capacitances vs. Drain to Source Voltage (0 - 1000V)




Fig. 14 Maximum Power Dissipation Derating vs. Case Temperature




Fig. 16 Transient Junction to Case Thermal Impedance






Fig. 17 Safe Operating Area




Fig. 18 Gate Charge Characteristics




Fig. 19 Clamped Inductive Switching Energy vs. Drain Current (V_{DD}=1200V)*




Fig. 20 Clamped Inductive Switching Energy vs. Drain Current (V_{DD}=900V)*





Fig. 21 Clamped Inductive Switching Energy vs. External Gate Resistor (R_{G(ext.)})*

^{*}Base on the results of calculation, note that the energy loss caused by the reverse recovery of FWD is not included in E on .



TO-247



Unit: mm				
Symbol	Min.	Max.		
Α	15. 95	16. 25		
В	20. 85	21. 25		
С	20. 95	21. 35		
D	40. 5	40. 9		
Е	1.9	2. 1		
F	2. 1	2. 25		
G	3. 1	3. 25		
Н	1.1	1. 3		
I	5. 40	5. 50		

Unit: mm				
Symbol	Min.	Max.		
K	2. 90	3. 10		
L	4. 90	5. 30		
M	1. 90	2. 10		
N	4. 50	4. 70		
0	5. 40	5. 60		
Р	2. 29	2. 49		
Q	0. 51	0. 71		
R	ф 3. 5	ф 3. 7		
S	ф 7. 1	ф 7. 3		

^{*}The information provided herein is subject to change without notice.



Disclaimer

All product specifications and data are subject to change without notice.

For documents and material available from this datasheet, Suzhou Convert does not warrant or assume any legal liability or responsibility for the accuracy, completeness of any product or technology disclosed hereunder.

No license, express or implied, by estoppels or otherwise, to any intellectual property rights is granted by this document or by any conduct of Suzhou Convert.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless. Customers using or selling Suzhou Convert products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Suzhou Convert for any damages arising or resulting from such use or sale.

Suzhou Convert disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Suzhou Convert's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

Suzhou Convert SemiConductor CO., Ltd. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

In the event that any or all Suzhou Convert products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. Suzhou Convert believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.