

## **Features**

- Lead Free Finish/RoHS Compliant ("P" Suffix Designates RoHS Compliant. See Ordering Information)
- Epoxy Meets UL 94 V-0 Flammability Rating
- Moisture Sensitivity Level 1
- Low Capacitance
- Low Forward Resistance


## **Maximum Ratings**

- Operating Junction Temperature Range: -65°C to +150°C
- Storage Temperature Range: -65°C to +150°C
- Thermal Resistance: 120°C/W Junction to Soldering Point

Parameter	Symbol	Limits	Unit
Reverse Voltage	V <sub>R</sub>	50	V
Forward Current	I <sub>F</sub>	100	mA
Power Dissipation (T <sub>S</sub> =90°C)	$P_{D}$	500	mW


## Device Marking: A1

# Silicon RF Switching Diode



DIMENSIONS					
DIM INCHES		MM		NOTE	
DIIVI	MIN	MAX	MIN	MAX	INOTE
Α	0.090	0.107	2.30	2.70	
В	0.063	0.071	1.60	1.80	
С	0.045	0.053	1.15	1.35	
D	0.031	0.045	0.80	1.15	
E	0.010	0.016	0.25	0.40	
G	0.004	0.018	0.10	0.45	
Н	0.004	0.010	0.10	0.25	
J		0.006		0.15	

#### SUGGESTED SOLDER PAD LAYOUT







# Electrical Characteristics @ 25°C Unless Otherwise Specified

Parameter	Symbol	Min.	Max.	Max.	Conditions
Forward Voltage	V <sub>F</sub>			1.0V	I <sub>F</sub> =10mA
Reverse Current	I <sub>R1</sub>			20nA	V <sub>R</sub> =20V
	I <sub>R2</sub>			100nA	V <sub>R</sub> =50V
Diode Capacitance	C <sub>d1</sub>		1.8pF	2.0pF	V <sub>R</sub> =0V,f=1MHz
	C <sub>d2</sub>		1.1pF	1.5pF	V <sub>R</sub> =1V,f=1MHz
	C <sub>d3</sub>		0.8pF	1.0pF	V <sub>R</sub> =3V,f=1MHz
Diode Forward Resistance	R <sub>D1</sub>		0.45Ω	0.7Ω	I <sub>F</sub> =3mA,f=100MHz
	R <sub>D2</sub>		0.36Ω	0.5Ω	I <sub>F</sub> =10mA,f=100MHz
Reverse Resistance	1/gp		100ΚΩ		V <sub>R</sub> =1V,f=100MHz
Series Inductance	L <sub>S</sub>		2nH		



## **Curve Characteristics**







## **Ordering Information**

Device	Packing
Part Number-TP	Tape&Reel: 3Kpcs/Reel

#### \*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp**. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp**. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp**, and all the companies whose products are represented on our website, harmless against all damages.

#### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.