


BD CONNECTOR (13mm) 13.0mm pitch/Disconnectable Crimp style connectors



Board-to-wire crimping type connector with high withstanding voltage, used for power supply of large LCD (Liquid Crystal Display or Liquid Crystal Television) back light.

Secure locking mechanism prevents from coming off housing when handling the wire harness.

- Secure locking mechanism
- Space saving
- · High withstand voltage design
- · Crimping special wire

Specifications -

1.0A AC, DC (AWG #24) Current rating:

 Voltage rating: 3,000V AC, DC • Temperature range: -25°C to +85°C

(including temperature rise in applying

electrical current)

• Contact resistance: Initial value/10m Ω max.

After environmental testing/20m Ω max.

• Insulation resistance: 1,000M Ω min. • Withstanding voltage: 5,000V AC/minute

• Applicable wire: AWG #28 to #24

* Compliant with RoHS.


* Refer to "General Instruction and Notice when using Terminals and Connectors" at the end of this catalog.


* Contact JST for details.

Standards -

Recognized E60389

PC board layout (viewed from component side) and Assembly layout






Note: 1. Tolerances are non-cumulative: ±0.05mm for all centers.

2. The dimensions above should serve as a guideline. Contact JST for details.

BD CONNECTOR (13mm)

Contact



Model No.	Applicable wire		Insulation O.D. (mm)	O'ty / rool
	mm ²	AWG#	insulation O.D. (illin)	Q ty / Teel
SBHS-002T-P0.5A	0.08~0.22	28~24	0.9~1.7	10,000

Material and Finish

Phosphor bronze, tin-plated (reflow treatment)


RoHS compliance

Note: Contact JST for SBHS-002T-P0.5.

	Crimping	Applicator			
Contact	machine	Crimp applicator	Dies	Crimp applicator with dies	
CRUC COST DO FA	AP-K2N	MKS-L	MK/SBHS-002-05-BDA	APLMK SBHS002-05-BDA	
SBHS-002T-P0.5A		_	_	_	

Note: When using this housing, standard applicator and dies for SBHS contact can not be applied.

Housing




Circuits	Model No.	Q'ty / bag			
2	BDAMR-02VAS-3	1,000			
Material					

PBT+UL94V-0, natural (white)

RoHS compliance

Shrouded header



Circuits	Model No.	Q'ty / reel
2	SM02-BDAS-3-TB	1,500

Material and Finish

Press post: Copper alloy, nickel-undercoated, tin/copper alloy-plated Wafer: PPA, UL94V-0, natural (ivory) Solder tab: Copper alloy, nickel-undercoated, tin/copper alloy-plated

RoHS compliance This product displays (LF) on a label. Note: The product listed above is supplied on embossed tape.