# Reference Only

P.1/9

# GHz Noise Suppression Chip Ferrite Bead BLM18H Murata Standard Reference Specification [AEC-Q200]

# 1. Scope

This reference specification applies to Chip Ferrite Bead for Automotive Electronics BLM18H\_SH Series based on AEC-Q200.

# 2. Part Numbering

(ex.)

(1)Product ID (2)Type (3)Dimension (L×W) (4)Characteristics

(5)Typical Impedance at 100MHz

(6)Performance (7)Category(for Automotive Electronics) (8)Numbers of Circuit (9)Packaging (D:Taping)

#### 3. Rating

Customer	MURATA	Impedance (Ω) (Under Standard Testing Condition) <b>(*1)</b> (refer to below comment)		Current (mA)		DC Resistance (Ω max.) (*1) (refer to below comment)		Remark	ESD Rank 1C:1kV	
Part Number	Part Number	at 1GHz				Initial Values		Remark	10.1KV	
		at 100MHz		Typical	at 85°C	at 125°C	values	Testing		
	BLM18HG471SH1D	470±25%	400 min.	600	2	00	0.85	0.95	For	
	BLM18HG601SH1D	600±25%	450 min.	700	2	00	1.0	1.1	general	
	BLM18HG102SH1D	1000±25%	750 min.	1000	1	00	1.6	1.7	use	
	BLM18HD471SH1D	470±25%	700 min.	1000	1	00	1.2	1.3	For	
	BLM18HD601SH1D	600±25%	850 min.	1200	1	00	1.5	1.6	high speed	1C
	BLM18HD102SH1D	1000±25%	1100 min.	1700	Ę	50	1.8	1.9	signal line	
	BLM18HE601SH1D	600±25%	300 min.	600	800(*2)	600(*2)	0.25	0.30	For	
	BLM18HE102SH1D	1000±25%	500min.	1000	600(*2)	500(*2)	0.35	0.40	power line	
	BLM18HE152SH1D	1500±25%	750min.	1500	500(*2)	400(*2)	0.50	0.55		

• Operating Temperature : -55°C to +125°C • Storage Temperature : -55°C to +125°C

# (\*1)


# **Standard Testing Conditions**

< Unless otherwise specified >

Temperature : Ordinary Temp. (15 °C to 35 °C ) Humidity : Ordinary Humidity (25%(RH) to 85%(RH))

(Note) As for the Rated current marked with (\*2), Rated Current is derated as right figure depending on the operating temperature.


< In case of doubt > Temperature : 20°C±2 °C Humidity : 60%(RH) to 70%(RH) Atmospheric pressure : 86kPa to 106kPa





**Reference Only** 

# 4. Style and Dimensions



## 5. Marking

No marking.

# 6. Specifications

## 6-1. Electrical Performance

No.	Item	Specification	Test Method
6-1-1	Impedance	Meet item 3.	Measuring Frequency : 100MHz±1MHz , 1GHz±1MHz Measuring Equipment : KEYSIGHT 4291A or the equivalent Test Fixture : KEYSIGHT 16192A or the equivalent
6-1-2	DC Resistance	Meet item 3.	Measuring Equipment : Digital multi meter *Except resistance of the Substrate and Wire

#### 6-2. Mechanical Performance (based on Table 13 for FILTER EMI SUPPRESSORS/FILTERS) AEC-Q200 Rev.D issued June. 1 2010

No.		AEC-Q200	Murata Specification / Deviation
	Stress	Test Method	Murata Specification / Deviation
3	Temperature Set for 24hours at room Ta		Meet Table A after testing. <u>Table A</u>
	Exposure	temperature, then measured.	Appearance No damage
			Impedance Change Within ±30% (at 100MHz)
			DC Resistance Meet item 3.
4	Temperature Cycling	1000cycles -55 deg C to +125 deg C Set for 24hours at room temperature, then measured.	Meet Table B after testing. <u>Table B</u> <u>Appearance</u> No damage Impedance Within ±30% Change (BLM18HE (at 100MHz) Within±50%) DC Resistance Meet item 3.
5	Destructive Physical Analysis	Per EIA469 No electrical tests	No defects
7	Biased Humidity	1000hours at 85 deg C, 85%RH Apply max rated current.	Meet Table B after testing.
8	Operational Life	Apply 125 deg C 1000hours Set for 24hours at room temperature, then measured	Meet Table B after testing.
9	External Visual	Visual inspection	No abnormalities

MURATA MFG.CO., LTD.


**Reference Only** 

No.		AEC-Q200	Munata Canadiliantian / Deviation	
INO.	Stress	Test Method	Murata Specification / Deviation	
10	Physical Dimension	Meet ITEM 4 (Style and Dimensions)	No defects	
12	Resistance to Solvents	Per MIL-STD-202 Method 215	Not Applicable	
13	Mechanical Shock	Per MIL-STD-202 Method 213 Condition F 1500g(14.7N)/0.5ms/Half sine	Meet Table A after testing.	
14	Vibration	5g's(0.049N) for 20 minutes, 12cycles each of 3 orientations Test from 10-2000Hz.	Meet Table A after testing.	
15	Resistance to Soldering Heat	Solder temperature 260C+/-5 deg C Immersion time 10s	Pre-heating:150C +/-10 deg,60s to 90s Meet Table B after testing.	
17	ESD	Per AEC-Q200-002	Meet Table A after testing. ESD Rank:Meet Item 3. (Rating)	
18	Solderability	Per J-STD-002	Method b : Not Applicable 95% of the terminations is to be soldered.	
19	Electrical Characterization	Measured : Impedance	No defects	
20	Flammability	Per UL-94	Not Applicable	
21	Board Flex	Epoxy-PCB 1.6mm Deflection 2mm(min) 60s minimum holding time	Meet Table A after testing.	
22	Terminal Strength	Per AEC-Q200-006	No defects	
30	Electrical Transient Conduction	Per ISO-7637-2	Not Applicable	



# 7. Specification of Packaging

7-1. Appearance and Dimensions (8mm-wide paper tape)



#### (1) Taping

Products shall be packaged in the cavity of the base tape of 8mm-wide,4mm-pitch continuously and sealed by top tape and bottom tape.

(2) Sprocket hole

The sprocket holes are to the right as the tape is pulled toward the user.

(3) Spliced point

The base tape and top tape have no spliced point

(4) Cavity

There shall not be burr in the cavity.

(5) Missing components number

Missing components number within 0.1% of the number per reel or 1 pc., whichever is greater, and are not continuous. The specified quantity per reel is kept.


# 7-2. Tape Strength

(1)Pull Strength

Top tape	5N min.
Bottom tape	_

(2)Peeling off force of Top tape

0.1N to 0.6N (Minimum value is typical.) \*Speed of Peeling off:300mm/min



# 7-3. Taping Condition

(1)Standard quantity per reel

Quantity per 180mm reel: 4000 pcs. / reel

(2)There shall be leader-tape (top tape and empty tape ) and trailer- tape(empty tape) as follows.

(3)On paper tape, the top tape and the base tape shall not be adhered at the tip of the empty leader tape for more than 5 pitch.

(4)Marking for reel

The following items shall be marked on a label and the label is stuck on the reel.

(Customer part number, MURATA part number, Inspection number(\*1), RoHS marking(\*2), Quantity, etc)

<li>*1) « Expression of Inspection</li>	on No. »	$ \begin{array}{c c} \square \\ \hline (1) \\ \hline (2) \\ \hline (3) \end{array} \times $
(1) Factory Code		
(2) Date	First digit	: Year / Last digit of year
	Second digit	: Month / Jan. to Sep. $\rightarrow$ 1 to 9, Oct. to Dec. $\rightarrow$ O, N, D
	Third, Fourth d	ligit : Day
(3) Serial No.		
*2) « Expression of RoHS n	narking »	ROHS – <u>Y</u> ( <u>△</u> )
		(1) (2)

(1) RoHS regulation conformity parts.

(2) MURATA classification number

MURATA MFG.CO., LTD.

P.4/9




P.5/9

(5) Outside package


These reels shall be packed in the corrugated cardboard package and the following items shall be marked on a label and the label is stuck on the box.

(Customer name, Purchasing Order Number, Customer Part Number, MURATA part number, RoHS marking(\*2), Quantity, etc)

(6) Dimensions of reel and taping (leader-tape, trailer-tape)



# 7-4. Specification of Outer Case



# 8. \land Caution

#### 8-1.Rating

Do not use products beyond the Operating Temperature Range and Rated Current.

#### 8-2.Surge current

Excessive surge current (pulse current or rush current) than specified rated current applied to the product may cause a critical failure, such as an open circuit, burnout caused by excessive temperature rise. Please contact us in advance in case of applying the surge current.

#### 8-3. Fail Safe

Be sure to provide an appropreate fail-safe function on your product to prevent from a second damage that may be caused by the abnormal function or the failure of our products.

#### 8-4. Limitation of Applications

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property.

- (1)Aircraft equipment
- (2)Aerospace equipment (3)Undersea equipment
- (4)Power plant control equipment (5)Medical equipment (6)Disaster prevention / crime prevention equipment (7)Traffic signal equipment (8)Transportation equipment (trains, ships, etc.)
- (9)Data-processing equipment

(10)Applications of similar complexity and /or reliability requirements to the applications listed in the above




#### 9. Notice

This product is designed for solder mounting.

Please consult us in advance for applying other mounting method such as conductive adhesive.

#### 9-1. Land pattern designing

• Standard land dimensions (Flow and Reflow soldering)



(in mm)

b

2.5

2.0

С

0.7

0.7

#### 9-2. Soldering conditions

Products can be applied to reflow and flow soldering.

(1) Flux, Solder

Flux	Use rosin-based flux, but not highly acidic flux (with chlorine content exceeding 0.2(wt)%.) Do not use water-soluble flux.
Solder	Use Sn-3.0Ag-0.5Cu solder Standard thickness of solder paste : 100 μm to 200 μm


#### (2) Soldering conditions


• Pre-heating should be in such a way that the temperature difference between solder and ferrite surface is limited to 150°C max. Also cooling into solvent after soldering should be in such a way that the temperature difference is limited to 100°C max.

Insufficient pre-heating may cause cracks on the ferrite, resulting in the deterioration of product quality.

• Standard soldering profile and the limit soldering profile is as follows.

The excessive limit soldering conditions may cause leaching of the electrode and / or resulting in the deterioration of product quality.






	Standard Profile	Limit Profile
Pre-heating	150°C, 60s min.	
Heating	250°C, 4s~6s	265°C±3°C, 5s max.
Cycle of flow	2 times	2 times

Reference Only

P.7/9

□Reflow soldering profile




	Standard Profile	Limit Profile
Pre-heating	150°C~180°C, 90s±30s	
Heating	above 220°C, 30s~60s	above 230°C, 60s max.
Peak temperature	245°C±3°C	260°C, 10s
Cycle of reflow	2 times	2 times

#### 9-3. Reworking with soldering iron

- Pre-heating: 150°C, 1 min
- Soldering iron output: 80W max.
- Tip temperature: 350°C max. • Tip diameter:  $\phi$  3mm max.
  - Times : 2times max.
- Soldering time : 3(+1,-0) seconds. Note : Do not directly touch the products with the tip of the soldering iron in order to prevent the crack on the ferrite material due to the thermal shock.

#### 9-4. Solder Volume

Solder shall be used not to be exceeded as shown below.




Accordingly increasing the solder volume, the mechanical stress to product is also increased. Exceeding solder volume may cause the failure of mechanical or electrical performance.



#### 9-5. Attention regarding P.C.B. bending

Spec. No. JENF243A-9104F-01

- The following shall be considered when designing and laying out P.C.B.'s.
- (1) P.C.B. shall be designed so that products are not subject to the mechanical stress for board warpage. <Products direction>




Products shall be located in the sideways direction (Length:a<br/>b) to the mechanical stress.

(2)Components location on P.C.B. separation.

It is effective to implement the following measures, to reduce stress in separating the board. It is best to implement all of the following three measures; however, implement as many measures as possible

to reduce stress.


Contents of Measures	Stress Level
(1) Turn the mounting direction of the component parallel to the board separation surface.	A > D*1
(2) Add slits in the board separation part.	A > B
(3) Keep the mounting position of the component away from the board separation surface.	A > C



\*1 A > D is valid when stress is added vertically to the perforation as with Hand Separation. If a Cutting Disc is used, stress will be diagonal to the PCB, therefore A > D is invalid.

#### (3) Mounting Components Near Screw Holes

When a component is mounted near a screw hole, it may be affected by the board deflection that occurs during the tightening of the screw. Mount the component in a position as far away from the screw holes as possible.



#### 9-6. Mounting density

Add special attention to radiating heat of products when mounting the inductor near the products with heating. The excessive heat by other products may cause deterioration at joint of this product with substrate.

#### 9-7. Operating Environment

Do not use this product under the following environmental conditions, on deterioration of the Insulation Resistance of the Ferrite material and/or corrosion of Inner Electrode may result from the use.

(1) in the corrodible atmosphere such as acidic gases, alkaline gases, chlorine, sulfur gases, organic gases and etc. (the sea breeze, Cl<sub>2</sub>, H<sub>2</sub>S, NH<sub>3</sub>, SO<sub>2</sub>, NO<sub>2</sub>,etc)

(2) in the atmosphere where liquid such as organic solvent, may splash on the products.

(3) in the atmosphere where the temperature / humidity changes rapidly and it is easy to dew.



#### 9-8. Resin coating

The impedance value may change and/or it may affect on the product's performance due to high cure-stress of resin to be used for coating / molding products. So please pay your careful attention when you select resin. In prior to use, please make the reliability evaluation with the product mounted in your application set.

#### 9-9. Cleaning Conditions

Products shall be cleaned on the following conditions.

(1)Cleaning temperature shall be limited to 60°C max. (40°C max. for IPA)

(2)Ultrasonic cleaning shall comply with the following conditions, avoiding the resonance phenomenon at the mounted products and P.C.B.

Power : 20W/I max.

Frequency : 28kHz to 40kHz

Time : 5 min max.

(3)Cleaner

1.Cleaner

Isopropyl alcohol (IPA)

2.Aqueous agent

•PINE ALPHA ST-100S

(4)There shall be no residual flux and residual cleaner after cleaning.

In the case of using aqueous agent, products shall be dried completely after rinse with de-ionized water in order to remove the cleaner.

(5)Other cleaning

Please contact us.

#### 9-10. Handling of a substrate

After mounting products on a substrate, do not apply any stress such as bending or twisting to the substrate when cropping the substrate, inserting and removing a connector from the substrate or tightening screw to the substrate. Excessive mechanical stress may cause cracking in the Product.

Bending

Twisting



#### 9-11. Storage Conditions

(1)Storage period

Use the products within 6 months after delivered.

Solderability should be checked if this period is exceeded.

(2)Storage conditions

• Products should be stored in the warehouse on the following conditions.

- Temperature : -10°C to 40°C
- Humidity : 15% to 85% relative humidity
- No rapid change on temperature and humidity
- Don't keep products in corrosive gases such as sulfur, chlorine gas or acid, or it may cause oxidization of electrode, resulting in poor solderability.
- Products should be stored on the palette for the prevention of the influence from humidity, dust and so on.
- Products should be stored in the warehouse without heat shock, vibration, direct sunlight and so on.
- Products should be stored under the airtight packaged condition.

#### (3)Delivery

Care should be taken when transporting or handling product to avoid excessive vibration or mechanical shock.

# 10. 🗥 Note

- (1)Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.
- (2)You are requested not to use our product deviating from the agreed specifications.
- (3) The contents of this reference specification are subject to change without advance notice. Please approve our product specifications or transact the approval sheet for product specifications before ordering.