



PARA LIGHT ELECTRONICS CO., LTD.

11F, No.8, Jiankang Rd,Zhonghe Dist,New Taipei City 253, Taiwan

Tel: 886-2-2225-3733

Fax: 886-2-2225-4800

E-mail: para@para.com.tw

<http://www.para.com.tw>

DATA SHEET

PART NO.:L-C295JGJRCT

REV: A / 1

CUSTOMER'S APPROVAL: _____

DCC: _____


DRAWING NO.: DS-78-18-005G

DATE:2019-4-17

PAGE

1 of 14

● PACKAGE OUTLINE DIMENSIONS



Note:

1. All dimensions are in millimeters.
2. Tolerance is $\pm 0.1\text{mm}$ (.004") unless otherwise noted

● Features

- * Dual color, top view, wide view angle Chip LED.
- * Package in 8mm tape on 7" diameter reels.
- * Compatible with automatic Pick & Place equipment.
- * Compatible with Reflow soldering and Wave soldering processes.
- * EIA STD package.
- * I.C. compatible.
- * Pb free product.



SURFACE MOUNT DEVICE LED

Part No.:L-C295JGJRCT

REV:A / 1

● Chip Materials

chip	Light Color	Dice Material	Lens Color
JR	Red	AlGaInP	Water Clear
JG	Green	AlGaInP	

● Absolute Maximum Ratings (Ta=25°C)

Symbol	Parameter	Rating		Unit
		Red	Green	
PD	Power Dissipation	75	76	mW
IPF	Peak Forward Current (1/10 Duty Cycle, 0.1ms Pulse Width)	80	80	mA
IF	Continuous Forward Current	30	20	mA
-	De-rating Linear From 25°C	0.25	0.25	mA/°C
VR	Reverse Voltage	5	5	V
ESD	Electrostatic Discharge Threshold (HBM) ^{Note A}	2000	1000	V
Topr	Operating Temperature Range	-20 ~ +80		°C
Tstg	Storage Temperature Range	-40 ~ +85		°C
-	Wave Soldering Condition (Two times Max.)	260 (for 5 seconds)		°C

Note A:

HBM: Human Body Model. Seller gives no other assurances regarding the ability of to withstand ESD.

● Electro-Optical Characteristics (Ta=25°C)

SYMBOL		PARAMETER	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
VF	Red	Forward Voltage	IF = 20mA	1.85	1.9	2.15	V
	Green			1.85	2.0	2.15	
IV	Red	Luminous Intensity	IF = 20mA	35.5	47.5	71	mcd
	Green			14	20.5	28	
2θ1/2		Half Intensity Angle	IF = 20mA		130		deg
λD	Red	Dominant Wavelength	IF = 20mA	624		633	nm
	Green			567		576	
λp	Red	Peak Emission Wavelength	IF = 20mA		639		nm
	Green				563		
Δλ	Red	Spectral Line Half-Width	IF = 20mA		17		nm
	Green				35		
IR	Red	Reverse Current	VR = 5V			10	μA
	Green					50	

Notes:

1. Luminous intensity is measured with a light sensor and filter combination that proximates the CIE eye-response curve.
2. $\theta_{1/2}$ is the off-axis angle at which the luminous intensity is half the axial luminous intensity.
3. The dominant wavelength λ_d is derived from the CIE chromaticity diagram and represents the single wavelength which defines the color of the device.
4. Caution in ESD:
Static Electricity and surge damages the LED. It is recommended use a wrist band or anti-electrostatic glove when handling the LED. All devices, equipment and machinery must be properly grounded.
5. Major standard testing equipment by "Instrument System" Model: CAS140B Compact Array Spectrometer and "KEITHLEY" Source Meter Model: 2400.

● Typical Electro-Optical Characteristics Curves




Fig.1 Red Relative Intensity vs. Wavelength




Fig.1 Super Green Relative Intensity vs. Wavelength

● Red Typical Electro-Optical Characteristics Curves

(25°C Ambient Temperature Unless Otherwise Noted)




Fig.2 Forward Current vs.Forward Voltage




Fig.3 Luminous Intensity vs.Forward Current




Fig.4 Relative Luminous Intensity vs.Forward Current




Fig.5 Luminous Intensity vs.Ambient Temperature




Fig.6 Forward Current Derating Curve




Fig.7 Relative Intensity vs.Angle

● Super Green Typical Electro-Optical Characteristics Curves

(25°C Ambient Temperature Unless Otherwise Noted)




Fig.2 Forward Current vs.Forward Voltage




Fig.3 Luminous Intensity vs.Forward Current




Fig.4 Relative Luminous Intensity vs.Forward Current




Fig.5 Luminous Intensity vs.Ambient Temperature




Fig.6 Forward Current Derating Curve




Fig.7 Relative Intensity vs.Angle



SURFACE MOUNT DEVICE LED

Part No.:L-C295JGJRCT

REV:A / 1

● Label Explanation



ITEM CODE:PARA LIGHT

PART NO:L-C295JGJRCT

IV --- Luminous Intensity Code

LOT NO:	<u>EM</u>	<u>S</u>	<u>L</u>	<u>12</u>	<u>09</u>	<u>0110</u>
	A	B	C	D	E	F

A---EM: Emos Code

B---S:SMD

L---Local

D---Year

E---Month

F---SPEC.

PACKING QUANTITY OF BAG :

3000pcs for 150、170、110、155、115 series

4000pcs for 191 series

5000pcs for 192 series


DATE CODE:	<u>2012</u>	<u>09</u>	<u>10</u>
	G	H	I

G--- Year

H--- Month

I--- Day


● Reel Dimensions



Notes:

1. Taping Quantity: 4000pcs
2. The tolerances unless mentioned is $\pm 0.1\text{mm}$, Angle $\pm 0.5^\circ$, Unit: mm.

● Package Dimensions Of Tape And Reel




Notes: All dimensions are in millimeters.


● Cleaning

- * If cleaning is required , use the following solutions for less than 1 minute and less than 40°C.
- * Appropriate chemicals: Ethyl alcohol and isopropyl alcohol.
- * Effect of ultrasonic cleaning on the LED resin body differs depending on such factors as the oscillator output, size of PCB and LED mounting method. The use of ultrasonic cleaning should be enforced at proper output after confirming there is no problem.


● Suggest Soldering Pad Dimensions



● Suggest Sn/Pb IR Reflow Soldering Profile Condition:



● Suggest Pb-Free IR Reflow Soldering Profile Condition:





SURFACE MOUNT DEVICE LED

Part No.:L-C295JGJRCT

REV:A / 1

● Bin Code List

Luminous Intensity (IV), Unit: mcd@20mA					
Red			Super Green		
Bin Code	Min	Max	Bin Code	Min	Max
N2	35.5	45	L2	14	18
P1	45	56	M1	18	22.4
P2	56	71	M2	22.4	28

Tolerance of each bin are $\pm 15\%$

Dominant Wavelength (Hue), Unit: nm@20mA		
Red		
Bin Code	Min	Max
R1	624	627
R2	627	630
R3	630	633

Tolerance of each bin are $\pm 1\text{nm}$

Dominant Wavelength (Hue), Unit: nm@20mA		
Super Green		
Bin Code	Min	Max
GA	567	570
GB	570	573
GC	573	576



SURFACE MOUNT DEVICE LED

Part No.:L-C295JGJRCT

REV:A / 1

● CAUTIONS

1.Application Limitation:

The LED's described here are intended to be used for ordinary electronic equipment (such as office equipment, communication equipment and household application). Consult PARA's sales in advance for information on application in which exceptional quality and reliability are required, particularly when the failure or malfunction of the LED's may directly jeopardize life or health (such as airplanes, automobiles, traffic control equipment, life support system and safety devices).

2.Storage:

Do not open moisture proof bag before the products are ready to use.

Before opening the package: The LEDs should be kept at 30°C or less and 90%RH or less.

After opening the package: The LED's floor life is 1 year under 30°C or less and 60% RH or less. If unused LEDs remain, it should be stored in moisture proof packages.

If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.

Baking treatment: 60±5°C for 24 hours

3.Soldering

Do not apply any stress to the lead frame during soldering while the LED is at high temperature.

Recommended soldering condition.

Reflow Soldering:

Pre-heat 120~150°C, 120sec. MAX., Peak temperature : 240°C Max. Soldering time: 10 sec Max.

Soldering Iron: (Not recommended)

Temperature 300°C Max., Soldering time : 3 sec. Max.(one time only), power dissipation of iron : 20W Max. use SN60 solder of solder with silver content and don't to touch LED lens when soldering.

Wave soldering:

Pre-heat 100°C Max, Pre-heat time 60 sec. Max, Solder wave 260°C Max, Soldering time 5 sec. Max. preformed consecutively cooling process is required between 1st and 2nd soldering processes.

4. Lead-Free Soldering

For Reflow Soldering:

- 1、Pre-Heat Temp:150-180°C,120sec.Max.
- 2、Soldering Temp: Temperature Of Soldering Pot Over 230°C,40sec.Max.
- 3、Peak Temperature:260°C , 5sec.
- 4、Reflow Repetition:2 Times Max.
- 5、Suggest Solder Paste Formula 93.3 Sn/3.1 Ag/3.1 Bi /0.5 Cu


For Soldering Iron (Not Recommended):

- 1、Iron Tip Temp:350°C Max.
- 2、Soldering Iron:30w Max.
- 3、Soldering Time:3 Sec. Max. One Time.

For Dip Soldering:

- 1、Pre-Heat Temp:150°C Max. 120 Sec. Max.
- 2、Bath Temp:265°C Max.
- 3、Dip Time:5 Sec. Max.

5. Drive Method



(A)Recommended circuit.

(B)The difference of brightness between LED`s could be found due to the Vf-If characteristics of LED.