

## **Product Overview**

## AR0140CS: CMOS Image Sensor, 1.0 MP, 1/4"

For complete documentation, see the data sheet.

ON Semiconductor's AR0140CS is a 1/4-inch CMOS digital image sensor with an active-pixel array of 1280Hx800V. It captures images in either linear or high dynamic rangemodes, with a rolling-shutter readout. It includes sophisticated camera functions such as in-pixel binning, windowing and both video and single frame modes. It is designed for both low light and high dynamic range scene performance. It is programmable through a simple two-wire serial interface. TheAR0140CS produces extraordinarily clear, sharp digital pictures, and its ability to capture both continuous video and single frames makes it the perfect choice for a wide range of applications.

## **Features**

· High Dynamic Range

## **Applications**

· Security

Part Electrical Specifications												
Product	Pricing (\$/Unit)	Compliance	Status	Туре	Megapix els	Frame Rate (fps)	Optical Format	Shutter Type	Pixel Size (µm)	Output Interface	Color	Package Type
AR0140CS2C00SUEA0 -DRBR		Pb-free Halide free	Active	CMOS	1	60	1/4 inch	Electroni c Rolling	3.0 x 3.0	Multi	RGB	IBGA-63
AR0140CS2C00SUEA0 -DRBR1		Pb-free Halide free	Active	CMOS	1	60	1/4 inch	Electroni c Rolling	3.0 x 3.0	Multi	RGB	IBGA-63

For more information please contact your local sales support at www.onsemi.com.

Created on: 8/21/2020