

ON Semiconductor® FCH104N60F-F085

N-Channel SuperFET II FRFET MOSFET

600 V, 37 A, 104 mΩ

Features


- Typical R_{DS(on)} = 91 mΩ at V_{GS} = 10 V, I_D = 18.5 A
- Typical Q_{q(tot)} = 109 nC at V_{GS} = 10V, I_D = 18.5 A
- UIS Capability
- Qualified to AEC Q101
- RoHS Compliant

Description

SuperFET® II MOSFET is ON Semiconductor's brand-new high voltage super-junction (SJ) MOSFET family that is utilizing charge balance technology for outstanding low on-resistance and lower gate charge performance. This technology is tailored to minimize conduction loss, provide superior switching performance, dv/dt rate and higher avalanche energy. Consequently SuperFETII is very well suited for the Soft switching and Hard Switching topologies like High Voltage Full Bridge and Half Bridge DC-DC, Interleaved Boost PFC, Boost PFC for HEV-EV automotive. SuperFET II FRFET® MOSFET's optimized body diode reverse

recovery performance can remove additional component and improve system reliability.

Maximum Ratings T_C = 25°C unless otherwise noted



Application



Automotive DC/DC converter for HEV

Symbol	Parameter		Ratings	Units	
V _{DSS}	Drain to Source Voltage		600	V	
V _{GS}	Gate to Source Voltage		±20	V	
		T _C = 25°C	37	А	
ID	Drain Current - Continuous (V _{GS} =10) (Note 1)	T _C = 25°C T _C = 100°C	24	А	
	Pulsed Drain Current		See Fig 4	Α	
E _{AS}	Single Pulse Avalanche Rating	(Note 2)	809	mJ	
dv/dt	MOSFET dv/dt		100	1//20	
	Peak Diode Recovery dv/dt	(Note 3)	50	V/ns	
P _D	Power Dissipation		357	W	
	Derate Above 25°C		2.85	W/ºC	
T _J , T _{STG}	Operating and Storage Temperature		-55 to + 150	°C	
$R_{\theta JC}$	Maximum Thermal Resistance Junction to Case		0.35	°C/W	
R _{0JA}	Maximum Thermal Resistance Junction to Ambie	ent (Note 4)	40	°C/W	

Package Marking and Ordering Information

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
FCH104N60F	FCH104N60F-F085	TO-247	-	-	30


Notes:


1: Current is limited by bondwire configuration.

2: Starting T_J = 25°C, L = 35mH, I_{AS} = 6.8A, V_{DD} = 100V during inductor charging and V_{DD} = 0V during time in avalanche. 3: I_{SD} ≤ 18.5A, di/dt ≤ 200 A/us, V_{DD} ≤ 380V, starting T_J = 25°C.


4: R_{0JA} is the sum of the junction-to-case and case-to-ambient thermal resistance, where the case thermal reference is defined as the solder mounting surface of the drain pins. R_{0JC} is guaranteed by design, while R_{0JA}is determined by the board design. The maximum rating presented here is based on mounting on a 1 in² pad of 2oz copper.


Symbol	Parameter	Test Conditions		Min	Тур	Max	Units
Off Cha	racteristics						
B _{VDSS}	Drain to Source Breakdown Voltage	I _D = 250μA, V _{GS} = 0V		600	-	-	V
	Drain to Source Lookage Current	V _{DS} =600V,		-	-	10	μA
IDSS	Drain to Source Leakage Current	$V_{GS} = 0V$	$T_J = 150^{\circ}C(Note 5)$	-	-	1	mA
I _{GSS}	Gate to Source Leakage Current	$V_{GS} = \pm 20V$		-	-	±100	nA
On Cha	racteristics						
V _{GS(th)}	Gate to Source Threshold Voltage	V _{GS} = V _{DS} , I _D = 250μA		3.0	4.0	5.0	V
00(11)		I _D = 18.5A,	T _J = 25 ^o C	-	91	104	mΩ
r _{DS(on)}	Drain to Source On Resistance	V _{GS} = 10V	$T_{\rm J} = 150^{\rm o} {\rm C}({\rm Note}\ 5)$	-	217	275	mΩ
-	c Characteristics				4000		
C _{iss}	Input Capacitance Output Capacitance	V _{DS} = 100V, V _{GS} = 0V, f = 1MHz		-	4302 134	-	pF
C _{oss}	Reverse Transfer Capacitance			-	1.7	-	pF pF
C _{rss} R _g	Gate Resistance	f = 1MHz			0.49	_	Ω
Q _{g(ToT)}	Total Gate Charge	1 - 110112		-	109	139	nC
$Q_{g(th)}$	Threshold Gate Charge	V _{DD} = 380V		-	8	11	nC
Q _{gs}	Gate to Source Gate Charge	I _D = 18.5A V _{GS} = 10V		-	23	-	nC
Q _{gd}	Gate to Drain "Miller" Charge			-	46	-	nC
	ing Characteristics				50		
t _{on}	Turn-On Time Turn-On Delay Time			-	58 35	78	ns
t _{d(on)}	Rise Time		- 19 5 4	-	23	-	ns ns
t _r t _{d(off)}	Turn-Off Delay Time	V _{DD} = 380V, V _{GS} = 10V, R			94	_	ns
t _f	Fall Time		6	-	5	-	ns
t _{off}	Turn-Off Time			-	98	131	ns
	ource Diode Characteristics				I	I	
V _{SD}	Source to Drain Diode Voltage	I _{SD} = 18.5A, V _{GS} = 0V		-	-	1.2	V
Trr	Reverse Recovery Time	I _F = 18.5A, dI _{SD} /dt = 100A/μs V _{DD} = 480V		-	162	-	ns
Q _{rr}	Reverse Recovery Charge			-	1223	-	nC
Notes: 5: The max	imum value is specified by design at T_J = 150	0°C. Product is not	tested to this condition	in produc	tion.		






www.onsemi.com 4





www.onsemi.com 6



www.onsemi.com 7

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such uninten

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative