



# HSF

**NOTES:**

Current Rating: 2.0AMP  
 Contact Resistance: 20mΩ Max  
 Withstand Voltage: 500V AC/DC  
 Insulation Resistance: 1000MΩ Min  $\Delta_2$   
 Operation Temperature: -40℃ to +125℃(Au)  
 -40℃ to +105℃(Sn)

Contact Material: Phosphor Bronze  
 Contact plating: Au Or Sn over Ni  
 Insulator Material: PA9T+33%GF UL94V-0

Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



## Ordering Information

2243N-2 XX S XX CUN T 2

No. of Pins per Row: 02-50Pin

Contact Plating:  
 G0=Gold Flash  
 G3=10μ"Gold  
 G4=15μ"Gold  
 G5=30μ"Gold  
 S0=Gold Flash/Tin  
 S3=10μ"Gold/Tin  
 S4=15μ"Gold/Tin  
 S5=30μ"Gold/Tin  
 SN=Tin  
 SM=Matte Tin

Packing:  
 T=Tube  
 P=Tube+CAP  
 R=Tape&Reel+CAP

Item	Pitch	Mating
Standard	2.00	1215/1220/3111
Alternate		

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW XSR	DATE	SCALE	FIT	PART NO.
A2	2019/11/11	Modify Drawing	-----	x.x ±0.40		2019/11/11	UNIT	mm	2243N-2XXSXXCUNT2
A1	2014/04/11	Modify drawing	-----	x.xx ±0.25	CHECK	DATE	SIZE	A4	TITLE:
A0	2012/07/12	NEW	-----	x.xxx ±0.15	APPROVE	DATE	SHEET	1/1	FH2.00 DUAL ROW 180°WITH BUMP H=4.3 W=4.0
				Angle ± 3°			PROJ.		Customer NO.
				DIM TOL					

# WCON

Http: www.wcon.com

WCON-Dongguan  
 Tel: +86 769 85358920  
 Fax: +86 769 85358915  
 E-mail: sales@wcon.com

WCON-Kunshan  
 Tel: +86 512 57468408  
 Fax: +86 512 57468468  
 E-mail: salesks@wcon.com