

ON Semiconductor®

FDG6332C-F085

20V N & P-Channel PowerTrench® MOSFETs

Features

• Q1 0.7 A, 20V. $R_{DS(ON)} = 300 \text{ m}\Omega \ @ \ V_{GS} = 4.5 \text{ V}$ $R_{DS(ON)} = 400 \text{ m}\Omega \ @ \ V_{GS} = 2.5 \text{ V}$

• **Q2** -0.6 A, -20V. $R_{DS(ON)} = 420$ m Ω @ $V_{GS} = -4.5$ V $R_{DS(ON)} = 630$ m Ω @ $V_{GS} = -2.5$ V

- · Low gate charge
- High performance trench technology for extremely low R_{DS(ON)}
- SC70-6 package: small footprint (51% smaller than SSOT-6); low profile (1mm thick)
- Qualified to AEC Q101
- · RoHS Compliant


General Description

The N & P-Channel MOSFETs are produced using ON Semiconductor's advanced PowerTrench process that has been especially tailored to minimize on-state resistance and yet maintain superior switching performance.


These devices have been designed to offer exceptional power dissipation in a very small footprint for applications where the bigger more expensive TSSOP-8 and SSOP-6 packages are impractical.

Applications

- DC/DC converter
- · Load switch
- · LCD display inverter



SC70-6



Absolute Maximum Ratings T_A=25°C unless otherwise noted

Symbol	Parameter		Q1	Q2	Units
V _{DSS}	Drain-Source Voltage		20	-20	V
V _{GSS}	Gate-Source Voltage		±12	±12	V
I _D	Drain Current - Continuous	(Note 1)	0.7	-0.6	А
	- Pulsed		2.1	-2	
P _D	Power Dissipation for Single Operation (Note 1)		0	W	
T _J , T _{STG}	Operating and Storage Junction Temperati	–55 to	°C		

Thermal Characteristics

$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	(Note 1)	415	°C/W
-----------------	---	----------	-----	------

Package Marking and Ordering Information

Device Marking	Device	Reel Size	Tape width	Quantity
.32	FDG6332C-F085	7"	8mm	3000 units

Symbol	Parameter Test Conditions			M	lin	Тур	Max	Units
Off Char	acteristics							
BV _{DSS}	Drain-Source Breakdown Volta	ge	$V_{GS} = 0 \text{ V}, \qquad I_D = 250 \mu\text{A} $ $V_{GS} = 0 \text{ V}, \qquad I_D = -250 \mu\text{A} $ Q		20 20			V
<u>ΔBVpss</u> ΔT _J	Breakdown Voltage Temperatur Coefficient	re	$I_D = 250 \mu A, Ref. to 25^{\circ}C$ Q $I_D = -250 \mu A, Ref. to 25^{\circ}C$ Q			14 –14		mV/°C
I _{DSS}	Zero Gate Voltage Drain Currer	nt	$egin{array}{c cccc} V_{DS} = & 16 \ V, & V_{GS} = 0 \ V \\ V_{DS} = & -16 \ V, & V_{GS} = 0 \ V \\ \end{array}$				1 -1	μΑ
I _{GSSF} /I _{GSSR}	Gate-Body Leakage, Forward		$V_{GS} = \pm 12 \text{ V}, V_{DS} = 0 \text{ V}$				±100	nA
I _{GSSF} /I _{GSSR}	Gate-Body Leakage, Reverse		$V_{GS} = \pm 12V$, $V_{DS} = 0 V$				±100	nA
On Char	acteristics (Note 2)							
V _{GS(th)}	Gate Threshold Voltage	Q1	$V_{DS} = V_{GS}, I_D = 250 \mu A$	0).6	1.1	1.5	V
		Q2	$V_{DS} = V_{GS}, I_{D} = -250 \mu A$	-(0.6	-1.2	-1.5	
$\Delta V_{GS(th)}$	Gate Threshold Voltage	Q1	I _D = 250 μA,Ref. To 25°C			-2.8		mV/°C
ΔT _J	Temperature Coefficient	Q2	$I_D = -250 \mu\text{A,Ref. to } 25^{\circ}\text{C}$			3	000	_
$R_{DS(on)}$	Static Drain–Source	Q1	$V_{GS} = 4.5 \text{ V}, I_{D} = 0.7 \text{ A}$ $V_{GS} = 2.5 \text{ V}, I_{D} = 0.6 \text{ A}$			180	300 400	mΩ
	On–Resistance		$V_{GS} = 2.5 \text{ V}, I_D = 0.7 \text{ A}, T_J = 125^{\circ}$	С		293 247	442	
		Q2	$V_{GS} = -4.5 \text{ V}, I_D = -0.6 \text{ A}$	_		300	420	
		QZ	$V_{GS} = -2.5 \text{ V}, I_D = -0.5 \text{ A}$			470	630	
			$V_{GS}=-4.5 \text{ V}, I_D=-0.6 \text{ A}, T_J=125^\circ$	C C		400	700	
g _{FS}	Forward Transconductance	Q1	$V_{DS} = 5 \text{ V}$ $I_{D} = 0.7 \text{ A}$			2.8		S
913		Q2	$V_{DS} = -5 \text{ V}$ $I_{D} = -0.6 \text{A}$			1.8		
1	On–State Drain Current		$V_{GS} = 4.5 \text{ V}, V_{DS} = 5 \text{ V}$		1	1.0		Α
I _{D(on)}	On-State Diam Current	Q1						^
		Q2	$V_{GS} = -4.5 \text{ V}, \ V_{DS} = -5 \text{ V}$	-	-2			
Dynamic	: Characteristics							
C _{iss}	Input Capacitance	Q1	V_{DS} =10 V, V $_{GS}$ = 0 V, f=1.0MHz			113		pF
		Q2	V_{DS} =-10 V, V $_{GS}$ = 0 V, f=1.0MH	z		114		
Coss	Output Capacitance	Q1	V _{DS} =10 V, V _{GS} = 0 V, f=1.0MHz			34		pF
- 000		Q2	V _{DS} =-10 V, V _{GS} = 0 V, f=1.0MH	z		24		'
C _{rss}	Reverse Transfer Capacitance	Q1	V_{DS} =10 V, V $_{GS}$ = 0 V, f=1.0MHz			16		pF
Orss	Neverse Transfer Capacitance	Q2	V_{DS} =-10 V, V $_{GS}$ = 0 V, f=1.0MH			9		PΓ
.		Q2	VDS=-10 V, V GS= 0 V, I=1.0WIT			9		
Switchin	g Characteristics (Note 2)		1			1	1	Т
$t_{d(on)}$	Turn-On Delay Time	Q1	For Q1 :			5	10	ns
		Q2	$V_{DS} = 10 \text{ V}, I_{D} = 1 \text{ A}$			5.5	11	
t _r	Turn-On Rise Time	Q1	V_{GS} = 4.5 V, R_{GEN} = 6 Ω			7	15	ns
		Q2	For Q2 :			14	25	
$t_{d(off)}$	Turn-Off Delay Time	Q1	$V_{DS} = -10 \text{ V}, I_{D} = -1 \text{ A}$			9	18	ns
		Q2	V_{GS} = -4.5 V, R_{GEN} = 6 Ω			6	12	
t _f	Turn-Off Fall Time	Q1				1.5	3	ns
		Q2				1.7	3.4	
Q_g	Total Gate Charge	Q1	For Q1 :			1.1	1.5	nC
		Q2	$V_{DS} = 10 \text{ V}, I_{D} = 0.7 \text{ A}$			1.4	2	
Q _{qs} G	Gate-Source Charge	Q1	V_{GS} = 4.5 V, R_{GEN} = 6 Ω			0.24		nC
		Q2	For Q2 :			0.3		
Q _{gd}	Gate-Drain Charge	Q1	$V_{DS} = -10 \text{ V}, I_{D} = -0.6 \text{ A}$ $V_{GS} = -4.5 \text{ V}, R_{GEN} = 6 \Omega$			0.3		nC
J.	I	Q2	VGS4.0 V, INGEN = 0.22			0.4		1

Electri	cai Characteristics		$T_A = 25^{\circ}C$ unless otherwise noted					
Symbol	Parameter		Test Condition	Min	Тур	Max	Units	
Drain-S	ource Diode Characteris	tics a	nd Maximum Rating	gs				
Is Maximum Continuous Drain–Sour			Diode Forward Current	Q1			0.25	Α
							-0.25	
V _{SD}	Drain-Source Diode Forward	Q1	$V_{GS} = 0 \text{ V}, I_{S} = 0.25 \text{ A}$	(Note 2)		0.74	1.2	V
	Voltage	Q2	$V_{GS} = 0 \text{ V}, I_{S} = -0.25 \text{ A}$	(Note 2)		-0.77	-1.2	

2. Pulse Test: Pulse Width < 300μ s, Duty Cycle < 2.0%

^{1.} R_{BJA} is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. $R_{\theta,JC}$ is guaranteed by design while $R_{\theta,JA}$ is determined by the user's board design. $R_{\theta,JA} = 415^{\circ}\text{C/W}$ when mounted on a minimum pad of FR-4 PCB in a still air environment.

Typical Characteristics: N-Channel




Figure 1. On-Region Characteristics.




Figure 3. On-Resistance Variation with Temperature.




Figure 5. Transfer Characteristics.




Figure 2. On-Resistance Variation with Drain Current and Gate Voltage.




Figure 4. On-Resistance Variation with Gate-to-Source Voltage.




Figure 6. Body Diode Forward Voltage Variation with Source Current and Temperature.

Typical Characteristics: N-Channel




Figure 7. Gate Charge Characteristics.




Figure 9. Maximum Safe Operating Area.




Figure 8. Capacitance Characteristics.




Figure 10. Single Pulse Maximum Power Dissipation.

Typical Characteristics: P-Channel




Figure 11. On-Region Characteristics.




Figure 13. On-Resistance Variation with Temperature.




Figure 15. Transfer Characteristics.




Figure 12. On-Resistance Variation with Drain Current and Gate Voltage.




Figure 14. On-Resistance Variation with Gate-to-Source Voltage.





Figure 16. Body Diode Forward Voltage Variation with Source Current and Temperature.

Typical Characteristics: P-Channel






Figure 17. Gate Charge Characteristics.






Figure 18. Capacitance Characteristics.




Figure 19. Maximum Safe Operating Area.

Figure 20. Single Pulse Maximum Power Dissipation.




Figure 21. Transient Thermal Response Curve.

Thermal characterization performed using the conditions described in Note 1. Transient thermal response will change depending on the circuit board design.

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hol

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Phone: 421 33 790 2910

Japan Customer Focus Center
Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative