

Features

- · High Power Gain
- · Low Noise Figure
- High Cut-off Frequency
- · RF Wideband Amplifiers and Oscillators.
- Halogen Free Available Upon Request By Adding Suffix "-HF"
- · Moisture Sensitivity Level 1
- · Epoxy Meets UL 94 V-0 Flammability Rating
- Lead Free Finish/RoHS Compliant ("P" Suffix Designates RoHS Compliant. See Ordering Information)

Maximum Ratings @ 25°C Unless Otherwise Specified

- Operating Junction Temperature Range: -55°C to +150°C
- Storage Temperature Range: -55°C to +150°C
- Thermal Resistance: 833°C/W Junction to Ambient


Parameter	Symbol	Rating	Unit
Collector-Base Voltage	V _{CBO}	20	V
Collector-Emitter Voltage	V _{CEO}	12	V
Emitter-Base Voltage	V _{EBO}	3	V
Collector Current	I _C	100	mA
Power Dissipation	P _D	150	mW

Internal Structure




Marking: R25

NPN RF Transistor



DIMENSIONS					
DIM	INC	HES	MM		NOTE
DIIVI	MIN	MAX	MIN	MAX	NOTE
Α	0.110	0.120	2.80	3.04	
В	0.083	0.104	2.10	2.64	
С	0.047	0.055	1.20	1.40	
D	0.034	0.041	0.85	1.05	
E	0.067	0.083	1.70	2.10	
F	0.018	0.024	0.45	0.60	
G	0.0004	0.006	0.01	0.15	
Н	0.035	0.043	0.90	1.10	
J	0.003	0.007	0.08	0.18	
K	0.014	0.020	0.35	0.51	
L	0.007	0.020	0.20	0.50	

Suggested Solder Pad Layout






Electrical Characteristics @ T_A =25°C Unless Otherwise Specified


Parameter	Symbol	Min	Тур	Max	Units	Conditions
Collector-Base Cutoff Current	I _{CBO}			1	μA	V_{CB} =20V, I_E =0
Emitter-Base Cutoff Current	I _{EBO}			1	μA	$V_{EB}=3V$, $I_{C}=0$
DC Current Gain*	h _{FE}	130		300		V _{CE} =10V, I _C =20mA
Transition Frequency	f _T		7		GHz	V _{CE} =10V, I _C =20mA
Power Gain	Gp		12.5		dB	V _{CE} =10V, I _C =20mA, f=1GHz
Noise Figure	N _F		1.1	2.0	dB	V _{CE} =10V, I _C =10mA, f=1GHz


^{*}Pulse Width ≤ 380µs, Duty Cycle≤2.0%




Curve Characteristics











Ordering Information

Device	Packing
Part Number-TP	Tape&Reel: 3Kpcs/Reel

Note: Adding "-HF" Suffix for Halogen Free, eg. Part Number-TP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp**. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp**, and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.