


HSF

NOTES:

Current Rating: 1.0A AC/DC
 Contact Resistance: 20milliohm Max
 Insulation Resistance: 100Megohm Min
 Withstand Voltage: 250V AC/minute
 Operation Temperature: -25°C to +105°C

Housing Material: PA9T+30%GF(UL94V-0)
 Contact Material: Brass
 Contact plating: Sn over Ni
 02-06Pin without slot "A"

RECOMMENDED PCB LAYOUT TOLERANCE IS ±0.05




Ordering Information

WF1001A-WZ XX E R1

No. of Pins: 2P~20P
 Insulator Color: E= Beige
 Packing: R=Tape & Reel

Ordering Information & Dimension:

Part No.	Dimension		
	A	B	C
WF1001A-WZ02ER1	1.00	4.30	2.60
WF1001A-WZ03ER1	2.00	5.30	3.60
WF1001A-WZ04ER1	3.00	6.30	4.60
WF1001A-WZ05ER1	4.00	7.30	5.60
WF1001A-WZ06ER1	5.00	8.30	6.60
WF1001A-WZ07ER1	6.00	9.30	7.60
WF1001A-WZ08ER1	7.00	10.30	8.60
WF1001A-WZ09ER1	8.00	11.30	9.60
WF1001A-WZ10ER1	9.00	12.30	10.60
WF1001A-WZ11ER1	10.00	13.30	11.60
WF1001A-WZ12ER1	11.00	14.30	12.60
WF1001A-WZ13ER1	12.00	15.30	13.60
WF1001A-WZ14ER1	13.00	16.30	14.60
WF1001A-WZ15ER1	14.00	17.30	15.60
WF1001A-WZ16ER1	15.00	18.30	16.60
WF1001A-WZ17ER1	16.00	19.30	17.60
WF1001A-WZ18ER1	17.00	20.30	18.60
WF1001A-WZ19ER1	18.00	21.30	19.60
WF1001A-WZ20ER1	19.00	22.30	20.60

				OPERATION	DRAW	DATE	SCALE	1:1	PART NO.	 Http: www.wcon-china.com WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon-china.com	WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: wconks@wcon-china.com	
				X.X	±0.40	KH	2013.12.23	UNIT	mm			TITLE:
				X.XX	±0.25	CHECK	DATE	SIZE	A4			J SH 1.0mm Wafer 90度SMT
A0	2013.12.23	NEW	-	X.XXX	±0.15	APPROVE	DATE	SHEET	1/1			Customer NO.
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	Angle	± 3°			PROJ.				
				DIM	TOL							