



P. C. B Layout

一. 电气性能:

- 1-1. 额定电流: 3A AC DC.
- 1-2. 接触电阻: $\leq 20m\Omega$
- 1-3. 绝缘电阻: $\geq 1000M\Omega$
- 1-4. 耐 压: 550V AC/Minute

二. 物理特性:

- 2-1. 操作温度: $-55^{\circ}C \sim 105^{\circ}C$
- 2-2. 焊接温度: $+260^{\circ}C$, 10s max

三. 材质:

- 3-1. 塑胶: PA6T(Black) UL94V-0
- 3-2. 插针: Brass/Gold plated

| PIN | A | B | C |
|-----|-------|-------|-------|
| 4 | 5.08 | 3.81 | 2.54 |
| 5 | 6.35 | 5.08 | 3.81 |
| 6 | 7.62 | 6.35 | 5.08 |
| 7 | 8.89 | 7.62 | 6.35 |
| 8 | 10.16 | 8.89 | 7.62 |
| 9 | 11.43 | 10.16 | 8.89 |
| 10 | 12.70 | 11.43 | 10.16 |
| 11 | 13.97 | 12.70 | 11.43 |
| 12 | 15.24 | 13.97 | 12.70 |
| 13 | 16.51 | 15.24 | 13.97 |
| 14 | 17.78 | 16.51 | 15.24 |
| 15 | 19.05 | 17.78 | 16.51 |
| 16 | 20.32 | 19.05 | 17.78 |
| 17 | 21.59 | 20.32 | 19.05 |
| 18 | 22.86 | 21.59 | 20.32 |
| 19 | 24.13 | 22.86 | 21.59 |
| 20 | 25.40 | 24.13 | 22.86 |
| 21 | 26.67 | 25.40 | 24.13 |
| 22 | 27.94 | 26.67 | 25.40 |
| 23 | 29.21 | 27.94 | 26.67 |
| 24 | 30.48 | 29.21 | 27.94 |
| 25 | 31.75 | 30.48 | 29.21 |
| 26 | 33.02 | 31.75 | 30.48 |
| 27 | 34.29 | 33.02 | 31.75 |
| 28 | 35.56 | 34.29 | 33.02 |
| 29 | 36.83 | 35.56 | 34.29 |
| 30 | 38.10 | 36.83 | 35.56 |
| 31 | 39.37 | 38.10 | 36.83 |
| 32 | 40.64 | 39.37 | 38.10 |
| 33 | 41.91 | 40.64 | 39.37 |
| 34 | 43.18 | 41.91 | 40.64 |
| 35 | 44.45 | 43.18 | 41.91 |
| 36 | 45.72 | 44.45 | 43.18 |
| 37 | 46.99 | 45.72 | 44.45 |
| 38 | 48.26 | 46.99 | 45.72 |
| 39 | 49.53 | 48.26 | 46.99 |
| 40 | 50.80 | 49.53 | 48.26 |
| 41 | 52.07 | 50.80 | 49.53 |
| 42 | 53.34 | 52.07 | 50.80 |
| 43 | 54.61 | 53.34 | 52.07 |
| 44 | 55.88 | 54.61 | 53.34 |
| 45 | 57.15 | 55.88 | 54.61 |
| 46 | 58.42 | 57.15 | 55.88 |
| 47 | 59.69 | 58.42 | 57.15 |
| 48 | 60.96 | 59.69 | 58.42 |
| 49 | 62.23 | 60.96 | 59.69 |
| 50 | 63.50 | 62.23 | 60.96 |

深圳市威电康精密科技有限公司

图名: PZ1.27-LT-2xNAT-2.0MM
图号: XXXXXXXXXXXXXXXXXXXX

未标注公差

| | | | |
|-----|-------|------|-----|
| XX. | ±0.40 | XX.° | ±2° |
| X. | ±0.30 | .XX° | ±1° |
| .X | ±0.20 | | |
| .XX | ±0.15 | | |

绘制: 韩金锋 单位: MM
签发: 比例: 1:1
审核: 视图: