




P.C.B Layout TOP view



Rating:0.5A 30V DC  
 Contact Resistance:100 mΩ Max.  
 Operating temperature:-20℃~70℃  
 Operating force:3-20N  
 Operating Life:5,000cycles

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.																																																																																																		
	A		NEW																																																																																																					
<table border="1"> <tr> <td>② Terminal</td> <td>—</td> <td>5</td> <td>Phosphor bronze</td> <td>Au Plating</td> <td></td> <td></td> </tr> <tr> <td>① Housing</td> <td>—</td> <td>1</td> <td>Nylon</td> <td>Black</td> <td></td> <td></td> </tr> <tr> <td>ITEM</td> <td>PART NAME</td> <td>TER.NO.</td> <td>QTY.</td> <td>MATERIAL</td> <td>FINISHING</td> <td>REMARK</td> </tr> <tr> <td colspan="2">APPROVALS</td> <td colspan="2">DATE</td> <td colspan="3"></td> </tr> <tr> <td colspan="2">DRAWN</td> <td colspan="2">J.X.Zhang</td> <td colspan="3">2018/3/14</td> </tr> <tr> <td colspan="7">                 TITLE: PHONE JACKES                  PART NO. PJ-327B                  ELECTRONICS CO.,LTD                  HONGKONG ELECTRONICS CO.,LTD             </td> </tr> <tr> <td colspan="2">CHECKED</td> <td colspan="2"></td> <td colspan="3"></td> </tr> <tr> <td colspan="2">APPROVALS</td> <td colspan="2"></td> <td colspan="3"></td> </tr> <tr> <td colspan="2">TOLERANCES ARE</td> <td>30~81L ±0.30</td> <td>ANGLE</td> <td colspan="3"></td> </tr> <tr> <td colspan="2"></td> <td>10~30 ±0.20</td> <td>UNIT: mm</td> <td colspan="3"></td> </tr> <tr> <td colspan="2"></td> <td>5~10 ±0.15</td> <td>SCALE: 1:1</td> <td colspan="3"></td> </tr> <tr> <td colspan="2"></td> <td>~ 5 ±0.10</td> <td>DRAWING NO.</td> <td colspan="3"></td> </tr> <tr> <td colspan="2"></td> <td></td> <td>PROJ-4</td> <td colspan="3"></td> </tr> <tr> <td colspan="2"></td> <td></td> <td>SHEET 1 OF 1</td> <td colspan="3"></td> </tr> </table>							② Terminal	—	5	Phosphor bronze	Au Plating			① Housing	—	1	Nylon	Black			ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK	APPROVALS		DATE					DRAWN		J.X.Zhang		2018/3/14			TITLE: PHONE JACKES PART NO. PJ-327B ELECTRONICS CO.,LTD HONGKONG ELECTRONICS CO.,LTD							CHECKED							APPROVALS							TOLERANCES ARE		30~81L ±0.30	ANGLE						10~30 ±0.20	UNIT: mm						5~10 ±0.15	SCALE: 1:1						~ 5 ±0.10	DRAWING NO.							PROJ-4							SHEET 1 OF 1			
② Terminal	—	5	Phosphor bronze	Au Plating																																																																																																				
① Housing	—	1	Nylon	Black																																																																																																				
ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK																																																																																																		
APPROVALS		DATE																																																																																																						
DRAWN		J.X.Zhang		2018/3/14																																																																																																				
TITLE: PHONE JACKES PART NO. PJ-327B ELECTRONICS CO.,LTD HONGKONG ELECTRONICS CO.,LTD																																																																																																								
CHECKED																																																																																																								
APPROVALS																																																																																																								
TOLERANCES ARE		30~81L ±0.30	ANGLE																																																																																																					
		10~30 ±0.20	UNIT: mm																																																																																																					
		5~10 ±0.15	SCALE: 1:1																																																																																																					
		~ 5 ±0.10	DRAWING NO.																																																																																																					
			PROJ-4																																																																																																					
			SHEET 1 OF 1																																																																																																					