SMD Power Inductor

TMPC0518HP-R68MG-D

	ECN HISTORY LIST							
REV	DATE	DESCRIPTION	APPROVED	CHECKED	DRAWN			
1.0	19/10/31	新發行	羅宜春	梁周虎	許靜			
備			I					
) 注								
/								

SMD Power Inductor


1. Features

- 1. Carbonyl Powder.
- 2. Compact design.
- 3. High current , low DCR , high efficiency.
- 4. Very low acoustic noise and very low leakage flux noise.
- 5. High reliability.
- 6. 100% Lead(Pb)-Free and RoHS compliant.
- 7. Operating temperature -40~+125°C (Including self temperature rise)

2. Applications

Note PC power system , incl. IMVP-6 DC/DC converter .

3. Dimensions



Series	A(mm)	B(mm)	C(mm)	D(mm)	E(mm)
TMPC0518HP	5.7±0.3	5.2±0.2	1.6±0.2	1.1±0.3	2.5±0.3

4. Part Numbering

TMPC	<mark>0518</mark>	HP	-	R68	MG -	D
А	В	С		D	E	F
A: Series						
B: Dimen	sion		BxC			
C: Type			H:Ca	arbonyl Po	wder,P:PAI	D broaden.
D: Inducta	ance		R68:	=0.68uH		

E: Inductance Tolerance F: Code M=±20%

Marking: Black.R68 and 1944(19 YY, 44 WW,follow production date).

5. Specification

Part Number	Inductance	I rms(A)	I sat(A)	DCR(mΩ)	DCR(mΩ)
	L0 (uH)±20%	Typ	Typ	Typ.@25℃	Max.@25℃
TMPC0518HP-R68MG-D	0.68	9.0	13.0	12.4	14.3

Note:

1. Test frequency : Ls : 100KHz /1.0V.

2. All test data referenced to $25^\circ\!\mathrm{C}$ ambient.

3. Testing Instrument(or equ) : L: HP4284A, CH11025, CH3302, CH1320, CH1320S LCR METER / Rdc: CH16502, Agilent 33420A MICRO OHMMETER.

4. Heat Rated Current (Irms) will cause the coil temperature rise approximately $\ {\rm \Delta T}$ of 40 $^\circ\!{\rm C}$


5. Saturation Current (Isat) will cause L0 to drop approximately 30%.

6. The part temperature (ambient + temp rise) should not exceed 125 °C under worst case operating conditions. Circuit design, component, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.

7. Special inquiries besides the above common used types can be met on your requirement.

Halogen-free RoHS


Recommend PC Board Pattern



L(mm)	G(mm)	H(mm)				
6.2	2.2	2.8				
Note: 1. The above PCB layout reference only.						

2. Recommend solder paste thickness at 0.12mm and above.

6.Material List



NO	Items	Materials
1	Core	Carbonyl Powder.
2	Wire	Polyester Wire or equivalent.
3	Clip	100% Pb free solder(Ni+SnPlating)
4	paint	Epoxy resin
5	Ink	Halogen-free ketone

7. Reliability and Test Condition

Item	Performance	Test Condition
Operating temperature	-40~+125°C (Including self - temperature rise)	
Storage temperature	110~+40℃,50~60%RH (Product with taping) 240~+125℃ (on board)	
Electrical Performance Te	st	
Inductance	Refer to standard electrical characteristics list.	HP4284A,CH11025,CH3302,CH1320,CH1320S LCR Meter.
DCR		CH16502, Agilent33420A Micro-Ohm Meter.
Saturation Current (Isat)	Approximately △L30%.	Saturation DC Current (Isat) will cause L0 to drop △L(%)
Heat Rated Current (Irms)	Approximately △T40°C	Heat Rated Current (Irms) will cause the coil temperature rise
Reliability Test		
Life Test		Preconditioning: Run through IR reflow for 2 times.(IPC/JEDEC J-STD-020DClassification Reflow Profiles) Temperature: 125±2°C (Inductor) Applied current: rated current Duration: 1000±12hrs Measured at room temperature after placing for 24±2 hrs
Load Humidity		Preconditioning: Run through IR reflow for 2 times.(IPC/JEDEC J-STD-020DClassification Reflow Profiles Humidity: $85\pm2\%$ R.H, Temperature: $85\%\pm2\%$ Duration: 1000hrs Min. with 100% rated current Measured at room temperature after placing for 24±2 hrs
Moisture Resistance	Appearance: No damage. Inductance: within±10% of initial value Q: Shall not exceed the specification value. RDC: within ±15% of initial value and shall not exceed the specification value	Preconditioning: Run through IR reflow for 2 times.(IPC/JEDEC J-STD-020DClassification Reflow Profiles 1. Baked at50°C for 25hrs, measured at room temperature after placing for 4 hrs. 2. Raise temperature to $65\pm2°C$ 90-100%RH in 2.5hrs, and keep 3 hours, cool down to $25°C$ in 2.5hrs. 3. Raise temperature to $65\pm2°C$ 90-100%RH in 2.5hrs, and keep 3 hours, cool down to $25°C$ in 2.5hrs, keep at $25°C$ for 2 hrs then keep at -10°C for 3 hrs 4. Keep at $25°C$ 80-100%RH for 15min and vibrate at the frequency of 10 to 55 Hz to 10 Hz, measure at room temperature after placing for 1~2 hrs.
Thermal shock		Preconditioning: Run through IR reflow for 2 times.(IPC/JEDEC J-STD-020DClassification Reflow Profiles Condition for 1 cycle Step1: $-40\pm2^{\circ}$ C 30 ± 5 min Step2: $25\pm2^{\circ}$ C \leq 0.5min Step3: $125\pm2^{\circ}$ C 30 ± 5 min Number of cycles: 500 Measured at room temperature after placing for 24±2 hrs
Vibration		Preconditioning: Run through IR reflow for 2 times. (IPC/JEDECJ-STD-020DClassification Reflow Profiles) Oscillation Frequency: 10Hz~2KHz~10Hz for 20 minutes Equipment. Vibration checker Total Amplitude: 10g Testing Time : 12 hours(20 minutes, 12 cycles each of 3 orientations).

TAI-TECH

Item	Performance	Test Condition			
Bending	Appearance ∶ No damage. Imoedance : within±15% of initial value	Shall be mounted on a FR4 substrate of the following dimensions: >=0805 inch(2012mm):40x100x1.2mm <0805 inch(2012mm):40x100x0.8mm Bending depth: >=0805 inch(2012mm):1.2mm <0805 inch(2012mm):0.8mm duration of 10 sec.			
Shock	Inductance:within±10% of initial value Q:Shall not exceed the specification value. RDC:within ±15% of initial value and shall not	Peak Normal duration (D) (g's) Wave form Velocity change (Vi)ft/sec			
	exceed the specification value	SMD 50 11 Half-sine 11.3 Lead 50 11 Half-sine 11.3			
Solder ability	More than 95% of the terminal electrode should be covered with solder。	Preheat: 150°C,608ec Solder: Sn96.5% Ag3% Cu0.5% Temperature: 245±5°C ° Flux for lead free: Rosin. 9.5% ° Dip time: 4±1sec ° Depth: completely cover the termination			
Resistance to Soldering Heat		Depth: completely cover the termination Temperature(°C) Time(s) Temperature ramp/immersion and emersion rate Number of heat cycles 260 ±5 10 ±1 25mm/s ±6 mm/s 1			
	Appearance : No damage. Impedance : within±15% of initial value Inductance : within±10% of initial value Q : Shall not exceed the specification value. RDC : within ±15% of initial value and shall not exceed the specification value e	Preconditioning: Run through IR reflow for 2 times.(IPC/JEDE J-STD-020DClassification Reflow Profiles With the component mounted on a PCB with the device to b tested, apply a force(>0805:1Kg, <=0805:0.5kg)to the side of device being tested. This force shall be applied for 60 + seconds. Also the force shall be applied gradually as not apply a shock to the component being tested.			
Terminal Strength		DUT substrate press tool			

Note : When there are questions concerning measurement result : measurement shall be made after 48 \pm 2 hours of recovery under the standard condition

8. Soldering and Mounting

(1) Soldering

Mildly activated rosin fluxes are preferred. The minimum amount of solder can lead to damage from the stresses caused by the difference in coefficients of expansion between solder, chip and substrate. TAI-TECH terminations are suitable for re-flow soldering systems. If hand soldering cannot be avoided, the preferred technique is the utilization of hot air soldering tools.

(2) Solder re-flow:

Recommended temperature profiles for re-flow soldering in Figure 1.

(3) Soldering Iron:

Reflow Soldering

tp(245¢& / 20~40s.)

60~180s

480s max

TEMPERATURE(¢⊠)

2

217

200 150 PRE-HEATING

Products attachment with a soldering iron is discouraged due to the inherent process control limitations. In the event that a soldering iron must be employed the following precautions are recommended.

 \cdot Preheat circuit and products to 150 $^\circ\!\!\mathbb{C}$ $}$ \cdot Never contact the ceramic with the iron tip

• 355°C tip temperature (max) • 1.0mm tip diameter (max)

SOLDERING

TP(260°C / 10s max.)

60~150s

TIME(sec.)

Reflow times: 3 times max.

Fig.1

NATURAL

ax)

TEMPERATURE(¢&)

150

Over 60s



TIME(sec.)

Iron Soldering times: 1 times max.

Fig.2


Gradual cooling

· Limit soldering time to 4~5sec.

Use a 20 watt soldering iron with tip diameter of 1.0mm


9. Packaging Information

(1) Reel Dimension



Туре	A(mm)	B(mm)	C(mm)	D(mm)
13"x12mm	12.4+2/-0	100±2	13+0.5/-0.2	330

(2) Tape Dimension



Series	Size	Bo(mm)	Ao(mm)	Ko(mm)	P(mm)	W(mm)	F(mm)	t(mm)	D(mm)
тмрс	0518	6.2±0.1	5.5±0.1	2.1±0.1	8.0±0.1	12.0±0.3	5.5±0.1	0.35±0.05	1.5±0.1

(3) Packaging Quantity

ТМРС	0518	
Chip / Reel	3000	
Inner box	6000	
Carton	24000	

(4) Tearing Off Force

165¢%/0180¢X Top cover tape Base tape

The force for tearing off cover tape is 10 to 130 grams in the arrow direction under the following conditions(referenced ANSI/EIA-481-D-2008 of 4.11 stadnard).

Room Temp.	Room Humidity	Room atm	Tearing Speed
(°C)	(%)	(hPa)	mm/min
5~35	45~85	860~1060	300

Application Notice

- · Storage Conditions
- To maintain the solderability of terminal electrodes:
- 1. TAI-TECH products meet IPC/JEDEC J-STD-020D standard-MSL, level 1.
- 2. Temperature and humidity conditions: Less than 40 $^\circ \! \mathbb{C}\,$ and 60% RH.
- Recommended products should be used within 12 months form the time of delivery.
 The packaging material should be kept where no chlorine or sulfur exists in the air.
- Transportation
- 1. Products should be handled with care to avoid damage or contamination from perspiration and skin oils.
- 2. The use of tweezers or vacuum pick up is strongly recommended for individual components.
- 3. Bulk handling should ensure that abrasion and mechanical shock are minimized.

10. Typical Performance Curves

