



Circuit Diagram

PART NO	H	Q	H
A	4.3	R	12.5
B	4.5	S	13
C	5	T	13.5
D	5.5	U	14
E	6	V	15
F	6.5	W	16
G	7	X	17
H	7.5	Y	18
I	8	Z	19
J	8.5		15.5
K	9		16.5
L	9.5		17.5
M	10		22
N	10.5		23
O	11		20
P	11.5		

PART NO	vigor
1	90±30
2	130±30
3	180±30
4	250±30
5	350±50

PART NO	MATERIAL/QTY
S	SUS/1PC
C	C5210/1PC
D	SUS/2PCS
F	C5210/2PCS

PART NO	L	L1
A	8	10
B	8.5	11
C	9	11
D	9.5	12
E	10	12

PART NO	NOTE
NO.5-NO.6	
01~99	SERIAL NUMBER

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	4	Brass(0.30t)	Plating silver	—
④	Contact	—	1	F.Ag/SUS	Black	—
③	Base	—	1	Nylon	Plating Nickel	—
②	Cover	—	1	SPCC	Black	—
①	Keystroke	—	1	Nylon	—	—

APPROVALS	DATE	TITLE:
DRAWN SUNNY	2020.7.7	TACT SWITCHS

APPROVALS	DATE	TITLE:
CHECKED		TACT SWITCHS
APPROVALS		TACT SWITCHS

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			



ELECTRONICS CO.,LTD

PART NO.	SCALE:	PROJ.	SHEET
K2-1102SP-0000-00	1:1		1 OF 1