

June 2015

Multilayer Low Pass Filter

For 470-787MHz

DEA160787LT-5032A1

1.6x0.8mm [EIA 0603]*

* Dimensions Code JIS[EIA]

Multilayer Low Pass Filter


公TDK


For 470-787MHz

DEA160787LT-5032A1


SHAPES AND DIMENSIONS

[Top view]






[Bottom view]




Terminal functions				
1	IN			
2	GND			
34	OUT			
4	GND			
5	N.C.			
6	GND			

Dimensions in mm

RECOMMENDED LAND PATTERN



EVALUATION BOARD



Line width to be designed to match 50Ω characteristic impedance, depending on PCB material and thickness.

O RoHS Directive Compliant Product: See the following for more details related to RoHS Directive compliant products. http://product.tdk.com/en/environment/rohs/

- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.

DEA160787LT-5032A1

ELECTRICAL CHARACTERISTICS

Item	Frequency Range (MHz)	Min.	Тур.	Max.
Incortion Loop (dP)	470 to 787	—	0.46	0.65
Insertion Loss (dB)	470 to 787	—	—	0.71(-40 to +85°C)
Return Loss (dB)	470 to 787	13.98	23.5	—
	1429 to 1501	26	39.7	_
	1565 to 1570	30	46.5	
Attenuation (dB)	1570 to 1580	35	46.8	
	1580 to 1607	30	46.9	_
	1920 to 1980	20	32.4	—
Power Handling (W)	470 to 787	—	—	3
Characteristic Impedance (Ω)			50 (Nominal)	

• Ta: +25±5°C

TEMPERATURE RANGE


Operating temperature	Storage temperature	
(° C)	(°C)	
-40 to +85	-40 to +85	

```
 All specifications are subject to change without notice. Before using these products, be sure to request the delivery specifications.
```


DEA160787LT-5032A1


FREQUENCY CHARACTERISTICS





RETURN LOSS





• All specifications are subject to change without notice.

• Before using these products, be sure to request the delivery specifications.

RECOMMENDED REFLOW PROFILE



Soldering Preheating Critical zone (T3 to T4) Peak Temp. Time Temp. Time Temp. Time T1 T2 **T**4 t1 ТЗ t2 t3* 150°C 200°C 60 to 120sec 217°C 60 to 120sec 240 to 260°C 30sec max.

*t3 : Time within 5°C of actual peak temperature

The maximum number of reflow is 3.

All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

▲ REMINDERS

The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this catalog.

- (1) Aerospace/Aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/ equipment or providing backup circuits, etc., to ensure higher safety.

• All specifications are subject to change without notice.

[·] Before using these products, be sure to request the delivery specifications.