

KA-4040SES





DESCRIPTIONS

- The Super Bright Orange device is made with AlGaInP (on GaAs substrate) light emitting diode chip
- · Electrostatic discharge and power surge could damage the LEDs
- It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs
- All devices, equipments and machineries must be electrically grounded

FEATURES

- Single color
- Suitable for all SMD assembly and solder process
- · Available on tape and reel
- · Ideal for backlighting
- Package: 500 pcs / reel
- Moisture sensitivity level: 3
- · RoHS compliant

APPLICATIONS


- Backlight
- · Status indicator
- · Home and smart appliances
- · Wearable and portable devices
- · Healthcare applications

ATTENTION

Observe precautions for handling electrostatic discharge sensitive devices




PACKAGE DIMENSIONS



RECOMMENDED SOLDERING PATTERN

(units: mm; tolerance: \pm 0.1)



- All dimensions are in millimeters (inches).
 Tolerance is ±0.25(0.01") unless otherwise noted.
- 3. The specifications, characteristics and technical data described in the datasheet are subject to
- change without prior notice.

 4. The device has a single mounting surface. The device must be mounted according to the specifications.

SELECTION GUIDE

Part Number	Emitting Color	Lens Type	Iv (mcd) @ 20mA [2]		Viewing Angle [1]	
rait Nullibei	(Material)	Lens Type	Min.	Тур.	201/2	
KA-4040SES	Super Bright Orange (AlGaInP)	Water Clear	300	450	- 120°	
			*120	*250	120	

Notes.

1. 61/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.

2. Luminous intensity / luminous flux: +/-15%.

* Luminous intensity value is traceable to CIE127-2007 standards.





ELECTRICAL / OPTICAL CHARACTERISTICS at T_A=25°C

Parameter	Symbol	Emitting Color	Value		Unit
Parameter	Symbol Emitti		Typ.	Max.	
Wavelength at Peak Emission I _F = 20mA	λ_{peak}	Super Bright Orange	610	-	nm
Dominant Wavelength I _F = 20mA	λ _{dom} ^[1]	Super Bright Orange	605	-	nm
Spectral Bandwidth at 50% Φ REL MAX I _F = 20mA	Δλ	Super Bright Orange	29	-	nm
Capacitance	С	Super Bright Orange	30	-	pF
Forward Voltage I _F = 20mA	V _F ^[2]	Super Bright Orange	2	2.5	V
Reverse Current (V _R = 5V)	I _R	Super Bright Orange	-	10	μΑ

ABSOLUTE MAXIMUM RATINGS at T₄=25°C

ABSOLUTE MAXIMUM RATINGS at 1 _A =25 C						
Parameter	Symbol	Value	Unit			
Power Dissipation	P _D	75	mW			
Reverse Voltage	V _R	5	V			
Junction Temperature	T _j	115	°C			
Operating Temperature	T_{op}	-40 to +85	°C			
Storage Temperature	T _{stg}	-40 to +85	°C			
DC Forward Current	I _F	30	mA			
Peak Forward Current	I _{FM} ^[1]	195	mA			
Electrostatic Discharge Threshold (HBM)	-	3000	V			

Notes:
1. 1/10 Duty Cycle, 0.1ms Pulse Width.
2. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.




The dominant wavelength (λd) above is the setup value of the sorting machine. (Tolerance λd:±1nm.)
 Forward voltage: ±0.1V.
 Wavelength value is traceable to CIE127-2007 standards.
 Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.




TECHNICAL DATA


RELATIVE INTENSITY vs. WAVELENGTH





SPATIAL DISTRIBUTION




SUPER BRIGHT ORANGE










REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS




Notes

- 1. Don't cause stress to the LEDs while it is exposed to high temperature.


 2. The maximum number of reflow soldering passes is 2 times.

 3. Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product.

TAPE SPECIFICATIONS (units: mm)




REEL DIMENSION (units: mm)





PACKING & LABEL SPECIFICATIONS



HANDLING PRECAUTIONS

(SP)XXXXXXXXXX

Compare to epoxy encapsulant that is hard and brittle, silicone is softer and flexible. Although its characteristic significantly reduces thermal stress, it is more susceptible to damage by external mechanical force. As a result, special handling precautions need to be observed during assembly using silicone encapsulated LED products. Failure to comply might lead to damage and premature failure of the LED.

1. Handle the component along the side surfaces by using forceps or appropriate tools.



2. Do not directly touch or handle the silicone lens surface. It may damage the internal circuitry.





3. As silicone encapsulation is permeable to gases, some corrosive substances such as H₂S might corrode silver plating of lead frame. Special care should be taken if an LED with silicone encapsulation is to be used near such substances.

PRECAUTIONARY NOTES

- The information included in this document reflects representative usage scenarios and is intended for technical reference only.
- The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to
- the latest datasheet for the updated specifications.

 When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If
- customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.

 The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.
- The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright All design applications should refer to Kingbright application notes available at https://www.Kingbright.com/application no

