High Frequency Chip Inductor (Lead Free)

HCI1005LF-33NJ-MS8

ECN HISTORY LIST								
REV	DATE	DESCRIPTION	APPROVED	CHECKED	DRAWN			
1.0	17/06/27	初版發行	楊祥忠	詹偉特	張嘉玲			
備			,					
註								

High Frequency Chip Inductor (Lead Free)

HCI1005LF-33NJ-MS8

1.Features


- 1. Monolithic inorganic material construction.
- 2. Closed magnetic circuit avoids crosstalk.
- 3. S.M.T. type.
- 4. Suitable for reflow soldering.
- 5. Shapes and dimensions follow E.I.A. spec.
- 6. Available in various sizes.
- 7. Excellent solder ability and heat resistance.
- 8. High SRF up to 6GHz and above.
- 9. 100% Lead(Pb) & Halogen-Free and RoHS compliant.







2. Dimensions



Chip Size					
Α	1.00±0.15				
В	0.50±0.15				
С	0.50±0.15				
D	0.25±0.10				

Units: mm

3. Part Numbering



A: Series


B: Dimension L x W

C: Category Code

D: Material Lead Free Material

E: Inductance 33N=33 nH F: Inductance Tolerance J=±5%


G: marking





4.Specification

Tai-Tech	Inductance	Test Frequency	Q	Rated Current	DCR (Ω)	SRF (MHz)	
Part Number	(nH)	(Hz)	min.	(mA) max	max.	min.	
HCI1005LF-33NJ-MS8	33±5%	100M / 50mV	8	200	0.80	1300	

- Rated current: based on temperature rise test
- In compliance with EIA 595







TAI-TECH TBM01-170800362 P3.

5. Reliability and Test Condition

Item	Performance	Test Condition				
Series No.	HCI					
Operating Temperature	-40~+105°C (Including self-temperature rise)					
Transportation Storage Temperature	-40~+105°C (on board)	For long			ons, please	see the
Inductance (Ls)		Agilent42				
Q Factor	Refer to standard electrical characteristics list					
DC Resistance						
Rated Current		DC Pow Over Ra some ris	ted Curi		ements, the	re will be
Temperature Rise Test	Rated Current < 1A ∆T 20°CMax Rated Current ≧ 1A ∆T 40°CMax	2. Temp			current. by digital s	urface
Life test	Appearance: no damage. Impedance: within±15%of initial value.	times.(II Reflow F Tempera Applied of Duration Measure for 24±2	PC/JED Profiles) ature: 10 current: : 1000± ed at ro hrs.	EC J-STD 05±2°C rated curr 12hrs. om tempe	erature afte	sification
Load Humidity	Preconditioning: Run through IR reflow for 2 times. (IPC/JEDEC J-STD-020D Classification Reflow Profiles) Humidity: 85±2%R.H. Temperature: 85±2°C. Duration: 1000hrs Min. with 100% rated current. Measured at room temperature after placing for 24±2 hrs.					
Thermal shock	Appearance: no damage. Appearance: no damage. Impedance: within±15% of initial value. Inductance: within±10% of initial value. Q : Shall not exceed the specification value. RDC : within ±15% of initial value and shall not exceed the specification value Preconditioning: Run through times. (IPC/JEDEC J-STD-020 Reflow) Condition for 1 cycle Step1: 40±2°C 30±5 min. Step2: 25±2°C ≤0.5min Step3: +105±2°C 30±5 min. Number of cycles: 500 Measured at room temperatur for 24±2 hrs.					sification
Vibration	Appearance: No damage. Impedance: within±15% of initial value Inductance: within±10% of initial value Q: Shall not exceed the specification value RDC: within ±15% of initial value and shall not exceed the specification value RDC: within±15% of initial value and shall not exceed the specification value Preconditioning: Run through IF times.(IPC/JEDEC J-STD-020D Reflow Profiles) Oscillation Frequency: 10 ~ 2K ~ minutes Equipment: Vibration checker Total Amplitude:1.52mm±10% Testing Time: 12 hours(20 minuteach of 3 orientations) ∘				\sim 2K \sim 10H ecker 10%	ssification
Bending	Appearance: No damage. Impedance: within±10% of initial value Inductance: within±10% of initial value Q: Shall not exceed the specification value. RDC: within±15% of initial value and shall not exceed the specification value	Shall be mounted on a FR4 substrate of the following dimensions: >=0805inch(2012mm):40x100x1.2mm <0805inch(2012mm):40x100x0.8mm Bending depth: >=0805inch(2012mm):1.2mm <0805inch(2012mm):0.8mm Duration of 10 sec for a min.				
	Appearance: No damage. Impedance: within±10% of initial value Inductance: within±10% of initial value Q: Shall not exceed the specification value. RDC: within±15% of initial value and shall not exceed the specification value		ndition	1:		
Shock			Peak Value (g's)	Normal duration (D) (ms)	Wave form	Velocity change (Vi)ft/sec
			50 50	11	Half-sine Half-sine	11.3 11.3
Insulation Resistance	IR>1GΩ	Chip Ind	uctor O			1


TAI-TECH TBM01-170800362 P4.

Item	Performance	Test Condition			
Solderability	More than 95% of the terminal electrode should be covered with solder.	Preheat: 150°C,60sec. Solder: Sn96.5%-Ag3%-Cu0.5% Solder temperature: 245±5°C Flux for lead free: Rosin. 9.5% Depth: completely cover the termination. Dip time: 4±1sec.			
		Number of heat cycles: 1			
Resistance to Soldering	Appearance : No damage. Impedance : within±15% of initial value	Temperature (°C) Time (s) Temperature ramp/immersion and emersion rate			
Heat	Inductance: within±10% of initial value Q: Shall not exceed the specification value. RDC: within ±15% of initial value and shall not exceed the specification value	260 ±5 (solder temp) 10 ±1 25mm/s ±6 mm/s			
		Depth: completely cover the termination			
Terminal strength	Appearance: No damage. Impedance: within±15% of initial value Inductance: within±10% of initial value Q: Shall not exceed the specification value. RDC: within ±15% of initial value and shall not exceed the specification value	Preconditioning: Run through IR reflow for 2 times. (IPC/JEDEC J-STD-020D Classification Reflow Profiles) Component mounted on a PCB apply a force >0805inch(2012mm): 1kg <=0805inch(2012mm): 0.5kg to the side of a device being tested. This force shall be applied for 60 +1 seconds. Also the force shall be applied gradually as not to shock the component being tested.			

6. Soldering and Mounting

6-1. Recommended PC Board Pattern

Chip Size							Land Patterns For Reflow Soldering			
Series	Type	A(mm)	B(mm)	C(mm)	D(mm)	E(mm)	F(mm)	G(mm)		
HCI	1005	1.00±0.15	0.50±0.15	0.50±0.15	0.25±0.10	0.50	0.40	0.60		



PC board should be designed so that products can prevent damage from mechanical stress when warping the board.

6-2. Soldering

Mildly activated rosin fluxes are preferred. The terminations are suitable for re-flow soldering systems. If hand soldering cannot be avoided, the preferred technique is the utilization of hot air soldering tools.

If wave soldering is used ,there will be some risk.

Re-flow soldering temperatures below 240 degrees, there will be non-wetting risk

6-2.1 Lead Free Solder re-flow:

Recommended temperature profiles for lead free re-flow soldering in Figure 1. (Refered to J-STD-020C)