


100V N-Channel Split Gate MOSFET

FEATURES

- Super Low Gate Charge
- 100% EAS Guaranteed
- RoHS compliant
- Green Device Available
- Excellent CdV/dt effect decline
- Advanced high cell density Trench technology

APPLICATIONS

- DC/DC Converter
- Ideal for high-frequency switching and synchronous rectification



Device Marking and Package Information

Device	Package	Marking
CSP10N4P2	TO-220	CSP10N4P2

Absolute Maximum Ratings at $T_j = 25^\circ\text{C}$ unless otherwise noted

Parameter	Symbol	Value	Unit
Drain-Source Voltage ($V_{GS} = 0\text{V}$)	V_{DSS}	100	V
Continuous Drain Current $T_C = 25^\circ\text{C}$ (note1)	I_D	180	A
Continuous Drain Current $T_C = 100^\circ\text{C}$ (note1)		110	
Pulsed Drain Current (note2)	I_{DM}	450	A
Gate Source Voltage	V_{GSS}	± 20	V
Single Pulse Avalanche Energy (note3)	E_{AS}	665	mJ
Power Dissipation $T_C = 25^\circ\text{C}$ (note4)	P_D	284	W
Operating Junction and Storage Temperature Range	T_J, T_{stg}	-55~+150	$^\circ\text{C}$







Thermal Characteristics







Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	0.4	$^\circ\text{C/W}$
Thermal Resistance, Junction-to-Ambient (note1)	$R_{\theta JA}$	50	

Electrical Characteristics $T_J = 25^\circ\text{C}$ unless otherwise specified						
Parameter	Symbol	Test Conditions	Value			Unit
			Min.	Typ.	Max.	
Static						
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS} = 0V, I_D = 250\mu A$	100	--	--	V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = 100V, V_{GS} = 0V, T_J = 25^\circ\text{C}$	--	--	1	μA
		$V_{DS} = 100V, V_{GS} = 0V, T_J = 55^\circ\text{C}$	--	--	5	μA
Gate-Source Leakage	I_{GSS}	$V_{GS} = \pm 20V$	--	--	± 100	nA
Gate-Source Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = 250\mu A$	2	--	4	V
Drain-Source On-Resistance (note2)	$R_{DS(on)}$	$V_{GS} = 10V, I_D = 60A$	--	3.5	4.2	m Ω
Dynamic						
Input Capacitance	C_{iss}	$V_{GS} = 0V,$ $V_{DS} = 25V,$ $f = 1.0\text{MHz}$	--	5505	--	pF
Output Capacitance	C_{oss}		--	1656	--	
Reverse Transfer Capacitance	C_{rss}		--	90	--	
Total Gate Charge (10V)	Q_g	$V_{DS} = 80V, I_D = 40A,$ $V_{GS} = 10V$	--	83	--	nC
Gate-Source Charge	Q_{gs}		--	24	--	
Gate-Drain Charge	Q_{gd}		--	19	--	
Turn-on Delay Time	$t_{d(on)}$	$V_{DS} = 50V, I_D = 30A$ $V_{GS} = 10V, R_G = 4.7\Omega$	--	25	--	ns
Turn-on Rise Time	t_r		--	33	--	
Turn-off Delay Time	$t_{d(off)}$		--	45	--	
Turn-off Fall Time	t_f		--	19	--	
Body Diode Characteristics						
Continuous Body Diode Current	I_{SD}		--	--	180	A
Pulsed Diode Forward Current	I_{SDM}		--	--	450	A
Body Diode Voltage	V_{SD}	$T_J = 25^\circ\text{C}, I_{SD} = 60A, V_{GS} = 0V$	--	--	1.2	V
Reverse Recovery Time	t_{rr}	$T_J = 25^\circ\text{C}$ $I_F = 30A$ $di_F/dt = 100A/\mu s$	--	71	--	ns
Reverse Recovery Charge	Q_{rr}		--	144	--	nC

Notes

1. The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.
2. The data tested by pulsed , pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$
3. The EAS data shows Max. rating . The test condition is $V_{DD} = 25V, V_{GS} = 10V, L = 0.5mH$
4. The power dissipation is limited by 150°C junction temperature
5. The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation.

Typical Characteristics $T_j = 25^\circ\text{C}$, unless otherwise noted

Figure 1. On-Region Characteristics

Figure 2. Transfer Characteristics

Figure 3. On-Resistance Variation vs Drain Current

Figure 4. On-Resistance Vs Gate to Source Voltage

Figure 5. Capacitance Characteristics

Figure 6. Gate Charge Characteristics

Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted

Figure 7. Breakdown Voltage Variation vs Temperature

Figure 8. On-Resistance Variation vs Temperature

Figure 9. Power Dissipation

Figure 10. Drain Current Derating

Figure 11. Maximum Safe Operating Area

Figure 12. Body-diode Forward Characteristics





Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted

Figure 13. Transient Thermal Response Curve

Figure A: Gate Charge Test Circuit and Waveform

Figure B: Resistive Switching Test Circuit and Waveform

Figure C: Unclamped Inductive Switching Test Circuit and Waveform


Disclaimer

All product specifications and data are subject to change without notice.

For documents and material available from this datasheet, Suzhou Convert does not warrant or assume any legal liability or responsibility for the accuracy, completeness of any product or technology disclosed hereunder.

No license, express or implied, by estoppels or otherwise, to any intellectual property rights is granted by this document or by any conduct of Suzhou Convert.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless. Customers using or selling Suzhou Convert products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Suzhou Convert for any damages arising or resulting from such use or sale.

Suzhou Convert disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Suzhou Convert's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

Suzhou Convert Semiconductor CO., Ltd. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

In the event that any or all Suzhou Convert products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. Suzhou Convert believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.