


TAI-TECH

Tai-Tech Part Number	Impedance (Ω)	Test Frequency (MHz)	DC Resistance (Ω) max.	Rated Current (mA) max.
FCM1608CF-100T07	10 \pm 25%	100	0.20	700
FCM1608CF-300T06	30 \pm 25%	100	0.25	600
FCM1608CF-600T06	60 \pm 25%	100	0.30	600
FCM1608CF-121T03	120 \pm 25%	100	0.40	300
FCM1608CF-151T03	150 \pm 25%	100	0.40	300
FCM1608CF-221T02	220 \pm 25%	100	0.60	250
FCM1608CF-301T02	300 \pm 25%	100	0.80	200
FCM1608CF-471T02	470 \pm 25%	100	0.85	200
FCM1608CF-601T01	600 \pm 25%	100	1.20	150
FCM1608CF-102T00	1000 \pm 25%	100	1.50	80

- Rated current: based on temperature rise test
- In compliance with EIA 595

Impedance Frequency Characteristics(Typical)



Impedance Frequency Characteristics(Typical)

