
muRata Inductor Data Sheet

# LQW18AN10NG10# "#" indicates a package specification code.

General 125 (Mag) Comax. (Mag) Tight RoHS REACH In Production

< List of part numbers with package codes >

LQW18AN10NG10D , LQW18AN10NG10J , LQW18AN10NG10B



	References
-	11010101000

Packaging code	Specifications	Minimum quantity
D	φ180mm Paper taping	4000
J	φ330mm Paper taping	10000
В	Packing in bulk	500

	Mass (Typ.)	
1 piece		0.003g

## Specifications

Inductance	10nH ±2%
Inductance test frequency	100MHz
Rated current (Itemp) (Based on Temperature rise)	800mA
Max. of DC resistance	0.058Ω
Q (min.)	38
Q test frequency	250MHz
Self resonance frequency (min.)	5000MHz
Operating temperature range (Self-temperature rise is not included)	-55°C to 125°C
Series	LQW18AN_10

### 🔔 Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued


without advance notice. Please check with our sales representatives or product engineers before ordering.


2. This datasheet has only typical specifications because there is no space for detailed specifications


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



## Chart of characteristic data (The charts below may show another part number which shares its characteristics.)







#### 🔔 Attention

 This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.