

March 2018

Thin-Film Directional Coupler

For 2400-2500MHz / 5150-5850MHz

TFSC06054125-2120A1X

0.65x0.5mm [EIA 0202]*


* Dimensions Code JIS[EIA]

Thin-Film Directional Coupler For 2400-2500MHz / 5150-5850MHz


公TDK

TFSC06054125-2120A1X

SHAPES AND DIMENSIONS



RECOMMENDED LAND PATTERN



Dimensions in mm

Line width be designed to match 50Ω characteristic impedance depending on PCB material and thickness.

O RoHS Directive Compliant Product: See the following for more details.https://product.tdk.com/info/en/environment/rohs/index.html

[•] Before using these products, be sure to request the delivery specifications.

TFSC06054125-2120A1X

ELECTRICAL CHARACTERISTICS

Item	Frequency Range (MHz)	Min.	Тур.	Max.
Coupling Fostor (dP)	2400 to 2500	18.6	19.4	20
Coupling Factor (dB)	5150 to 5850	<i></i>	14	
Insertion Loss (dB)	2400 to 2500	—	0.07	0.2
	5150 to 5850	—	0.34	0.5
Return Loss (dB)	2400 to 2500	20.83	35.8	—
Heidin Loss (dB)	5150 to 5850	19.08	23.7	_
Directivity (dP)	2400 to 2500	16	19.9	—
Directivity (dB)	5150 to 5850	20	23.8	_
Power Handling (W)		—	—	3
Characteristic Impedance (Ω)			50 (Nominal)	

• Ta: +25°C±5°C

TEMPERATURE RANGE


Operating temperature	Storage temperature
(° C)	(°C)
-40 to +85	-40 to +85

All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.


TFSC06054125-2120A1X


FREQUENCY CHARACTERISTICS






RETURN LOSS














• All specifications are subject to change without notice.


• Before using these products, be sure to request the delivery specifications.

ATDK

TFSC06054125-2120A1X


PACKAGING STYLE

REEL DIMENSIONS



Dimensions in mm

TAPE DIMENSIONS



Dimensions in							ensions in mm			
А	В	С	D	E	F	G	Н	J	К	Т
0.63±0.03	0.81±0.03	8.0±0.2	3.5±0.05	1.75±0.1	2.0±0.05	2.0±0.05	4.0±0.1	ø1.5+0.1/0	0.34±0.03	0.20±0.05


PACKAGE QUANTITY

Standard package quantity (pieces/reel)
10,000

All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.

TFSC06054125-2120A1X

RECOMMENDED REFLOW PROFILE



Preheating			Soldering Critical zone (T3 to T4) Peak			
Temp.		Time	Temp.	Time	Temp.	Time
T1	T2	t1	Т3	t2	T4	t3*
150°C	200°C	60 to 120sec	217°C	60 to 120sec	240 to 260°C	30sec max.

*t3 : Time within 5°C of actual peak temperature

The maximum number of reflow is 3.

All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

⚠ REMINDERS

The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this catalog.

- (1) Aerospace/Aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/ equipment or providing backup circuits, etc., to ensure higher safety.

· All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.