SMD Power Inductor

TMPC1235HP-Series-D

	ECN HISTORY LIST								
REV	DATE	DESCRIPTION	APPROVED	CHECKED	DRAWN				
1.0	17/05/20	新發行	羅宜春	梁周虎	張光				
備									
注									

SMD Power Inductor


1. Features


- 1. Carbonyl powder inductor.
- 2. Compact design.
- 3. High current , low DCR , high efficiency.
- 4. Very low acoustic noise and very low leakage flux noise.
- 5. High reliability.
- 6. 100% Lead(Pb) & Halogen-Free and RoHS compliant.
- 7. AEC-Q200 Grade 1 qualified ($40^\circ\!\mathrm{C}$ to +125 $^\circ\!\mathrm{C}$ ambient)

2. Applications

Note PC power system , incl. IMVP-6 DC/DC converter .

3. Dimensions





4. Part Numbering



- **B:** Dimension

F: 印 D/C

C: Type D: Inductance

E: Inductance Tolerance


BxC HP:H:Carbonyl Powder,P:PAD broaden. 8R2=8.20uH M=±20%

印字:黑色.8R2 及 D/C 1206 (12 年,06 週期)(依實際生產日期而定)



TMPC1235HP-Series-D

Recommend PC Board Pattern



L(mm)	G(mm)	H(mm)
14.2	8.0	5.0
Note: 1. The	e above PCE	3 layout refe

e only. 2. Recommend solder paste thickness at 0.15mm and above.

5. Specification

Part Number	Inductance L0 (uH)±20% @ 0 A	l rms(A) Typ.	l rms(A) Max	l sat(A) Typ.	l sat(A) Max	DCR (mΩ) Typ. @25℃	DCR (mΩ) Max. @25℃
TMPC1235HP-1R0MG-D	1.00	24	20	40	35	2.7	3.5
TMPC1235HP-1R2MG-D	1.20	21	18	37	34	4.0	5.0
TMPC1235HP-1R5MG-D	1.50	19	17	35	31	4.8	5.5
TMPC1235HP-1R8MG-D	1.80	17	15	30	28	5.2	7.0
TMPC1235HP-2R2MG-D	2.20	16	14	29	26	6.3	8.0
TMPC1235HP-3R3MG-D	3.30	12	10	27	23	11	13.5
TMPC1235HP-4R7MG-D	4.70	10	8	24	19	15.3	18.5
TMPC1235HP-5R6MG-D	5.60	9.5	7.5	19	15	18	22
TMPC1235HP-6R8MG-D	6.80	9	7.0	18	14	20	24
TMPC1235HP-8R2MG-D	8.20	8.5	6.5	16	13	23	28
TMPC1235HP-100MG-D	10.0	7.5	6.0	14	11	29	34
TMPC1235HP-150MG-D	15.0	6.5	5.5	10	8	55	65
TMPC1235HP-220MG-D	22.0	4.5	4.0	7	6	83	99
TMPC1235HP-330MG-D	33.0	3.5	3.0	6.0	5	132	160
TMPC1235HP-470MG-D	47.0	3	2.5	5.5	4.5	181	218

Note:

1. Test frequency : Ls : 100KHz /1.0V.

2. All test data referenced to 25 $^\circ\!\!\mathbb{C}$ ambient.

3. Testing Instrument(or equ) : L: HP4284A, CH11025, CH3302, CH1320, CH1320S LCR METER / Rdc: CH16502, Agilent 33420A MICRO OHMMETER.


4. Heat Rated Current (Irms) will cause the coil temperature rise approximately $\, \Delta T$ of 40 $^\circ \! C$

5. Saturation Current (Isat) will cause L0 to drop approximately 20%.

6. The part temperature (ambient + temp rise) should not exceed 125 °C under worst case operating conditions. Circuit design, component, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.

7. Special inquiries besides the above common used types can be met on your requirement.

6. Material List



NO	Items	Materials
1	Core	Carbonyl Powder.
2	Wire	Polyester Wire or equivalent.
3	Clip	100% Pb free solder(Ni+SnPlating)
4	Ink	Halogen-free ketone
5	paint	Epoxy resin

7. Reliability and Test Condition

Item	Performance	Test Condition
Operating temperature	-40~+125°C (Including self - temperature rise)	
Storage temperature	110~+40℃,50~60%RH (Product without taping) 240~+125℃ (on board)	
Electrical Performance 1	Test	
Inductance	Refer to standard electrical characteristics list.	HP4284A,CH11025,CH3302,CH1320,CH1320S LCR Meter.
DCR		CH16502, Agilent33420A Micro-Ohm Meter.
Saturation Current (Isat)	Approximately	Saturation DC Current (Isat) will cause L0 to drop △L(%)
Heat Rated Current (Irms)	Approximately △T40°C	Heat Rated Current (Irms) will cause the coil temperature rise
Reliability Test		
Life Test		Preconditioning: Run through IR reflow for 2 times.(IPC/JEDEC J-STD-020DClassification Reflow Profiles) Temperature : 125±2°C(Inductor) Applied current : rated current Duration : 1000±12hrs Measured at room temperature after placing for 24±2 hrs
Load Humidity		Preconditioning: Run through IR reflow for 2 times. (IPC/JEDEC J-STD-020DClassification Reflow Profiles Humidity : 85±2% R.H, Temperature : 85℃±2℃ Duration : 1000hrs Min. with 100% rated current Measured at room temperature after placing for 24±2 hrs
Moisture Resistance	Appearance : No damage. Inductance : within±10% of initial value Q : Shall not exceed the specification value. RDC : within ±15% of initial value and shall not exceed the specification value	Preconditioning: Run through IR reflow for 2 times.(IPC/JEDEC J-STD-020DClassification Reflow Profiles 1. Baked at50°C for 25hrs, measured at room temperature after placing for 4 hrs. 2. Raise temperature to $65\pm2°C$ 90-100%RH in 2.5hrs, and keep 3 hours, cool down to $25°C$ in 2.5hrs. 3. Raise temperature to $65\pm2°C$ 90-100%RH in 2.5hrs, and keep 3 hours, cool down to $25°C$ in 2.5hrs, keep at $25°C$ for 2 hrs then keep at $-10°C$ for 3 hrs 4. Keep at $25°C$ 80-100%RH for 15min and vibrate at the frequency of 10 to 55 Hz to 10 Hz, measure at room temperature after placing for 1–2 hrs.
Thermal shock		$eq:preconditioning: Run through IR reflow for 2 times. (IPC/JEDEC J-STD-020DClassification Reflow Profiles Condition for 1 cycle Step1: -40+2°C 30±5min Step2: 25±2°C \leq0.5min Step3: 125±2°C 30±5min Number of cycles: 500 Measured at room temperature after placing for 24±2 hrs$
Vibration		Oscillation Frequency: 10~2K~10Hz for 20 minutes Equipment : Vibration checker Total Amplitude:1.52mm±10% Testing Time : 12 hours(20 minutes, 12 cycles each of 3 orientations) ∘

TAIPAQ

Item	Performance	Test Condition				
Shock	Appearance : No damage. Inductance : within±10% of initial value Q : Shall not exceed the specification value. RDC : within ±15% of initial value and shall not	Type SMI	(g's) 0 50	Normal duration (D) (ms) 11	Half-sine	Velocity change (Vi)ft/sec 11.3
Bending	exceed the specification value	Lead 50 11 Half-sine Shall be mounted on a FR4 substrate of the following dimensions: >=0805:40x100x1.2mm <0805:40x100x0.8mm				
Solderability	More than 95% of the terminal electrode should be covered with solder $^\circ$	Solde Temp Flux Dip t	perature: 245 for lead free: me: 4±1sec	Ag3% Cu0.5% ±5℃。 Rosin. 9.5%。		
Resistance to Soldering Heat		T (° 2	emperature C) 60 ±5(solder emp)	Time(s)	Temperature ramp/immers and emersio 25mm/s ±6 r	sion n rate
Terminal Strength	Appearance : No damage. Inductance : within±10% of initial value Q : Shall not exceed the specification value. RDC : within ±15% of initial value and shall not exceed the specification value		w Profiles the compon- sted, apply a 05:1kg , <=0 d. This force ed for 60 +1 ually as not to	force 0805:0.5kg)to shall be seconds. Als	Classification on a PCB wi the side of the force	
			DU		press tool	wide

Note : When there are questions concerning measurement result : measurement shall be made after 48 ± 2 hours of recovery under the standard condition.

8. Soldering and Mounting

(1) Soldering

Mildly activated rosin fluxes are preferred. The minimum amount of solder can lead to damage from the stresses caused by the difference in coefficients of expansion between solder, chip and substrate. TAI-TECH terminations are suitable for re-flow soldering systems. If hand soldering cannot be avoided, the preferred technique is the utilization of hot air soldering tools.

(2) Solder re-flow:


Recommended temperature profiles for re-flow soldering in Figure 1.

(3) Soldering Iron:

Products attachment with a soldering iron is discouraged due to the inherent process control limitations. In the event that a soldering iron must be employed the following precautions are recommended.


- \bullet Preheat circuit and products to 150 $^\circ\!{\rm C}$ $$\bullet$$ Never contact the ceramic with the iron tip
- 355°C tip temperature (max) 1.0mm tip diameter (max)
- <)

Use a 20 watt soldering iron with tip diameter of 1.0mm
Limit soldering time to 4–5sec.




9. Packaging Information

(1) Reel Dimension



Туре	A(mm)	B(mm)	C(mm)	D(mm)
13"x24mm	24.4+2/-0	100±2	13+0.5/-0.2	330

(2) Tape Dimension




Series	Size	Bo(mm)	Bz(mm)	Ao(mm)	Az(mm)	Ko(mm)	P(mm)	W(mm)	F(mm)	t(mm)
TMPC	1235	14.1±0.1	13.0±0.1	12.9±0.1	7.0±0.1	4.0±0.1	16.0±0.1	24±0.3	11.5±0.1	0.35±0.05

(3) Packaging Quantity

ТМРС	1235
Chip / Reel	500
Inner box	1000
Carton	4000

(4) Tearing Off Force



The force for tearing off cover tape is 10 to 130 grams in the arrow direction under the following conditions(referenced ANSI/EIA-481-C-2003 of 4.11 stadnard).

Room Temp.	Room Humidity (%)	Room atm (hPa)	Tearing Speed mm/min	
5~35	45~85	860~1060	300	

Application Notice

- Storage Conditions
 To maintain the solderability of terminal electrodes:

 TAIPAQ products meet IPC/JEDEC J-STD-020D standard-MSL, level 1.
 Temperature and humidity conditions: Less than 40°C and 60% RH.
 Recommended products should be used within 12 months form the time of delivery.
- 4. The packaging material should be kept where no chlorine or sulfur exists in the air.
- Transportation
- 1. Products should be handled with care to avoid damage or contamination from perspiration and skin oils.
- 2. The use of tweezers or vacuum pick up is strongly recommended for individual components.
- 3. Bulk handling should ensure that abrasion and mechanical shock are minimized.



