



SHENZHEN TUOFENG SEMICONDUCTOR TECHNOLOGY CO. LTD

N-CHANNEL MOSFET


SSS2N60

2 Amps, 600Volts**N-CHANNEL MOSFET****■ DESCRIPTION**

The SSS2N60 is a high voltage MOSFET and is designed to have better characteristics, such as fast switching time, low gate charge, low on-state resistance and have a high rugged avalanche characteristics. This power MOSFET is usually used at high speed switching applications in power supplies .PWM motor controls, high efficient DC to DC converters and bridge circuits.

■ FEATURES

- $R_{DS(ON)}=3.8 \Omega @V_{GS}=10V$
- Ultra Low gate charge(typical 9.0nC)
- Low reverse transfer capacitance($C_{rss}=\text{typical } 5.0\text{pF}$)
- Fast switching capability
- Avalanche energy specified
- Improved dv/dt capability,high ruggedness

■ SYMBOL**■ ORDERING INFORMATION**

Order Number		Package	Pin Assignment			Packing
Normal	Lead Free Plating		1	2	3	
2N60-TA3-T	2N60L-TA3-T	TO-220	G	D	S	Tube
2N60-TF3-T	2N60L-TF3-T	TO-220F	G	D	S	Tube
2N60-TM3-T	2N60L-TM3-T	TO-251	G	D	S	Tube
2N60-TN3-R	2N60L-TN3-R	TO-252	G	D	S	Tape Reel
2N60-TN3-T	2N60L-TN3-T	TO-252	G	D	S	Tube

Note:Pin Assignment: G:Gate D:Drain S:Source

2N60L-TA3-T (1) Packing Type (2) Package Type (3) Lead Plating	(1)T:Tube,R:Tape Reel (2)TA3:TO220,TF3:TO-220F,TM3:TO-251,TN3:TO-252 (3)L:Lead Free Plating Blank: Pb/Sn
---	--

■ ABSOLUTE MAXIMUM RATINGS ($T_c=25^\circ\text{C}$, unless otherwise specified)

PARAMETER		SYMBOL	PATINGS	UNIT
Drain-Source Voltage		V_{DSS}	600	V
Gate-Source Voltage		V_{GSS}	± 30	V
Avalanche Current(Note 2)		I_{AP}	2.0	A
Drain Currentet Continuous	$T_c=25^\circ\text{C}$	I_D	2.0	A
	$T_c=100^\circ\text{C}$		1.26	A
Drain Current Pulsed(Note 2)		I_{DP}	8.0	A



SHENZHEN TUOFENG SEMICONDUCTOR TECHNOLOGY CO. LTD

N-CHANNEL MOSFET

SSS2N60

Avalanche Energy	Repetitive(Note 2)	E _{AR}	4.5	mJ
	Single Pulse(Note 3)	E _{AS}	120	mJ
Peak Diode Recovery dv/dt(Note 4)		dv/dt	4.5	v/ns
Total Power Dissipation	T _c =25°C	P _D	45	W
	Derate above 25°C		0.36	W/°C
Junction Temperature	T _J		+150	°C
Storage Temperature	T _{STG}		-55~+150	°C

Note:1.Absolute maximum ratings are those values beyond which the device could be permanently damaged

Absolute maximum ratings are stress ratings only and functional device operation is not implied

2.Repetitive Rating:Pulse width limited bu maximum junction temperature

3.L=64mH,I_{AS}=2.0A,V_{DD}=50V,R_G=25 Ω ,Starting T_J=25°C4. I_{SD}≤2.4A,di/dt≤200A/ μ s, V_{DD}≤BV_{DSS}, Starting T_J=25°C

■ THERMAL DATA

PARAMETER	PACKAGE	SYMBOL	RATINGS	UNIT
Thermal Resistance Junction-Ambient	TO-251	θ _{JA}	112	°C/W
	TO-252		112	
	TO-220		54	
	TO-220F		54	
Thermal Resistance Junction-Case	TO-251	θ _{JC}	12	°C/W
	TO-252		12	
	TO-220		4	
	TO-220F		4	

■ ELECTRICAL CHARACTERISTICS(T_J=25°C, unless Otherwise specified.)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Off Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V,I _D =250 μ A	600			V
Zero Gate Voltage Drain Current	I _{DS}	V _{DS} =600V,V _{GS} =0V			10	μ A
Gate-Body Leakage Current	I _{GSS}	V _{GS} =30V,V _{DS} =0V			100	nA
		V _{GS} =-30V,V _{DS} =0V			-100	nA
Breakdown Voltage Temperature	△BV _{DSS} /△T _J	I _D =250 μ A		0.4		V/°C
On Characteristics						
Gate Threshold Voltage	V _{GS(TH)}	V _{DS} =V _{GS} , I _D =250 μ A	2.0		4.0	V
Static Drain-Source On-Resistance	R _{DS(ON)}	V _{DS} =10V,I _D =1A		3.8	5	Ω
Forward Transconductance	g _{FS}	V _{DS} =50V,I _D =1A(Note 1)		2.25		S
Dynamic Characteristics						
Input Capacitance	C _{ISS}	V _{DS} =25V,V _{GS} =0V,f=1MHz		270	350	pF
Output Capacitance	C _{OSS}			40	50	pF
Reverse Transfer Capacitance	C _{rss}			5	7	pF

■ ELECTRICAL CHARACTERISTICS(Cont.)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
-----------	--------	-----------------	-----	-----	-----	------



SHENZHEN TUOFENG SEMICONDUCTOR TECHNOLOGY CO. LTD

N-CHANNEL MOSFET

SSS2N60

Switching Characteristics

Turn-On Delay Time	$t_{D(ON)}$	$V_{DD}=300V, I_D=2.4A, R_G=25\Omega$	10	30	ns
Rise Time	t_R		25	60	ns
Turn-Off Delay Time	$t_{D(OFF)}$		20	50	ns
Fall Time	t_F		25	60	ns
Total Gate Charge	Q_G	$V_{DS}=480V, V_{GS}=10V, I_D=2.4A$	9.0	11	nC
Gate-Source Charge	Q_{GS}		1.6		nC
Gate-Drain Charge	Q_{GD}		4.3		nC







Drain-Source Diode Characteristics

Drain-Source Diode Forward Voltage	V_{SD}	$V_{GS}=0V, I_{SD}=2.0A$			1.4	V
Continuous Drain-Source Current	I_{SD}				2.0	A
Pulsed Drain-Source Current	I_{SM}				8.0	A
Reverse Recovery Time	t_{RR}	$V_{GS}=0V, I_{SD}=2.4A,$ $di/dt=100A/\mu A$		180		ns
Reverse Recovery Charge	Q_{RR}			0.72		μC

Note: 1. Pulse Test: Pulse Width $\leq 300 \mu s$, Duty Cycle $\leq 2\%$

2. Essentially Independent of Operating Temperature

TYPICAL CHARACTERISTICS






SHENZHEN TUOFENG SEMICONDUCTOR TECHNOLOGY CO. LTD

N-CHANNEL MOSFET


SSS2N60

■ TYPICAL CHARACTERISTICS(Cont)


Breakdown Voltage vs Temperature




On-Resistance vs Temperature



Max. Safe Operating Area



Max. Drain Current vs. Case Temperature



Thermal Response

