

# **30V N-Channel Trench MOSFET**


### **FEATURES**

- Super Low Gate Charge
- 100% EAS Guaranteed
- RoHS compliant
- Green Device Available
- Excellent CdV/dt effect decline
- Advanced high cell density Trench technology

### **APPLICATIONS**

- Switch Mode Power Supply (SMPS)
- Uninterruptible Power Supply (UPS)
- Hard switched and high frequency circuits





Device Marking and Package Information						
Device	Package	Marking				
CTP03N2P7	TO-220	CTP03N2P7				

Absolute Maximum Ratings at T <sub>j</sub> = 25°C unless otherwise noted							
Parameter		Symbol	Value	Unit			
Drain-Source Voltage (V <sub>GS</sub> = 0V)		V <sub>DSS</sub>	30	V			
Continuous Drain Current T <sub>C</sub> = 25°C	(note1)	,	230	А			
Continuous Drain Current T <sub>C</sub> = 100°C	(note1)	I <sub>D</sub>	150	Α			
Pulsed Drain Current (note2)		I <sub>DM</sub>	500	А			
Gate Source Voltage		V <sub>GSS</sub>	±20	V			
Single Pulse Avalanche Energy (note3)		E <sub>AS</sub>	246	mJ			
Power Dissipation $T_C = 25^{\circ}C$ (note4)		P <sub>D</sub>	187	W			
Operating Junction and Storage Temperatu	re Range	$T_J, T_{stg}$	-55~+175	∘C			

Thermal Characteristics					
Parameter		Symbol	Value	Unit	
Thermal Resistance, Junction-to-Case		$R_{ heta JC}$	0.8	°C/W	
Thermal Resistance, Junction-to-Ambient	p-Ambient (note1) R <sub>eJA</sub> 62				




Parameter	Symbol	Test Conditions		Value	l	Unit
			Min.	Тур.	Max.	
Static						
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS} = 0V, I_D = 250\mu A$	30			V
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	$V_{DS} = 30V, V_{GS} = 0V, T_{J} = 25^{\circ}C$			1	uA
2010 Odio Voltago Brain Odinoni	.022	$V_{DS} = 30V, V_{GS} = 0V, T_{J} = 55^{\circ}C$			5	uA
Gate-Source Leakage	$I_{GSS}$	$V_{GS} = \pm 20 V$			±100	nA
Gate-Source Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_{D} = 250 \mu A$	1.0		2.5	V
Drain Course On Decistones (note2)	D	$V_{GS} = 10V, I_D = 30A$		2.0	2.7	mΩ
Drain-Source On-Resistance (note2)	$R_{DS(on)}$	$V_{GS} = 4.5V, I_D = 15A$		2.6	3.8	mΩ
Dynamic						
Input Capacitance	C <sub>iss</sub>	V <sub>GS</sub> = 0V,		5850		pF
Output Capacitance	C <sub>oss</sub>	$V_{DS} = 15V$ ,		720		
Reverse Transfer Capacitance	C <sub>rss</sub>	f = 1.0MHz		525		
Total Gate Charge (4.5V)	$Q_g$			56.9		пС
Gate-Source Charge	$Q_{gs}$	$V_{DS} = 15V, I_{D} = 15A,$ $V_{GS} = 4.5V$		13.8		
Gate-Drain Charge	$Q_{gd}$	30		23.5		
Turn-on Delay Time	t <sub>d(on)</sub>			20.1		ns
Turn-on Rise Time	t <sub>r</sub>	V <sub>DS</sub> = 15V, I <sub>D</sub> = 1A		6.3		
Turn-off Delay Time	t <sub>d(off)</sub>	$V_{DS} = 15V, I_{D} = 1A$ $V_{GS} = 10V, R_{G} = 3\Omega$		124.6		
Turn-off Fall Time	t <sub>f</sub>			15.8		
Body Diode Characteristics						
Source-Drain Current(Body Diode)	I <sub>SD</sub>				230	А
Pulsed Source-Drain Current(Body Diode)					500	
Body Diode Voltage	$V_{SD}$	$T_J = 25^{\circ}C$ , $I_{SD} = 1A$ , $V_{GS} = 0V$			1.2	V

#### **Notes**

- 1. The data tested by surface mounted on a 1 inch2 FR-4 board with 2OZ copper.
- 2. The data tested by pulsed , pulse width≤300us , duty cycle≤2%
- 3. The EAS data shows Max. rating . The test condition is VDD =25V,VGS =10V,L=0.1mH  $\,$
- 4. The power dissipation is limited by 175°C junction temperature
- 5. The data is theoretically the same as ID and IDM , in real applications , should be limited by total power dissipation.



## **Typical Characteristics** $T_J = 25^{\circ}\text{C}$ , unless otherwise noted






Fig.1 Typical Output Characteristics




Fig.2 On-Resistance vs. G-S Voltage




Fig.3 Forward Characteristics of Reverse Diode




Fig.5 Normalized V<sub>GS(th)</sub> vs. T<sub>J</sub>

Fig.4 Gate-Charge Characteristics





Fig.6 Normalized R<sub>DSON</sub> vs. T<sub>J</sub>



# **Typical Characteristics** $T_J = 25^{\circ}\text{C}$ , unless otherwise noted






Fig.7 Capacitance

Fig.8 Safe Operating Area




Fig.9 Normalized Maximum Transient Thermal Impedance



Figure A: Gate Charge Test Circuit and Waveform




Figure B: Resistive Switching Test Circuit and Waveform






Figure C: Unclamped Inductive Switching Test Circuit and Waveform





# **TO-220 Dimension**



DIM	Millimeters		Inches		DIM	Millimeters		Inches	
	Min.	Max.	Min.	Max.	ואווט	Min.	Max.	Min.	Max.
Α	4.400	4.600	0.173	0.181	е	2.540*		0.100*	
A1	2.250	2.550	0.089	0.100	e1	4.980	5.180	0.196	0.204
b	0.710	0.910	0.028	0.036	F	2.650	2.950	0.104	0.116
b1	1.170	1.370	0.046	0.054	Н	7.900	8.100	0.311	0.319
С	0.330	0.650	0.013	0.026	h	0.000	0.300	0.000	0.012
c1	1.200	1.400	0.047	0.055	L	12.900	13.400	0.508	0.528
D	9.910	10.250	0.390	0.404	L1	2.850	3.250	0.112	0.128
Е	8.950	9.750	0.352	0.384	V	7.500 REF		0.295 REF	
E1	12.650	12.950	0.498	0.510	Φ	3.600	3.800	0.142	0.150



## **Disclaimer**

All product specifications and data are subject to change without notice.

For documents and material available from this datasheet, Suzhou Convert does not warrant or assume any legal liability or responsibility for the accuracy, completeness of any product or technology disclosed hereunder.

No license, express or implied, by estoppels or otherwise, to any intellectual property rights is granted by this document or by any conduct of Suzhou Convert.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless. Customers using or selling Suzhou Convert products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Suzhou Convert for any damages arising or resulting from such use or sale.

Suzhou Convert disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Suzhou Convert's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

Suzhou Convert SemiConductor CO., Ltd. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

In the event that any or all Suzhou Convert products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. Suzhou Convert believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.