

# Ultra Low ON-Resistance, Low Voltage, Dual, SPDT Analog Switch

# FEATURES

- -3dB Bandwidth: 30MHz
- High Speed, Typically 50ns
- Supply Range: +1.8V to +5.5V
- Low ON-State Resistance, 0.6Ω(TYP)
- Break-Before-Make Switching
- Rail-to-Rail Operation
- TTL/CMOS Compatible
- Extended Industrial Temperature Range: -40°C to +125°C

# **APPLICATIONS**

- Wearable Devices
- Battery-Operated Equipment
- Signal Gating, Chopping, Modulation or Demodulation (Modem)
- Portable Computing
- Cell Phones

# **FUNCTION TABLE**

LOGIC	NO	NC
0	OFF	ON
1	ON	OFF


### **PIN DESCRIPTION**

# DESCRIPTION

The RS2323 is a dual, low on-resistance, single-pole double-throw (SPDT) analog switch that is designed to operate from 1.8 V to 5.5 V.

The RS2323 device can handle both analog and digital signals. It features fast switching speeds (50ns) and low on-resistance ( $0.6\Omega$  TYP).

Applications include signal gating, chopping, modulation or demodulation (modem), and signal multiplexing for analog-to-digital and digital-to-analog conversion systems.



NAME	PIN	FUNCTION
V+	1	Power Supply
NO1, NO2	2, 10	Normally-Open Terminal
COM1, COM2	3, 9	Common Terminal
IN1, IN2	4, 8	Digital Control Pin
NC1, NC2	5, 7	Normally-Closed Terminal
GND	6	Ground

1



#### ABSOLUTE MAXIMUM RATINGS<sup>(1)</sup>

V+, IN to GND	0.3V to 7.0V
Analog, Digital Voltage Range (2)	- 0.3 to (V+) + 0.3V
Continuous Current NO, NC, or COM	±500mA
Peak Current NO, NC, or COM	±800mA
Storage Temperature	. −65°C to +150°C
Operating Temperature	−40°C to +125°C
Junction Temperature	
Package Thermal Resistance @ TA = +2	25°C
SOT23-5, SOT23-6	200°C/W
MSOP-10, SOIC-8 ,TSSOP-8	150°C/W
SOIC-14, TSSOP-14	100°C/W
Lead Temperature (Soldering, 10s)	260°C
ESD Susceptibility	
НВМ	1000V
MM	100V

(1) Stresses above these ratings may cause permanent damage. Exposure to absolute maximum conditions for extended periods may degrade device reliability. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those specified is not implied.

(2) Input terminals are diode-clamped to the power-supply rails. Input signals that can swing more than 0.3V beyond the supply rails should be current-limited to 10mA or less.



ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

# **PACKAGE/ORDERING INFORMATION**

PRODUCT	ORDERING NUMBER	TEMPERATURE RANGE	PACKAGE LEAD	PACKAGE MARKING	PACKAGE OPTION
RS2323	RS2323XUTQK10	-40°C~125°C	QFN- 1.4x1.8-10L	2323X	Tape and Reel,3000

NOTE: X = Date Code

#### **MARKING INFORMATION**





#### **ELECTRICAL CHARACTERISTICS**

V+ = 5.0 V,  $T_A$ = -40°C to 125°C (unless otherwise noted)

PARAMETER	SYMBOL	CONDITIONS	V+	TA	MIN	ТҮР	MAX	UNITS
ANALOG SWITCH								
Analog Signal Range	Vno, Vnc, Vcom			FULL	0		V+	V
		$0 \leqslant (V_{NO} \text{ or } V_{NC}) \leqslant V+,$ I <sub>COM</sub> = -10mA, Switch ON, See Figure 1	5)/	+25°C		0.6	1.0	Ω
	_		5V	FULL			1.2	Ω
On-Resistance	Ron		0.01/	+25°C		1.0	1.5	Ω
			3.3V	FULL			1.7	Ω
				+25°C		0.04	0.1	Ω
On-Resistance Match	A	$0 \leqslant$ (V <sub>NO</sub> or V <sub>NC</sub> ) $\leqslant$ V+,	5V	FULL			0.12	Ω
Between Channels	ΔRon	I <sub>COM</sub> = -10mA, Switch ON, See Figure 1		+25℃		0.04	0.1	Ω
			3.3V	FULL			0.12	Ω
	Rflat(on)	$0 \leqslant (V_{NO} \text{ or } V_{NC}) \leqslant V+,$ I <sub>COM</sub> = -10mA, Switch ON, See Figure 1		+25℃		0.18	0.3	Ω
			5V	FULL			0.4	Ω
On-Resistance Flatness			3.3V	+25°C		0.54	0.7	Ω
				FULL			0.8	Ω
NC,NO OFF Leakage Current	INC(OFF), INO(OFF)	V <sub>NO</sub> or V <sub>NC</sub> = 0.3V, V+/2 V <sub>COM</sub> = V+/2, 0.3V See Figure 2	1.8 to 5.5V	FULL			1	μA
NC,NO,COM ON Leakage Current	Inc(on), Ino(on), Icom(on)	V <sub>NO</sub> or V <sub>NC</sub> = 0.3V, Open V <sub>COM</sub> = Open, 0.3V See Figure 2	1.8 to 5.5V	FULL			1	μA
DIGITAL CONTROL INP	UTS <sup>(1)</sup>		1		1	I		
Input High Voltage	Vinh		5V	FULL	1.5			V
			3.3V	FULL	1.3			V
Input Low Voltage	Vinl		5V	FULL			0.6	V
			3.3V	FULL			0.5	V
Input Leakage Current	lin	VIN = VIO or 0	1.8 to 5.5V	FULL			1	μA

(1) All unused digital inputs of the device must be held at VIO or GND to ensure proper device operation.





# **ELECTRICAL CHARACTERISTICS (continued)** V+ = 5.0 V, TEMP= -40°C to 125°C (unless otherwise noted))


PARAMETER	SYMBOL	CONDITIONS		V+	TEMP	MIN	ТҮР	MAX	UNITS
DYNAMIC CHARACTER	RISTICS								
Turn On Time	tau	$V_{COM} = V_{+}, R_{L} = 300\Omega, C_{L} = 35pF,$		5V	. 05%0		50		ns
Turn-On Time	ton	See Figure 5			+25℃		50		
Turn-Off Time	toff	$V_{COM} = V+, R_{L} = 300\Omega, C_{L} = 35pF,$		5V	1.05%		15		ne
	LOFF	See Figure 5		3.3V	+25℃		17		ns
Break-Before-Make	tввм	$V_{NO1} = V_{NC1} = V_{NO2} = V$	,	5V	+25°C		10		ns
Time Delay	LBBM	$R_L = 300\Omega, C_L = 35pF,$	See Figure 6	3.3V	+23 0		11		
	Oiso	R <sub>L</sub> = 50Ω, Switch OFF, See Figure 8	f = 100KHz		+25°C		-68		dB
Off Isolation			f = 10KHz		+25°C		-86		dB
-3dB Bandwidth	BW	Switch ON, R <sub>L</sub> = 50Ω See Figure 7			+25°C		30		MHz
NC,NO OFF Capacitance	CNC(OFF), CNO(OFF)	V <sub>NC</sub> or V <sub>NO</sub> =V+/2 or GND, Switch OFF See Figure 4			+25°C		80		pF
NC,NO,COM ON Capacitance	CNC(ON), CNO(ON), CCOM(ON)	$V_{NC}$ or $V_{NO}$ =V+/2 or GN ON See Figure 4	ND, Switch		+25°C		350		pF
POWER REQUIREMEN	тѕ								
Power Supply Range	V+				FULL	1.8		5.5	V
Power Supply Current	l+	$V_{IN}$ = GND or V+		5.5V	FULL			1	μA



#### **TYPICAL CHARACTERISTICS**









# **Parameter Measurement Information**




Figure 1.ON-State Resistance (ron)




Figure 2.OFF-State Leakage Current (ICOM(OFF), INO(OFF))





Figure 3.ON-State Leakage Current (ICOM(ON), INO(ON))










Figure 5.Turn-On (ton) and Turn-Off Time (toff)





Figure 6.Break-Before-Make Time (t<sub>BBM</sub>)





#### Figure 7.Bandwidth (BW)




Figure 8.OFF Isolation (O<sub>ISO</sub>)






Figure 9.Crosstalk (XTALK)





#### Figure 10.Charge Injection (Qc)



# Figure11.Total Harmonic Distortion (THD)



# $\label{eq:qensions} \begin{array}{l} \mbox{Package outline dimensions} \\ \mbox{QFN-1.4x1.8-10L} \end{array}$

