

## Description

The HSU90N02 is the high cell density trenched N-ch MOSFETs, which provide excellent RDSON and gate charge for most of the synchronous buck converter applications.


The HSU90N02 meet the RoHS and Green Product requirement, 100% EAS guaranteed with full function reliability approved.

- 100% EAS Guaranteed
- Green Device Available
- Super Low Gate Charge
- Battery protection
- Power management

## Product Summary

$V_{DS}$	20	V
$R_{DS(ON),typ}$	2.7	mΩ
$I_D$	90	A

## TO252 Pin Configuration



## Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
$V_{DS}$	Drain-Source Voltage	20	V
$V_{GS}$	Gate-Source Voltage	$\pm 12$	V
$I_D @ T_c = 25^\circ C$	Continuous Drain Current, $V_{GS} @ 10V_1$	90	A
$I_D @ T_c = 100^\circ C$	Continuous Drain Current, $V_{GS} @ 10V_1$	59	A
$I_{DM}$	Pulsed Drain Current <sup>2</sup>	350	A
EAS	Single Pulse Avalanche Energy <sup>3</sup>	108	mJ
$P_D @ T_c = 25^\circ C$	Total Power Dissipation <sup>4</sup>	82	W
$T_{STG}$	Storage Temperature Range	-55 to 175	°C
$T_J$	Operating Junction Temperature Range	-55 to 175	°C

## Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient (Steady State) <sup>1</sup>	---	50	°C/W
$R_{\theta JA}$	Thermal Resistance Junction-Ambient 1 ( $t \leq 10s$ )	---	25	°C/W
$R_{\theta JC}$	Thermal Resistance Junction-Case <sup>1</sup>	---	1.92	°C/W

**Electrical Characteristics (T<sub>J</sub>=25 °C, unless otherwise noted)**

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV <sub>DSS</sub>	Drain-Source Breakdown Voltage	V <sub>GS</sub> =0V , I <sub>D</sub> =250μA	20	---	---	V
△BV <sub>DSS</sub> /△T <sub>J</sub>	BVDSS Temperature Coefficient	Reference to 25°C , I <sub>D</sub> =1mA	---	0.028	---	V/°C
R <sub>Ds(ON)</sub>	Static Drain-Source On-Resistance <sub>2</sub>	V <sub>GS</sub> =4.5V , I <sub>D</sub> =30A	---	2.7	4	mΩ
		V <sub>GS</sub> =2.5V , I <sub>D</sub> =20A	---	4.1	6	
V <sub>GS(th)</sub>	Gate Threshold Voltage	V <sub>GS</sub> =V <sub>DS</sub> , I <sub>D</sub> =250μA	0.4	0.7	1.1	V
△V <sub>GS(th)</sub>	V <sub>GS(th)</sub> Temperature Coefficient		---	-6.16	---	mV/°C
I <sub>DSS</sub>	Drain-Source Leakage Current	V <sub>DS</sub> =20V , V <sub>GS</sub> =0V , T <sub>J</sub> =25°C	---	---	1	uA
		V <sub>DS</sub> =20V , V <sub>GS</sub> =0V , T <sub>J</sub> =55°C	---	---	5	
I <sub>GSS</sub>	Gate-Source Leakage Current	V <sub>GS</sub> =±12V , V <sub>DS</sub> =0V	---	---	±100	nA
Q <sub>g</sub>	Total Gate Charge (4.5V)	V <sub>DS</sub> =15V , V <sub>GS</sub> =4.5V , I <sub>D</sub> =18A	---	50	---	nC
Q <sub>gs</sub>	Gate-Source Charge		---	3.9	---	
Q <sub>gd</sub>	Gate-Drain Charge		---	22	---	
T <sub>d(on)</sub>	Turn-On Delay Time	V <sub>DD</sub> =15V , V <sub>GS</sub> =4.5V , R <sub>G</sub> =1.8Ω	---	10	---	ns
T <sub>r</sub>	Rise Time		---	33	---	
T <sub>d(off)</sub>	Turn-Off Delay Time		---	68	---	
T <sub>f</sub>	Fall Time		---	52	---	
C <sub>iss</sub>	Input Capacitance	V <sub>DS</sub> =15V , V <sub>GS</sub> =0V , f=1MHz	---	3200	---	pF
C <sub>oss</sub>	Output Capacitance		---	430	---	
C <sub>rss</sub>	Reverse Transfer Capacitance		---	414	---	

**Diode Characteristics**

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I <sub>S</sub>	Continuous Source Current <sub>1,5</sub>	V <sub>G</sub> =V <sub>D</sub> =0V , Force Current	---	---	90	A
I <sub>SM</sub>	Pulsed Source Current <sub>2,5</sub>		---	---	360	A
V <sub>SD</sub>	Diode Forward Voltage <sub>2</sub>	V <sub>GS</sub> =0V , I <sub>S</sub> =30A , T <sub>J</sub> =25°C	---	---	1.2	V
t <sub>rr</sub>	Reverse Recovery Time	I <sub>F</sub> =30A , dI/dt=100A/μs ,	---	24	---	nS
Q <sub>rr</sub>	Reverse Recovery Charge	T <sub>J</sub> =25°C	---	12	---	nC

Note :

- 1.The data tested by surface mounted on a 1 inch<sup>2</sup> FR-4 board with 2OZ copper.
- 2.The data tested by pulsed , pulse width ≤ 300us , duty cycle ≤ 2%
- 3.The EAS data shows Max. rating . The test condition is V<sub>DD</sub>=15V,V<sub>GS</sub>=4.5V,L=0.5mH,I<sub>AS</sub>=22A
- 4.The power dissipation is limited by 175°C junction temperature
- 5.The data is theoretically the same as I<sub>D</sub> and I<sub>DM</sub> , in real applications , should be limited by total power dissipation.



Typical Characteristics




Figure 1 Output Characteristics




Figure 2 Transfer Characteristics




Figure 3 Rdson-Drain Current




Figure 4 Rdson-JunctionTemperature




Figure 5 Gate Charge




Figure 6 Source- Drain Diode Forward




Figure 7 Capacitance vs Vds




Figure 8 Safe Operation Area




Figure 9 Power De-rating




Figure 10  $V_{GS(th)}$  vs Junction Temperature






Figure 11 Normalized Maximum Transient Thermal Impedance





## Test Circuit & Waveform



Gate Charge Test Circuit & Waveform





Resistive Switching Test Circuit & Waveforms



Unclamped Inductive Switching (UIS) Test Circuit & Waveforms




Diode Recovery Test Circuit & Waveforms



## Ordering Information

Part Number	Package code	Packaging
HSU90N02	TO252-2	2500/Tape&Reel



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	2.200	2.400	0.087	0.094
A1	0.000	0.127	0.000	0.005
B	1.350	1.650	0.053	0.065
b	0.500	0.700	0.020	0.028
b1	0.700	0.900	0.028	0.035
c	0.430	0.580	0.017	0.023
c1	0.430	0.580	0.017	0.023
D	6.350	6.650	0.250	0.262
D1	5.200	5.400	0.205	0.213
E	5.400	5.700	0.213	0.224
e	2.300 TYP.		0.091 TYP.	
e1	4.500	4.700	0.177	0.185
L	9.500	9.900	0.374	0.390
L1	2.550	2.900	0.100	0.114
L2	1.400	1.780	0.055	0.070
L3	0.600	0.900	0.024	0.035
V	3.800 REF.		0.150 REF.	