

# 350MHz, Rail-to-Rail Input/Output High Speed Operational Amplifiers

#### **Features**

■ 350MHz @ -3dB bandwidth

■ Operates on 2.5V ~ 5.5V Supplies

■ Slew Rate: 250V/µs

Rail-to-Rail Input and Output (RRIO)

■ Low Quiescent Current: 4.5mA

Unity Gain Stable

No Phase Reversal

Extended Temperature Ranges
 From -40°C to +125°C

Small Packaging
 COS8091 available in SOT23-5/SOP-8
 COS8092 available in SOP-8/MSOP-8
 COS8094 available in SOP14/TSSOP14

# **Applications**

- Coaxial cable drivers
- Active filters
- Video and Cameras
- CCD imaging systems
- Clock buffers
- Base stations
- A-to-D Drivers

## **General Description**

The COS8091(single), COS8092(dual) and COS8094(quad) are low cost, voltage feedback, rail-to-rail input and output, high speed amplifiers operated on 2.5 to 5.5 supplies. They have bandwidth and slew rate typically found in current feedback amplifiers. The wide bandwidth and fast slew rate make these amplifiers useful in many general-purpose, high speed applications.

Despite their low cost, the COS8091/2/4 family provide excellent overall performance and versatility. They have both rail-to-rail input and output range. The output voltage swing extends to within 10 mV of each rail, providing the maximum output dynamic range with excellent overdrive recovery. This makes COS8091/2/4 family useful for video electronics, such as cameras, video switchers, or any high speed portable equipment. Low distortion and fast settling make them ideal for active filter applications.


Rev1.0
Copyright@2018 Cosine Nanoelectronics Inc. All rights reserved

The information provided here is believed to be accurate and reliable. Cosine Nanoelectronics assumes no reliability for inaccuracies and omissions. Specifications described and contained here are subjected to change without notice on the purpose of improving the design and performance. All of this information described herein should not be implied or granted for any third party.

1



# 1. Pin Configuration and Functions



## **Pin Functions**

Name	Description	Note
+Vs	Positive power supply	A bypass capacitor of 0.1µF as close to the part as possible should be placed between power supply pins or between supply pins and ground.
-Vs	Negative power supply or ground	If it is not connected to ground, bypass it with a capacitor of 0.1µF as close to the part as possible.
-IN	Negative input	Inverting input of the amplifier. Voltage range of this pin can go from -Vs -0.3V to +Vs + 0.3V.
+IN	Positive input	Non-inverting input of the amplifier. This pin has the same voltage range as –IN.
OUT	Output	The output voltage range extends to within millivolts of each supply rail.
NC	No connection	

# 2. Package and Ordering Information

Model	Channel	Order Number	Package	Package Option	Marking Information
COS8091	1	COS8091TR	SOT23-5	Tape and Reel, 3000	C8091
CO28091 1	ļ ,	COS8091SR	SOP-8	Tape and Reel, 3000	COS8091
COS8092 2	COS8092SR	SOP-8	Tape and Reel, 3000	COS8092	
	COS8092MR	MSOP-8	Tape and Reel, 3000	COS8092	
COS8094 4	4	COS8094SR	SOP-14	Tape and Reel, 3000	COS8094
	4	COS8094TR	TSSOP-14	Tape and Reel, 3000	COS8094



# 3. Product Specification

## 3.1 Absolute Maximum Ratings (1)

Parameter	Rating	Units
Power Supply: +Vs to -Vs	6	V
Input Voltage	-Vs -0.5V to +Vs + 0.5V	V
Input Current (2)	10	mA
Storage Temperature Range	-65 to 150	°C
Junction Temperature	150	°C
Operating Temperature Range	-40 to 125	°C
ESD Susceptibility, HBM	2000	V

<sup>(1)</sup> Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

#### 3.2 Thermal Data

Parameter	Rating	Unit
Package Thermal Resistance	190 (SOT23-5) 206 (MSOP8) 155 (SOP8) 105 (TSSOP14) 82 (SOP14)	°C/W

#### 3.3 Recommended Operating Conditions

Parameter	Rating	Unit
DC Supply Voltage	2.5V ~ 5.5V	V
Input common-mode voltage range	-Vs ~ +Vs	V
Operating ambient temperature	-40 to +85	°C

<sup>(2)</sup> Input terminals are diode-clamped to the power-supply rails. Input signals that can swing more than 0.5V beyond the supply rails should be current-limited to 10mA or less.



#### 3.4 Electrical Characteristics

(+V<sub>S</sub>=+5V, -V<sub>S</sub>=0, V<sub>CM</sub>=V<sub>S</sub>/2,  $T_A$ =+25°C,  $R_L$ =2k $\Omega$  to V<sub>S</sub>/2, unless otherwise noted)

Parameter	Symbol	Conditions	Min	Тур	Max	Unit	
Input Characteristics							
Input Offset Voltage	Vos			2	10	mV	
Input Offset Voltage Drift	ΔVos/ΔT	-40 to 125°C		10		μV/°C	
Input Bias Current	IB			±2.5		рА	
Input Offset Current	los			±2.5		рА	
Common-Mode Voltage Range	V <sub>CM</sub>		-0.1		5.6	V	
Common-Mode Rejection Ratio	CMRR	V <sub>CM</sub> =0.1V to 11.9V		125		dB	
Open-Loop Voltage Gain	AOL	Vo=0.2V to 11.8V		120		dB	
<b>Output Characteristics</b>							
		R <sub>L</sub> =10kΩ		10		mV	
Output Voltage Swing from Rail		R <sub>L</sub> =2kΩ		25		mV	
		R <sub>L</sub> =150Ω		200		mV	
Short-Circuit Current	Isr	Sourcing		110		mA	
Short-Circuit Current	Isk	Sinking		120		mA	
Power Supply							
Operating Voltage Range			2.5		5.5	V	
Power Supply Rejection Ratio	PSRR	Vs = 2.5V to 5.5V		90		dB	
Quiescent Current / Amplifier	IQ	V <sub>S</sub> =5V		4.5		mA	
Dynamic Performance							
Gain Bandwidth Product	GBWP	G=+1		350		MHz	
Slew Rate	SR	G = +1 , 2V Output Step		250		V/µs	
Settling Time to 0.1%	ts	G = +1 , 2V Output Step		50		ns	
Noise Performance							
Voltage Noise Density	en	f=1kHz		6		nV/ √ Hz	



## 4.0 Application Notes

#### **Driving Capacitive Loads**

Driving large capacitive loads can cause stability problems for voltage feedback op amps. As the load capacitance increases, the feedback loop's phase margin decreases, and the closed loop bandwidth is reduced. This produces gain peaking in the frequency response, with overshoot and ringing in the step response. A unity gain buffer (G = +1) is the most sensitive to capacitive loads, but all gains show the same general behavior.

When driving large capacitive loads with these op amps (e.g., > 100 pF when G = +1), a small series resistor at the output (R<sub>ISO</sub> in Figure 1) improves the feedback loop's phase margin (stability) by making the output load resistive at higher frequencies. It does not, however, improve the bandwidth.

To select  $R_{ISO}$ , check the frequency response peaking (or step response overshoot) on the bench. If the response is reasonable, you do not need  $R_{ISO}$ . Otherwise, start  $R_{ISO}$  at 1 k $\Omega$  and modify its value until the response is reasonable.




Figure 1. Indirectly Driving Heavy Capacitive Load

An improvement circuit is shown in Figure 2. It provides DC accuracy as well as AC stability.  $R_F$  provides the DC accuracy by connecting the inverting signal with the output,  $C_F$  and  $R_{\rm ISO}$  serve to counteract the loss of phase margin by feeding the high frequency component of the output signal back to the amplifier's inverting input, thereby preserving phase margin in the overall feedback loop.




Figure 2. Indirectly Driving Heavy Capacitive Load with DC Accuracy



For noninverting configuration, there are two others ways to increase the phase margin: (a) by increasing the amplifier's gain or (b) by placing a capacitor in parallel with the feedback resistor to counteract the parasitic capacitance associated with inverting node, as shown in Figure 3.




Figure 3. Adding a Feedback Capacitor in the Noninverting Configuration

#### Power-Supply Bypassing and Layout

The COS8091/2/4 operates from a single +2.5V to +5.5V supply or dual  $\pm 1.25$ V to  $\pm 2.25$ V supplies. For single-supply operation, bypass the power supply +Vs with a  $0.1\mu$ F ceramic capacitor which should be placed close to the +Vs pin. For dual-supply operation, both the +Vs and the -Vs supplies should be bypassed to ground with separate  $0.1\mu$ F ceramic capacitors.  $2.2\mu$ F tantalum capacitor can be added for better performance.

The length of the current path is directly proportional to the magnitude of parasitic inductances and thus the high frequency impedance of the path. High speed currents in an inductive ground return create an unwanted voltage noise. Broad ground plane areas will reduce the parasitic inductance. Thus a ground plane layer is important for high speed circuit design.

#### **Typical Application Circuits**

#### **Differential Amplifier**

The circuit shown in Figure 4 performs the differential function. If the resistors ratios are equal  $(R_4 / R_3 = R_2 / R_1)$ , then  $V_{OUT} = (V_{IP} - V_{IN}) \times R_2 / R_1 + V_{REF}$ .






Figure 4. Differential Amplifier

#### **Low Pass Active Filter**

When receiving low-level signals, limiting the bandwidth of the incoming signals into the system is often required. The simplest way to establish this limited bandwidth is to place an RC filter at the noninverting terminal of the amplifier. If even more attenuation is needed, a multiple pole filter is required. The Sallen-Key filter can be used for this task, as Figure 5. For best results, the amplifier should have a bandwidth that is 8 to 10 times the filter frequency bandwidth. Failure to follow this guideline can result in reduction of phase margin. The large values of feedback resistors can couple with parasitic capacitance and cause undesired effects such as ringing or oscillation in high-speed amplifiers. Keep resistors value as low as possible and consistent with output loading consideration.





Figure 5. Two-Pole Low-Pass Sallen-Key Active Filter




# 5. Package Information

# **5.1 SOT23-5 (Package Outline Dimensions)**



Symbol		nsions imeters	Dimensions In Inches	
	Min	Max	Min	Max
Α	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.400	0.012	0.016
С	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
е	0.950TYP		0.03	7TYP
e1	1.800	2.000	0.071	0.079
L	0.700REF 0.02		0.028	BREF
L1	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°


# 5.2 SOP8 (Package Outline Dimensions)



Symbol		nsions meters	Dimensions In Inches	
	Min	Max	Min	Max
Α	1.350	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	0.053	0.061
В	0.330	0.510	0.013	0.020
С	0.190	0.250	0.007	0.010
D	4.780	5.000	0.188	0.197
E	3.800	4.000	0.150	0.157
E1	5.800	6.300	0.228	0.248
е	1.270TYP		0.050	TYP
L	0.400	1.270	0.016	0.050
θ	0°	8°	0°	8°





# 5.3 MSOP8 (Package Outline Dimensions)



Symbol		nsions meters	Dimensions In Inches	
	Min	Max	Min	Max
Α	0.800	1.200	0.031	0.047
A1	0.000	0.200	0.000	0.008
A2	0.760	0.970	0.030	0.038
b	0.30 TYP		0.012 TYP	
С	0.15	TYP	0.006 TYP	
D	2.900	3.100	0.114	0.122
е	0.65	TYP	0.026	TYP
E	2.900	3.100	0.114	0.122
E1	4.700	5.100	0.185	0.201
L	0.410	0.650	0.016	0.026
θ	0°	6°	0°	6°

# 5.4 SOP14 (Package Outline Dimensions)






Symbol	Dimensions In Millimeters			
•	MIN	NOM	MAX	
Α	1.35	1.60	1.75	
A1	0.10	0.15	0.25	
A2	1.25	1.45	1.65	
A3	0.55	0.65	0.75	
b	0.36		0.49	
b1	0.35	0.40	0.45	
С	0.16		0.25	
c1	0.15	0.20	0.25	
D	8.53	8.63	8.73	
E	5.80	6.00	6.20	
E1	3.80	3.90	4.00	
е		1.27 BS0	0	
L	0.45	0.60	0.80	
L1		1.04 REI	F	
L2		0.25 BS0	0	
R	0.07			
R1	0.07			
h	0.30	0.40	0.50	
θ	0°		8°	
θ1	6°	8°	10°	
θ2	6°	8°	10°	
θ3	5°	7°	9°	
θ4	5°	7°	9°	



# 5.5 TSSOP14 (Package Outline Dimensions)



Symbol	I	imensio Millime	
	MIN	NOM	MAX
Α	_	_	1.20
A1	0.05	_	0.15
A2	0.90	1.00	1.05
A3	0.34	0.44	0.54
b	0.20	_	0.28
b1	0.20	0.22	0.24
С	0.10	_	0.19
c1	0.10	0.13	0.15
D	4.86	4.96	5.06
Е	6.20	6.40	6.60
E1	4.30	4.40	4.50
е		0.65 BSC	
L	0.45	0.60	0.75
L1		1.00 REF	•
L2		0.25 BSC	
R	0.09	_	_
R1	0.09	_	_
S	0.20	_	_
θ1	0°	_	8°
θ2	10°	12°	14°
θ3	10°	12°	14°

# 6. Related Parts

Part Number	Description
COS6041/2/4	24kHz, 0.5μA, RRIO Op Amps, 1.8 to 5.5V Supply
COS1347/2347/4347	350kHz, 15μA, RRIO Op Amps, 1.8 to 5.5V Supply
COS6001/2/4	1.5MHz, 50µA, RRIO Op Amps, 1.8 to 5.5V Supply
COS1314/2314/4314	3MHz, 150μA, RRIO Op Amps, 1.8 to 5.5V Supply
COS821/2/4	5MHz, 300μA, RRIO Op Amps, 1.8 to 5.5V Supply
COS1374/2374/4374	7MHz, 500μA, RRIO Op Amps, 1.8 to 5.5V Supply
COS721/2/4	10MHz, 650μA, RRIO Op Amps, 2.1 to 5.5V Supply
COS1333/2333/4333	0.35MHz, 18μA, RRIO Op Amps, 1.8 to 5.5V Supply, Zero Drift, Vos<20μV
COS8551/2/4	1.5MHz, 55μA, RRIO Op Amps, 1.8 to 5.5V Supply, Zero Drift, Vos<10μV