

40V P-Channel Trench MOSFET(Preliminary)

General Description

- Trench Power technology
- Low R_{DS(ON)}
- Simple driver requirement
- Optimized for fast-switching applications

Applications

- Synchronous Rectification in DC/DC and AC/DC Converters
- Isolated DC/DC Converters in Telecom and Industrial

Product Summary

 V_{DS} -40V

 I_D (at V_{GS} =-10V)


 $R_{DS(ON)}$ (at V_{GS} =-10V) < 14m Ω


 $R_{DS(ON)}$ (at V_{GS} =-4.5V) < 20m Ω

100% UIS Tested



-50A





Part Number	Package Type	Form	Marking	
TTD50P04AT	TO-252	Tape & Reel	TTD50P04AT	

Absolute Maximum Ratings (T_A =25°C unless otherwise noted)

Parameter		Symbol	Maximum	Units
Drain-Source Voltage		V _{DS}	-40	V
Gate-Source Voltage		V _{GS}	±20	V
Continuous Drain Current B	T _C =25°C	- I _D	-46	Δ.
Continuous Drain Current B	T _C =100°C		-38	Α
Pulsed Drain Current A		I _{DM}	-150	А
Avalanche Current ^A		I _{AS}	-36	А
Single Pulse Avalanche Energy L =0.3mH ^A		E _{AS}	194.4	mJ
Dower Discipation C	T _C =25°C	P _D	75	W
Power Dissipation ^C	T _C =100°C		37.5	W
Junction and Storage Temperature Range		T_J , T_{STG}	-55 to 175	°C
Thermal Characteristics				

Thermal Characteristics

Parameter		Symbol	Maximum	Units
Maximum Junction-to-Case	Steady-State	$R_{\Theta JC}$	2	00.004
Maximum Junction-to-Ambient	Steady-State	$R_{\Theta JA}$	100	°C/W



Electric	al Characteristics(T _J =25°C ur	nless otherwise r	noted)				
Comple of	Devenuetes	Conditions		Value			11.24
Symbol	Parameter			Min	Тур	Max	Units
STATIC PA	ARAMETERS						
BV_{DSS}	Drain-Source Breakdown Voltage	$I_D = -250 \mu A, V_{GS} = 0 V$		-40			V
	7 0 1 1/1 1 2 1 0 1	T _J =25				-1	
I _{DSS}	Zero Gate Voltage Drain Current	V_{DS} =-40V, V_{GS} =0V T	T _J =125°C			-100	μΑ
I _{GSS}	Gate-Body Leakage Current	$V_{DS} = 0V, V_{GS} = \pm 20V$	I			±100	nA
$V_{GS(th)}$	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =-250μA		-1	-1.6	-2.4	V
		V _{GS} =-10V, I _D =-30A			11	14	mΩ
R _{DS(ON)}	Static Drain-Source On-Resistance	$V_{GS} = -4.5V, I_D = -30A$			15	20	mΩ
g _{FS}	Forward Transconductance	V _{DS} =-5V, I _D =-20A			48		S
V _{SD}	Diode Forward Voltage	I _S =-30A, V _{GS} =0V				-1	V
I _S	Maximum Body-Diode Continuous Curre	nt ^B				-46	Α
DYNAMIC	PARAMETERS				!		
C _{iss}	Input Capacitance	$V_{GS} = 0V, V_{DS} = -20V, f = 1MH_Z$			3098		pF
C _{oss}	Output Capacitance				320		
C _{rss}	Reverse Transfer Capacitance				261		
R_g	Gate Resistance	f =1MH _Z			6.5		Ω
SWITCHIN	IG PARAMETERS	•					
Q _g (-10V)	Total Gate Charge	V _{GS} =-10V,V _{DS} =-20V, I _D =-20A			60		
Q _g (-4.5V)	Total Gate Charge				32		nC
Q_{gs}	Gate Source Charge				10		
Q_{gd}	Gate Drain Charge				15		
t _{D(on)}	Turn-On Delay Time	V_{GS} =-10V, V_{DS} =-20V, I_{D} =-20A, R_{G} =3 Ω			28		ns
t _r	Turn-On Rise Time				11		
t _{D(off)}	Turn-Off Delay Time				54		
t _f	Turn-Off Fall Time				13		
t _{rr}	Body Diode Reverse Recovery Time	1 - 200 d:/d+ -4000/			23		ns
Q _{rr}	Body Diode Reverse Recovery Charge	-I _F =-20A, di/dt =100A/μs			26		nC

- A. Single pulse width limited by maximum junction temperature.
- B. The maximum current rating is package limited.
- C. The power dissipation P_D is based on $T_{J(MAX)}$ =175°C, using junction-to-case thermal resistance, and is more useful in setting the upper dissipation limit for cases where additional heatsinking is used.

TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS




Figure 1: On-Region Characteristics




Figure 2: Transfer Characteristics




Figure 3: On-Resistance vs. Drain Current




Figure 4: Capacitance Characteristics




Figure 5: Gate Charge Characteristics




Figure 6: Body Diode Forward Voltage



TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS




Figure A: Gate Charge Test Circuit and Waveform




Figure B: Resistive Switching Test Circuit and Waveform







Figure C: Unclamped Inductive Switching Test Circuit and Waveform







TO-252(M)








COMMON DIMENSIONS (UNITS OF MEASURE =MILLIMETER)






SYMBOL	MIN	NOM	MAX
Α	2,20	2,30	2,38
A1	0	_	0.10
A2	0.90	1.01	1.10
b	0,72	_	0.85
b1	0,71	0.76	0.81
b2	0,72	_	0,90
b3	5.13	5.33	5.46
С	0.47	_	0.60
c1	0,46	0.51	0.56
c2	0,47	_	0,60
D	6,00	6,10	6,20
D1	5,25	_	_
Е	6.50	6.60	6.70
E1	4.70	_	_
e	2.186	2,286	2,386
Н	9,80	10.10	10.40
L	1,40	1,50	1,70
L1	2	,90 REF	
L2	0	.508 BSC	
L3	0.90	_	1,25
L4	0,60	0.80	1.00
L5	0,15	_	0,75
L6	1.80 REF		
θ	0°	_	8°
θ1	5°	7°	9°
02	5°	7°	9°



TO-252 (I)



SYMBOL	MIN	NOM	MAX	
A	2,20	2,30	2,38	
A1	0	_	0,10	
A2	0,90	1,01	1,10	
b	0.72	_	0.85	
b1	0.71	0.76	0.81	
b2	0.72	_	0.90	
b3	5.13	5.33	5.46	
c	0.47	_	0.60	
c1	0,46	0.51	0,56	
c2	0.47	_	0,60	
D	6,00	6,10	6,20	
D1	5,25	_	_	
E	6.50	6.60	6.70	
E1	4.70	_	_	
e	2.186	2.286	2.386	
Н	9.80	10.10	10.40	
L	1,40	1,50	1,70	
L1	2	2,90 REF		
L2	0,508 BSC			
L3	0,90	_	1,25	
L4	0,60	0,80	1,00	
L5	0.15	<u> </u>	0.75	
L6	1.80 REF			
0	0°	<u> </u>	8°	
θ1	5°	7°	9°	
92	5°	7°	9°	



Disclaimer

All product specifications and data are subject to change without notice.

For documents and material available from this datasheet, Wuxi Unigroup does not warrant or assume any legal liability or responsibility for the accuracy, completeness of any product or technology disclosed hereunder.

No license, express or implied, by estoppels or otherwise, to any intellectual property rights is granted by this document or by any conduct of Wuxi Unigroup.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling Wuxi Unigroup products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Wuxi Unigroup for any damages arising or resulting from such use or sale.

Wuxi Unigroup disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Wuxi Unigroup's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

Wuxi Unigroup Microelectronics CO., LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

In the event that any or all Wuxi Unigroup products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

Information (including circuit diagrams and circuit parameters) herein is for example only. It is not guaranteed for volume production. Wuxi Unigroup believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.