

Dual P-Ch 20V Fast Switching MOSFETs
Description


The HSW6811 is the high cell density trenched P-ch MOSFETs, which provides excellent RDSON and efficiency for most of the small power switching and load switch applications.

The HSW6811 meet the RoHS and Green Product requirement with full function reliability approved.

- Green Device Available
- Super Low Gate Charge
- Excellent CdV/dt effect decline
- Advanced high cell density Trench technology

Product Summary

V _{DS}	-20	V
R _{DS(ON),typ}	115	mΩ
I _D	-2	A

SOT23-6L Pin Configuration

Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V _{DS}	Drain-Source Voltage	-20	V
V _{GS}	Gate-Source Voltage	±12	V
I _D @T _A =25°C	Continuous Drain Current, V _{GS} @ -4.5V ₁	-2	A
I _D @T _A =70°C	Continuous Drain Current, V _{GS} @ -4.5V ₁	-1.4	A
I _{DM}	Pulsed Drain Current ₂	-8	A
P _D @T _A =25°C	Total Power Dissipation ₃	1	W
T _{STG}	Storage Temperature Range	-55 to 150	°C
T _J	Operating Junction Temperature Range	-55 to 150	°C

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
R _{θJA}	Thermal Resistance Junction-ambient ₁	---	125	°C/W
R _{θJC}	Thermal Resistance Junction-Case ₁	---	80	°C/W

Dual P-Ch 20V Fast Switching MOSFETs
Electrical Characteristics (T_J=25 °C, unless otherwise noted)







Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V , I _D =-250μA	-20	---	---	V
R _{DSON}	Static Drain-Source On-Resistance ₂	V _{GS} =-4.5V , I _D =-2A	---	115	130	mΩ
		V _{GS} =-2.5V , I _D =-1A	---	150	180	
V _{GS(th)}	Gate Threshold Voltage	V _{GS} =V _{DS} , I _D =-250μA	-0.5	-0.65	-1.0	V
I _{bss}	Drain-Source Leakage Current	V _{DS} =-16V , V _{GS} =0V , T _J =25°C	---	---	-1	uA
		V _{DS} =-16V , V _{GS} =0V , T _J =55°C	---	---	-5	
I _{GS}	Gate-Source Leakage Current	V _{GS} =±12V , V _{DS} =0V	---	---	±100	nA
g _{fS}	Forward Transconductance	V _{DS} =-5V , I _D =-1A	---	5	---	S
Q _g	Total Gate Charge (-4.5V)	V _{DS} =-10V , V _{GS} =-4.5V , I _D =-2A	---	4.3	---	nC
Q _{gs}	Gate-Source Charge		---	0.8	---	
Q _{gd}	Gate-Drain Charge		---	1	---	
T _{d(on)}	Turn-On Delay Time	V _{DD} =-10V , V _{GS} =-4.5V , R _G =1Ω I _D =-2A	---	12	---	ns
T _r	Rise Time		---	20	---	
T _{d(off)}	Turn-Off Delay Time		---	24	---	
T _f	Fall Time		---	9	---	
C _{iss}	Input Capacitance	V _{DS} =-10V , V _{GS} =0V , f=1MHz	---	280	---	pF
C _{oss}	Output Capacitance		---	54	---	
C _{rss}	Reverse Transfer Capacitance		---	44	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I _s	Continuous Source Current _{1,4}	V _G =V _D =0V , Force Current	---	---	-2	A
V _{SD}	Diode Forward Voltage ₂	V _{GS} =0V , I _s =-1A , T _J =25°C	---	---	-1.2	V

Note :

- 1.The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.
- 2.The data tested by pulsed , pulse width ≤ 300us , duty cycle ≤ 2%
- 3.The power dissipation is limited by 150°C junction temperature
- 4.The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation.

Typical Characteristics

Fig.1 Typical Output Characteristics

Fig.2 On-Resistance vs. G-S Voltage

Fig.3 Source Drain Forward Characteristics

Fig.4 Gate-Charge Characteristics

Fig.5 Normalized $V_{GS(th)}$ vs. T_J

Fig.6 Normalized $R_{DS(on)}$ vs. T_J



HUASHUO
SEMICONDUCTOR

HSW6811

Dual P-Ch 20V Fast Switching MOSFETs




Fig.7 Capacitance




Fig.8 Safe Operating Area




Fig.9 Normalized Maximum Transient Thermal Impedance




Fig.10 Switching Time Waveform





Fig.11 Gate Charge Waveform



SOT23-6L Package Outline Dimensions



SYMBOLS	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
D	2.692	3.099	0.106	0.122
E	2.591	3.000	0.102	0.118
E1	1.397	1.803	0.055	0.071
e	0.950 REF.		0.037 REF.	
e1	1.900 REF.		0.075 REF.	
b	0.300	0.500	0.012	0.020
C	0.080	0.200	0.003	0.008
A	0.000	0.100	0.000	0.004
A1	0.700	1.200	0.028	0.048
L	0.300	0.600	0.012	0.024
L1	0.600 REF.		0.023 REF.	
θ	0°	9°	0°	9°