




承认书

SPECIFICATION FOR APPROVAL

CUSTOMER:			
CUSTOMER P/N:			
Cybermax P/N:	CMLH0704S102MTT		
DRAWN NO. :	CM191024001		
DATE:	19.10.24	REVISION NO.	A

Signature:

APPROVED BY	CHECKED BY	DRAWN BY
		

DATE	Chang Item
2019-10-24	新制定

CUSTOMER:		PAGE:	1/5
CUSTOMER P/N:		REVISION:	
Cybermax P/N:	CMLH0704S102MTT	DATE:	19.10.24
DRAWN NO.:	CM191024001		

SHAPE & DIMENSION (UNIT:mm)

ELECTRICAL SCHEMATIC:

ELECTRICAL SPECIFICATION

MEAS. ITEM	SPEC.				TEST FREQ.	CONDITIONS
L	1.0	mH	±	20%	100KHz/0.25V	Ta=25°C , Idc=0A
DCR	5.5	Ω	Max.			Ta=25°C
IDC	180	mA	Max.		100KHz/0.25V	ΔL/L ≤ 35%

GENERAL SPECIFICATION

Electrical specifications :	at 25°C
Operation Temperature :	-40~+125°C
Storage Temperature :	-40~+125°C


WIRE: $\Phi 0.10 \times 152TS$

CUSTOMER:		PAGE:	2/5
CUSTOMER P/N:		REVISION:	
Cybermax P/N:	CMLH0704S102MTT	DATE:	19.10.24
DRAWN NO.:	CM191024001		

ITEM	L	IDC	DCR	A1	A2	B
SPEC	1000uH±20%	180mA MAX (≥LOA*0.65)	5.5 Ω Max	7.3±0.2 MM	7.3±0.2 MM	4.5 MAX
1	989.8	OK	4.56	7.22	7.21	4.30
2	1003.0	OK	4.58	7.19	7.18	4.28
3	996.3	OK	4.52	7.22	7.22	4.26
4	994.9	OK	4.54	7.25	7.24	4.28
5	1003.1	OK	4.43	7.24	7.23	4.30
6	997.8	OK	4.58			
7	995.8	OK	4.53			
8	997.7	OK	4.62			
9	993.0	OK	4.53			
10	992.9	OK	4.52			
R	996.43		4.54	7.224	7.216	4.284
X	13.3		0.19	0.06	0.06	0.04
Judge	OK	OK	OK	OK	OK	OK
APPROVE BY		CHECKD BY		TESTEER BY		
Derek		Lewis		Dave		


CUSTOMER:		PAGE:	3/5
CUSTOMER P/N:		REVISION:	
Cybermax P/N:	CMLH0704S102MTT	DATE:	19.10.24
DRAWN NO.:	CM191024001		

REFLOW-PROFILE



CUSTOMER:		PAGE:	4/5
CUSTOMER P/N:		REVISION:	
Cybermax P/N:	CMLH0704S102MTT	DATE:	19.10.24
DRAWN NO.:	CM191024001		



B.O.M



No.	Part name	Material
①	Drum Core	Ni-Zn Ferrite Core
②	Wire	Polyurethane enameled copper wire
③	Ring Core	Ni-Zn Ferrite Core
④	Adhesive	Epoxy Resin
⑤	Electrode	Cu + Sn plating

CUSTOMER:		PAGE:	5/5
CUSTOMER P/N:		REVISION:	
Cybermax P/N:	CMLH0704S102MTT	DATE:	19.10.24
DRAWN NO.:	CM191024001		

PACKAGING



Dimensions of reel (mm)				Packing Unit
A	B	C	W	Φ330mm
330	100	13	16	1000pcs/reel

