

### Features

- For use in low voltage, high frequency inverters
- Free wheeling, and polarity protection applications


### Mechanical data

- **Case:** JEDEC SOD-323 molded plastic body
- **Terminals:** Solder plated, solderable per MIL-STD-750, Method 2026
- **Polarity:** Color band denotes cathode end
- **Mounting Position:** Any

### Marking : SL



### Package outline




### Maximum ratings and Electrical Characteristics (AT $T_A=25^\circ\text{C}$ unless otherwise noted)

PARAMETER	SYMBOLS	B5817WS	B5818WS	B5819WS	UNITS
Peak repetitive peak reverse voltage	$V_{RRM}$				
Working peak	$V_{RWM}$	20	30	40	V
DC Blocking voltage	$V_R$				
RMS Reverse voltage	$V_{R(RMS)}$	14	21	28	V
Average rectified output current	$I_o$		1		A
Peak forward surge current @=8.3ms	$I_{FSM}$		9		A
Power dissipation	$P_d$		250		mW
Thermal resistance junction to ambient	$R_{\theta JA}$		500		K/W
Operating junction temperature range	$T_J$		-55 to +150		$^\circ\text{C}$
Storage temperature	$T_{STG}$		-55 to +150		
Non-Repetitive peak reverse voltage	$V_{RM}$	20	30	40	V


PARAMETER	SYMBOLS	Min.	Max.	Unit	Test conditions
Reverse breakdown voltage	$V_{(BR)}$	20		V	$I_R=1\text{mA}$ B5817WS B5818WS B5819WS
		30		V	
		40		V	
Reverse voltage leakage current	$I_R$		1	mA	$V_R=20\text{V}$ B5817WS
					$V_R=30\text{V}$ B5818WS
					$V_R=40\text{V}$ B5819WS
Forward voltage	$V_F$		0.45 0.75	V	$I_F=1\text{A}$ $I_F=3\text{A}$ B5817WS B5818WS B5819WS
			0.55 0.875		
			0.6 0.9		
Diode capacitance	$C_D$		120	pF	$V_R=4\text{V}, f=1.0\text{MHz}$

**Rating and characteristic curves**


**FIG. 1- FORWARD CURRENT DERATING CURVE**




**FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT**




**FIG. 3- TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS**



**FIG. 4- TYPICAL REVERSE CHARACTERISTICS**



**FIG. 5- TYPICAL JUNCTION CAPACITANCE**



**FIG. 6-TYPICAL TRANSIENT THERMAL IMPEDANCE**

