


# ME-CA Series

Low Impedance

Small




- 105°C 1,000 to 3,000hours
- Solvent proof (within 5 minutes)



## Specifications

Items	Condition	Specifications						
Rated voltage (V)	—	6.3	10	16	25	35	50	
Surge voltage (V)	Room temperature	8.0	13	20	32	44	63	
Category temperature range (°C)	—	-55 to +105						
Capacitance tolerance (%)	120Hz/20°C	M : ±20						
Dissipation Factor (tan δ)	tanδ(max.) 120Hz/20°C	0.28	0.24	0.20	0.16	0.14	0.12	
Leakage current (LC)	μA/after 2minutes (max.)	Exceeding 1,000μF, +0.02 every 1,000μF						
Impedance ratio at low temperature	Based on the value at 120Hz, +20°C	-40°C / Z/Z <sub>20°C</sub>	3	3	2	2	2	2
		-55°C / Z/Z <sub>20°C</sub>	6	5	4	4	3	3
Endurance	105°C rated voltage applied (With the rated ripple current)	Test	φ5 to φ8 : 1,000hours, φ10 : 2,000hours, φ12.5 to φ16 : 3,000hours					
		ΔC/C	Within ±25% of the initial value					
		tanδ	Less than 200% of the specified value					
		LC	Less than the specified value					

## Dimensions



$$\alpha : L < 20 \quad \alpha = 1.5, L \geq 20 \quad \alpha = 2.0$$

A pressure relief vent is provided for φD=6.3 or bigger

(Unit : mm)

φD	5	6.3	8	10	12.5	16
F	2.0	2.5	3.5	5.0	5.0	7.5
φd	0.5	0.5	0.6	0.6	0.6	0.8

## Size, Impedance, Rated Ripple Current


Case size φD×L (mm)	Items	6.3			10		
		Capacitance (μF)	Impedance (Ωmax.) (20°C/100kHz)	Rated ripple current (mA rms) (105°C/10k to 200kHz)	Capacitance (μF)	Impedance (Ωmax.) (20°C/100kHz)	Rated ripple current (mA rms) (105°C/10k to 200kHz)
5×11		220	0.50	180			
6.3×11		330	0.30	280	220	0.30	280
6.3×11		470	0.24	280	330	0.24	280
8×11.5		1000	0.15	560	470	0.16	410
10×12.5					1000	0.086	710
10×16		2200	0.066	950			
10×20		3300	0.047	1150	2200	0.047	1150
12.5×20		4700	0.042	1460	3300	0.042	1460
12.5×25		6800	0.031	1780	4700	0.031	1780
16×25		10000	0.026	2000	6800	0.026	2000
16×31.5					10000	0.022	2200
16×35.5		15000	0.022	2200			

**Size, Impedance, Rated Ripple Current**

Case size φD×L (mm)	Items	16			25		
		Capacitance (μF)	Impedance (Ωmax.) (20°C/100kHz)	Rated ripple current (mA rms) (105°C/10k to 200kHz)	Capacitance (μF)	Impedance (Ωmax.) (20°C/100kHz)	Rated ripple current (mA rms) (105°C/10k to 200kHz)
5×11		100	0.50	180			
6.3×11		220	0.24	280	100	0.30	280
8×11.5		330	0.16	410	220	0.16	410
8×11.5		470	0.15	560	330	0.15	560
10×12.5					470	0.086	710
10×16		1000	0.066	950			
10×20					1000	0.047	1150
12.5×20		2200	0.042	1460			
12.5×25		3300	0.035	1780	2200	0.035	1780
16×25		4700	0.026	2000	3300	0.026	2000
16×31.5		6800	0.022	2200	4700	0.022	2200

Case size φD×L (mm)	Items	35			50		
		Capacitance (μF)	Impedance (Ωmax.) (20°C/100kHz)	Rated ripple current (mA rms) (105°C/10k to 200kHz)	Capacitance (μF)	Impedance (Ωmax.) (20°C/100kHz)	Rated ripple current (mA rms) (105°C/10k to 200kHz)
5×11					2.2	3.0	45
5×11					3.3	2.7	55
5×11					4.7	2.0	90
5×11					10	1.7	110
5×11		33	0.72	180	22	1.2	120
5×11		47	0.50	180	33	0.95	130
6.3×11		100	0.24	280	47	0.56	190
8×11.5		220	0.15	560	100	0.30	320
10×12.5		330	0.086	710	220	0.16	520
10×16		470	0.066	950	330	0.12	670
10×20					470	0.088	820
12.5×20		1000	0.042	1460			
12.5×25					1000	0.053	1200
16×25		2200	0.026	2000			
16×31.5					2200	0.029	1750
16×35.5		3300	0.022	2200			

Please refer to page 14 for ripple current frequency coefficients.

**Part number**

 Radial Lead Type  
 Aluminum Electrolytic Capacitors

- ME-SWB
- ME-UZ-SZ
- ME-UAX-SAX
- ME-SWG
- ME-HC
- ME-LS
- ME-CZ
- ME-CA**
- ME-CX
- ME-AX
- ME-WX
- ME-WA
- ME-WL
- ME-WG
- ME-FX
- ME-PX
- ME-HPC-HPD
- ME-FC-FD
- ME-FH
- ME-SWN
- ME-HWN