Ceramic Low Pass Filter

500

DC⁽¹⁾ to 95 MHz

Maximum Ratings


Operating Temperature	-55°C to 100°C			
Storage Temperature	-55°C to 100°C			
RF Power Input*	8.5W max. at 25°C			

* Passband rating, derate linearly to 3.5W at 100°C ambient Permanent damage may occur if any of these limits are exceeded.

Pin Connections

RF IN	1
RF OUT	3
GROUND	2.4


Outline Drawing



Outline Dimensions (inch)

	G	F	E	D	С	В	Α
)	.169	.009	.032	.020	.037	.063	.126
)	4.29	0.23	0.81	0.51	0.94	1.60	3.20
o wt	Р	Ν	М	L	к	J	н
o wt I grams	P .071		M .087	L .024	K .122	J .024	H .087
l grams	P .071 1.80	.012		.024	.122	.024	

Demo Board MCL P/N: TB-270 Suggested PCB Layout (PL-137)



Features

- excellent power handling, 8.5W
- small size
- 7 sections
- temperature stable
- LTCC construction
- protected by U.S. Patent 6,943,646

Applications

- harmonic rejection
- VHF/UHF transmitters/receivers






Generic photo used for illustration purposes only CASE STYLE: FV1206

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




Electrical Specifications ^(1,2) at 25°C							
Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Insertion Loss	DC-F1	DC-95	_	_	1.0	dB
Pass Band	Freq. Cut-Off	F2	165	—	3.0	—	dB
	VSWR	DC-F1	DC-95	—	1.2	—	:1
		F3	240	20	—	—	dB
Stop Band	Rejection Loss	F4-F5	255-1600	—	40	—	dB
		F6	4500	—	20	—	dB
	VSWB	E3-E6	240-4500		20		·1

(1) In Application where DC voltage is present at either input or output ports, coupling capacitors are required. (2) Measured on Mini-Circuits Characterization Test Board TB-270.




Electrical Schematic



Typical Performance Data at 25°C

71					
Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)			
10.00 95.00	0.30 0.83	1.06 1.07			
165.00	2.56	1.79			
180.00	4.08	2.58			
220.00	17.29	8.75			
240.00	30.37	11.55			
250.00	36.66	12.43			
410.00	55.58	23.11			
700.00	53.60	50.04			
1235.00	44.98	76.58			
1600.00	39.94	68.40			
2000.00	33.54	63.70			
2500.00	27.39	48.12			
4500.00	20.96	24.63			
5000.00	19.57	21.89			





Notes
A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please wish Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

REV. K M158161 LFCN-95+ ED11960/3 RVN/AD/CF 160920

