Low Pass Filter

DC⁽¹⁾ to 400 MHz 50Ω

LFCN-400+



Generic photo used for illustration purposes only

CASE STYLE: FV1206

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site

Available Tape and Reel at no extra cost

for RoHS Compliance methodologies and qualifications



Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	8.5W max. at 25°C


* Passband rating, derate linearly to 3.5W at 100°C ambient Permanent damage may occur if any of these limits are exceeded


Pin Connections

RF IN	1
RF OUT	3
GROUND	2,4

Product Marking: JY

Outline Drawing






Outline Dimensions (inch)

	G	F	E	D	С	В	Α
	.169	.009	.032	.020	.037	.063	.126
	4.29	0.23	0.81	0.51	0.94	1.60	3.20
wt	Р	N	M	L	K	J	Н
grams	.071	.012	.087	.024	.122	.024	.087
.020	1.80	0.30	2.21	0.61	3.10	0.61	2.21

Demo Board MCL P/N: TB-270 Suggested PCB Layout (PL-137)



COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH THICKNESS .020" ± .0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE. DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Features

- · excellent power handling, 8.5W
- small size
- 7 sections
- temperature stable
- LTCC construction
- protected by U.S. Patent 6,943,646


Applications

- harmonic rejection
- VHF/UHF transmitters/receivers


Electrical Specifications(1,2) at 25°C

Pa	rameter	F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Insertion Loss	DC-F1	DC-400	_	_	1.0	dB
Pass Band	Freq. Cut-Off	F2	560	_	3.0	_	dB
	VSWR	DC-F1	DC-400	_	1.2	_	:1
		F3	660	20	_	_	dB
Stop Band	Rejection Loss	F4-F5	680-3000	_	40	_	dB
Stop Ballu		F6	5500	_	20	_	dB
	VSWR	F3-F6	660-5500	_	20	_	:1

(1) In Applications where DC isolation to ground is required, coupling capacitors are recommended to avoid DC leakage. Alternatively, if DC pass IN-OUT is required, Mini-Circuits' "D" suffix version of this model will support DC IN-OUT, and provide>100 MOhm isolation to ground. (2) Measured on Mini-Circuits Characterization Test Board TB-270.




Electrical Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
1.00	0.06	1.02
100.00	0.25	1.10
400.00	0.76	1.11
560.00	2.71	1.97
680.00	35.71	14.74
700.00	45.62	17.22
800.00	42.97	25.19
1000.00	42.26	40.41
1550.00	55.94	75.53
1770.00	71.17	66.82
2500.00	51.63	72.39
3000.00	50.38	57.91
3500.00	43.35	56.04
4340.00	18.96	14.62
5500.00	26.38	28.03





A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms_isp