

Document No.	
Released Date	2020/8/17
Page No.	1/10

Metal Film Anti-Surge Low-Resistance Chip Resistor — TGL Series



Top view

Application

- Consumer electronics
- Computer & relative products
- Communication devices
- Measuring instrument
- Industrial / Power supply
- Battery management system




Bottom view

Features

- Low Resistance / TCR / Inductance(≤5nH)
- Excellent long-term stability
- High precision current sensing
- High rated power capability and excellent Anti-Surge
- Halogen free and lead free
- RoHs compliant

Parts Number Explanation

Example:






Document No.	S-10-12-35-08
Released Date	2020/8/17
Page No.	2/10

Standard Electrical Specifications

Туре	Rated Power at 70°C	Max. Rated Current	Max. Overload Current	T.C.R. (ppm/°C)	Resistance Range D(0.5%), F(1.0%), G(2.0%), J(5.0%)
TGL1206	1W	4.47A	10.00A	±100	$50 \text{ m}\Omega \leq R < 100 \text{ m}\Omega$
TGL1210	1VV	4.47A	10.00A	±50	$100 \text{ m}\Omega \leq \text{R} \leq 33 \Omega$
TGL2010	1.5W	5.48A	12.25A		
TOL 2542	2W	6.32A	14.14A	±50	$50~\text{m}\Omega~\leq~R~\leq~50~\Omega$
TGL2512	3.5W(U)	8.37A	18.71A		

- For non-standard parts, please contact our sales dept.
- Operating Temperature Range : -55° C $\sim +170^{\circ}$ C.


Anti-Surge Ability:






Document No.	S-10-12-35-08
Released Date	2020/8/17
Page No.	3/10

Type Dimension







Unit: mm

TYPE	L	W	Н	I 1	l 2
TGL1206	3.10±0.10	1.60±0.10	0.55±0.10	0.40±0.20	0.45±0.20
TGL1210	3.10±0.10	2.50±0.15	0.55±0.10	0.50±0.20	0.50±0.20
TGL2010	5.00±0.20	2.50±0.15	0.55±0.10	0.60±0.25	0.60±0.25
TGL2512	6.30±0.20	3.20±0.20	0.55±0.10	0.65±0.25	0.65±0.25
TGL2512(U)	6.30±0.20	3.20±0.20	0.70±0.15	0.65±0.25	0.65±0.25

Construction





1	Alumina Substrate	7	Bottom Protective Overcoat
2	Top Resistive Layer	8	Marking
3	Bottom Resistive Layer	9	Side Inner Electrode
4	Top Inner Electrode (Cu)	10	Barrier Layer (Ni)
5	Bottom Inner Electrode (Cu)	11	Solder coating (Sn)
6	Top Protective Overcoat		



Document No.	S-10-12-35-08
Released Date	2020/8/17
Page No.	4/10


Performance Characteristics

Power Derating Curve

The Operating Temperature Range: -55°C ~+170°C.

Power rating or current rating is in the case based on continuous full-load at ambient temperature of 70°C. For operation at ambient temperature in excess of 70°C, the load should be derated in accordance with figure of derating Curve.

Derating Curve



Rated Current

Resistance Range: $< 1\Omega$

Rated Current: The resistor shall have a DC continuous working current or a AC (rms) continuous working current at commercial-line frequency and wave form corresponding to the power rating, as determined formula as following:

I = Rated current (A)
$$P = Rated power (W)$$

$$R = Nominal resistance (\Omega)$$

Rated Voltage

Resistance Range: $\geq 1\Omega$

Rated Voltage: The resistor shall have a DC continuous working voltage or a RMS AC continuous working voltage at commercial-line frequency and wave form corresponding to the power rating, as determined formula as following:

$$V = \text{Rated voltage (V)}$$

$$P = \text{Rated power (W)}$$

$$R = \text{Nominal resistance } (\Omega)$$



Document No.	S-10-12-35-08
Released Date	2020/8/17
Page No.	5/10

■ Reliability Test and Requirement

Test Item	Test Method	Procedure	Requirements
Temperature Coefficient of Resistance (T.C.R)	JIS-C-5201-1 4.8 IEC-60115-1 4.8	At 25° C / +125 $^{\circ}$ C, 25° C is the reference temperature	Refer to Standard Electrical Specifications
Short Time Overload	JIS-C-5201-1 4.13 IEC-60115-1 4.13	5 times rated power whichever is less for 5 seconds.	±(1.0%+0.001Ω)
Insulation Resistance	JIS-C-5201-1 4.6 IEC-60115-1 4.6	Applied 100VDC for 1 minute.	<u>≥</u> 10GΩ
Dielectric Withstanding Voltage	JIS-C5201-1 4.7	Applied 500VAC for 1 minute.	No short or burned on the appearance.
Core Body Strength	JIS-C5201-1 4.15	Central part pressurizing force : 10N , 10 seconds	No broken
Solderability	JIS-C-5201-1 4.17 IEC-60115-1 4.17	245±5°C for 3 seconds.	>95% Coverage No Visual damage
Resistance to Soldering Heat	JIS-C-5201-1 4.18 IEC-60115-1 4.18	260±5°C for 10 seconds.	±(1.0%+0.001Ω) No Visual damage
Leaching	JIS-C-5201-1 4.18 IEC-60068-2-58 8.2.1	260±5°C for 30 seconds.	>95% Coverage No Visual damage
Rapid Change of Temperature	JIS-C-5201-1 4.19 IEC-60115-1 4.19	-55℃ to +155℃, 300 cycles	±(1.0%+0.001Ω) No Visual damage
Damp Heat with Load	JIS-C-5201-1 4.24 IEC-60115-1 4.24	40±2°C, 90~95% R.H. RCWV or Max. working current whichever is less for 1000 hrs with 1.5 hrs "ON" and 0.5 hr "OFF"	±(1.0%+0.001Ω)
Biased Humidity	MIL-STD-202 Method 103	1,000 hours; 85°C / 85% RH, 10% of operating power. Measurement at 24±4 hours after test conclusion.	±(1.0%+0.05Ω)
Load Life (Endurance)	JIS-C-5201-1 4.25 IEC-60115-1 4.25.1	70±2°C, Rated power, or Max. working current whichever is less for 1000 hrs with 1.5 hrs "ON" and 0.5 hr "OFF".	±(1.0%+0.001Ω)
High Temperature Exposure	JIS-C-5201-1 4.23.2 IEC 60068-2-2	At +170±5℃ for 1000 +48/-0 hours.	±(1.0%+0.001Ω)
Resistance to Solvent	JIS-C-5201-1 4.29	The tested resistor be immersed into isopropyl alcohol of 20~25℃ for 60 secs. Then the resistor is left in the room for 48 hrs.	±(1.0%+0.001Ω) No Visual damage
Terminal Strength (SMD)	JIS-C5201-1 4.32 AEC Q200-006	Pressurizing force for 60 seconds 1206 and above: 17.7N	No broken
Bending Strength	JIS-C-5201-1 4.33 IEC-60115-1 4.33	Bending once for 5 seconds D: 1206 \ 1210 = 3mm 2010 \ 2512 = 2mm	±(1.0%+0.001Ω) No Visual damage

- ullet Temperature Coefficient of Resistance test to 55 $\,^{\circ}\text{C}\,$ is available on request
- We can also provide AEC-Q200 test reports if required by customers.

Document No.	S-10-12-35-08
Released Date	2020/8/17
Page No.	6/10

Marking


■ TGL1206 ~ TGL2512 : 4 digit marking

First 3 digits are the significant figures, the 4th digit is the multiplier. "R"= decimal point. Examples:


Resistance value	Code	Example
50 mΩ ~ 99 mΩ	R0XX	R050 = 0.05 Ω
100 mΩ ~ 999 mΩ	RXXX	R470 = 0.47 Ω
1 Ω ~ 9.9 Ω	XRXX	4R70 = 4.7 Ω
10 Ω ~ 50 Ω	XXRX	50R0 = 50 Ω

Recommended Customer Soldering Parameters

Wave solder Temperature condition



Solder reflow Temperature condition






Document No.	
Released Date	2020/8/17
Page No.	7/10

- Rework temperature (hot air equipment): 350°C, 3~5seconds
- Recommended reflow methods

IR, vapor phase oven, hot air oven

If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.

■ Recommend Land Pattern Design



Unit: mm

TYPE	A	В	С
TGL1206	2.20	4.20	1.80
TGL1210	2.00	4.40	2.70
TGL2010	3.80	6.60	2.70
TGL2512	4.90	8.10	3.40

Plating Thickness

 $Ni: \geq \, 3 \mu m$

 $Sn(Tin): \ge 3\mu m$




Document No.	S-10-12-35-08
Released Date	2020/8/17
Page No.	8/10

Appendix For SMD Chip Resistor

Packaging Information

■ Reel Dimensions



Unit: mm


TYPE	SIZE		SIZE		SIZE		Α	ΦВ	ФС	ΦD	W	ФМ
TGL1206	7"	5K/Reel	2.0±0.5	13.5±1.0	21±1.0	60±1.0	11.5±2.0	178±2.0				
TGL1210	7"	5K/Reel	2.0±0.5	13.5±1.0	21±1.0	60±1.0	16.0±2.0	178±2.0				
TGL2010	7"	4K/Reel	2.0±0.5	13.5±1.0	21±1.0	60±1.0	16.0±2.0	178±2.0				
TGL2512	7"	4K/Reel	2.0±0.5	13.5±1.0	21±1.0	60±1.0	16.0±2.0	178±2.0				



Document No.	S-10-12-35-08
Released Date	2020/8/17
Page No.	9/10

■ Packaging Information


■ Tapping Specifications



Unit: mm

	Packaging	Type	Α	В	W	ш	F	G	Н	Т	ΦD	Р
	Paper Type	1206	1.90±0.2	3.05±0.2	8.0±0.2	1.75±0.1	3.5±0.05	4.0±0.1	2.0±0.05	0.05 0.75±0.1 4.00	4.0±0.1	
	Рарег туре	1210	2.85±0.2	3.05±0.2	8.0±0.2	1.75±0.1	3.5±0.05	4.0±0.1	2.0±0.05	0.75±0.1	1.50_0	4.0±0.1

■ Embossed Dimensions



Unit: mm


Packaging	Туре	A	В	W	Е	ш	G	Н	T	ΦD	ΦD1	T1	Р
Embossed	2010	2.80±0.2	5.60±0.2	12±0.1	1.75±0.1	5.5±0.05	4.0±0.1	2.0±0.05	0.23±0.1	1.50+0.1	1.50±0.1	0.85±0.15	4.0±0.1
Туре	2512	3.40±0.2	6.70±0.2	12±0.1	1.75±0.1	5.5±0.05	4.0±0.1	2.0±0.05	0.23±0.1		1.50±0.1	0.85±0.15	4.0±0.1




Document No.	S-10-12-35-08
Released Date	2020/8/17
Page No.	10/10

Packing Material Data / Storage Data

Front & Back Lead Dimensions




■ Top Adhesive Peel Off Strength: 10~70g




Package

Inner Box Size						
Reel	Size H(mm)					
1	13					
2	24					
3	36					
5	60					
10	113					



)					
	Contain (Kpcs)	Length (mm)	Width (mm)	Width (mm)		
	25K	180	180	60		
	50K	180	180	110 200		
	150K	430	200			
	300K	400	400	200		



Storage Data :

Storage time at the environment temp: 25±5°C& humidity: 60±20% is valid for one year from the date of delivery.