



1N4148WS / BAV16WS

SURFACE MOUNT FAST SWITCHING DIODE

Features

- Fast Switching Speed
- Small Surface Mount Package
- For General Purpose Switching Applications
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- PPAP Capable (Note 4)

Mechanical Data

- Case: SOD323
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Matte Tin Finish Annealed Over Alloy 42 Leadframe (Lead-Free Plating). Solderable per MIL-STD-202, Method 208 (3)
- Polarity: Cathode Band
- Weight: 0.006 grams (Approximate)

SOD323



Top View



Device Schematic

Ordering Information (Notes 4 & 5)

Part Number	Compliance	Case	Packaging
1N4148WS-7-F	Standard	SOD323	3,000/Tape & Reel
1N4148WSQ-7-F	Automotive	SOD323	3,000/Tape & Reel
1N4148WS-13-F	Standard	SOD323	10,000/Tape & Reel
1N4148WSQ-13-F	Automotive	SOD323	10,000/Tape & Reel
BAV16WS-7-F	Standard	SOD323	3,000/Tape & Reel

Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.

2. See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-Free.

Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
 Automotive products are AEC-Q101 qualified and are PPAP capable. Automotive, AEC-Q101 and standard products are electrically and thermally the

4. Automotive products are AEC-Q101 qualified and are PPAP capable. Automotive, AEC-Q101 and standard products are electrically and thermally the same, except where specified. For more information, please refer to http://www.diodes.com/quality/product_compliance_definitions/.

5. For packaging details, go to our website at http://www.diodes.com/products/packages.html.

Marking Information





Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit
Non-Repetitive Peak Reverse Voltage (Note 6)		V _{RM}	100	V
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage		V _{RRM} V _{RWM} V _R	75	V
RMS Reverse Voltage		V _{R(RMS)}	53	V
Forward Continuous Current		I _{FM}	300	mA
Average Rectified Output Current		lo	150	mA
Non-Repetitive Peak Forward Surge Current	@ t = 1.0µs @ t = 1.0s	IFSM	2.0 1.0	А

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Power Dissipation (Note 7)	PD	200	mW
Thermal Resistance Junction to Ambient Air (Note 7)	R _{0JA}	625	°C/W
Operating and Storage Temperature Range	T_J , T_STG	-65 to +150	°C

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Max	Unit	Test Condition
Reverse Breakdown Voltage (Note 6)	V _{(BR)R}	75		V	I _R = 1.0μA
Forward Voltage	V _{FM}	_	0.715 0.855 1.0 1.25	V	$I_{F} = 1.0mA$ $I_{F} = 10mA$ $I_{F} = 50mA$ $I_{F} = 150mA$
Peak Reverse Current (Note 6)	I _{RM}	_	1.0 50 30 25		$V_R = 75V$ $V_R = 75V, T_J = +150^{\circ}C$ $V_R = 25V, T_J = +150^{\circ}C$ $V_R = 20V$
Total Capacitance	CT	_	2.0	pF	V _R = 0, f = 1.0MHz
Reverse Recovery Time	t _{RR}	_	4.0	ns	$I_F = I_R = 10 \text{mA},$ $I_{RR} = 0.1 \text{ x } I_R, R_L = 100 \Omega$


6. Short duration pulse test used to minimize self-heating effect.7. Part mounted on FR-4 PC board with recommended pad layout, which can be found on our website http://www.diodes.com/package-outlines.html.

Notes:

1N4148WS / BAV16WS








PULSE WIDTH (ms)

Fig. 6 Maximum Non-Repetitive Surge Current



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.




SOD323					
Dim	Min	Max	Тур		
A1	-	0.10	0.05		
A2	1.00	1.10	1.05		
b	0.25	0.35	0.30		
С	0.10	0.15	0.11		
D	1.20	1.40	1.30		
Е	1.60	1.80	1.70		
He	2.30	2.70	2.50		
L	0.20	0.40	0.30		
а	0°	8°	_		
All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOD323



Dimensions	Value (in mm)
Х	0.590
X1	2.700
Y	0.450

1N4148WS / BAV16WS

Document number: DS30097 Rev. 25- 2



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2016, Diodes Incorporated

www.diodes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated: 1N4148WS-7-F BAV16WS-7-F 1N4148WS-13-F BAV16WS-13-F