







CUSTOMER DRAWING



PCB LAYOUT T=1.6
TOP VIEW TOL: ±0.05

版次 REV.	ECN编号 ECN NUMBER	设变内容 MODIFICATION	日期 DATE	制图 DRAW	核准 APPROVE
A		初版发行	20-SEP-18	DOREN	DDS

NOTES:

MATERIAL:

- 1.HOUSING MATERIAL:GLASS FILLED POLYESTER(UL94V-0).
- 2.CONTACT MATERIAL:PHOSPHOR BRONZE ϕ 0.46mm .
- 3.PLATING:GOLD PLATING OVER NICKEL.

ELECTRICAL:

- 1.VOLTAGE RATING:125 VAC RMS.
- 2.CURRENT RATING:1.5 AMP.
- 3.CONTACT RESISTANCE:40 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE:500 MEGOHMS MIN @ 500V DC.
- 5.DIELECTRIC WITHSTANDING RESISTANCE:
500V DC RMS 50Hz. 1MIN.

MECHANICAL:

- 1.DURRABILITY:750 CYCLES MIN.

ENVIRONMENTAL:

- 1.STORAGE:-40°C TO +85°C.
2. OPERATION: 0°C TO 70°C.

RB 0 00 - ZZ 1 - F 1 X - 012A



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GMA AND SHALL BE COPIED OR NOT BE REPRODUCED, CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GMA	DIMENSION IN mm [Inch]		GMA 东莞市国满电子科技有限公司 Dongguan Guoman Electronic Technology Co., Ltd.	
	TOLERANCE UNLESS OTHERWISE SPECIFIED		料号 FILE NO.	图号 DWG NO.
	.X± 0.35	X°± 3°	RB000-ZZ1-F1X-012A	RB012A-11
	.XX± 0.25	.X°± 2°	名称 TITLE	
	.XXX± 0.15	.XX°± 1°	5301 1x4 全塑 DIP B款	
核准 APPROVE	审核 CHECK	制图 DRAW	角法 PROJ.	图纸 SIZE A4
		比例 SCALE 1:1	张数 SHEET 1/1	版次 REV A