



创 容 新 能 源

APPROVE SHEET

TO: 缓冲吸收电容 2uF ±5% 1200V

Main Materials		MARKING & OUTLINE DRAWING	
Construction	Materials	<p style="text-align: right;">$L \times F \times N \times S = 14 \times 15 \times 8.5 \times 6.5$</p>	<p>MKP- HS 2.0uF K datecode .1200V.DC www.csdcap.com</p>
Dielectric	Metallized Polypropylene Film		
Terminal	Tinned copper plate		
Filling	Flame-retardant epoxy resin, white		
Case	Flame-retardant plastic case, grey		

Part No.	TYPE	Dimensions (mm)					NOTE
		W	H	T	P1	P	
HS5082	MKP-HS2.0μFK 1200VDC	57.5	45	30	12	26	

CUSTOMER CONFIRMATION			CR OFFER		
STAMP	APPROVED BY	CHECKED BY	STAMP	APPROVED BY	PREPARED BY
				张东泽	李道燕
DATE			DATE	2017-05-11	

深圳众瑞电子技术有限公司
深圳市创容新能源有限公司

深圳市南山区登良路汉京大厦 5F-528

电话: 0755-82598029 传真: 0755-29494958

深圳市光深深圳市宝安区松岗街道燕川社区北部工业园研发中心 6 楼 7 楼


CRC-BDE-08

Technical Data


Items	Symbols	Values
Rated capacitance	C_N	$2.0\mu\text{F} \pm 10\%$
Rated voltage	U_N	1200V.DC
Non-recurrent surge voltage	U_s	1800V.DC
Maximum current	I_{rms}	20A
Maximum peak current	\hat{I}	1500A
Maximum surge current	I_s	4500A
Series resistance	R_s	$\leq 4\text{m}\Omega$
Tangent of the loss	$\tan \delta$	≤ 0.0010 (1kHz)
Insulation Resistance	$C \times R_{is}$	$\geq 5000\text{S}$
Self inductance	L_e	$\leq 30\text{nH}$
Lowest operating temperature	Θ_{min}	-40°C
Maximum operating temperature	Θ_{max}	105°C
operating humidity	RH	0~95%
Storage temperature	$\Theta_{storage}$	85°C
Service life		100000h
At $\Theta_{hotspot}$		$\leq 70^\circ\text{C}$
Failure quota		100Fit
Test data		
Voltage test between terminals	V_{tt}	1800V.DC/10S
A.C. voltage test between terminals and case	V_{t-c}	3000V.AC/10S
Operating altitude		2000m (max)
Terminal tightening torque		4.5Nm (max)
Bottom tightening torque		---
Weight		kg

ELECTRICAL CHARACTERISTICS OF FILM CAPACITOR

1. Lifetime Expectancy




Lifetime expectancy vs. Charging temperature




Lifetime expectancy vs. Charging voltage


2. Temperature Characteristics




Capacitance change rate vs. Temperature



Operating current vs. Temperature




Operating voltage vs. Temperature




(CR value) IR vs. Temperature

3. Frequency Characteristics



Capacitance change rate vs. Frequency



Dissipation factor vs. Frequency