

# LEGM35BE120L4H

## IGBT Power Module


### Features:

- $V_{CE}=1200V$   $I_C=35A$
- Low  $V_{CE(sat)}$
- $V_{CEsat}$  with positive temperature coefficient
- Maximum junction temperature 175 °C
- Isolation Type Package


### Applications:

- The inverter
- Motor control and drives

### Package Type & Internal Circuit



L4



Internal Circuit

### Maximum Rated Values ( IGBT,Inverter )

Symbol	Parameter	Conditions	Ratings	Unit
$V_{CES}$	Collector-emitter voltage	$V_{EC}= 0 V, I_C= 1 mA, T_{vj}= 25\text{ }^\circ\text{C}$	1200	V
$I_C$	Continuous Collector Current	$T_C= 100\text{ }^\circ\text{C}$	35	A
$I_{CRM}$	Peak Collector Current	$I_{CRM}= 2 I_C$	70	A
$V_{GES}$	Gate-Emitter Voltage	$T_{vj}= 25\text{ }^\circ\text{C}$	$\pm 30$	V
$P_{tot}$	Total Power Dissipation	$T_C= 25\text{ }^\circ\text{C}, T_{vjmax}= 175\text{ }^\circ\text{C}$	200	W

**Characteristics Values (IGBT Inverter )**

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit	
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage	$I_C=35\text{ A}, V_{GE}=15\text{ V}, T_{vj}=25\text{ }^\circ\text{C}$		2.00		V	
		$I_C=35\text{ A}, V_{GE}=15\text{ V}, T_{vj}=150\text{ }^\circ\text{C}$		2.50		V	
$V_{GE(th)}$	Gate Threshold Voltage	$I_C=5.0\text{ mA}, V_{CE}=V_{GE}, T_{vj}=25\text{ }^\circ\text{C}$		5.8		V	
$I_{CES}$	Collector-Emitter Cut-off Current	$V_{CE}=1200\text{ V}, V_{GE}=0\text{ V}, T_{vj}=25\text{ }^\circ\text{C}$			1.2	mA	
$I_{GES}$	Gate-Emitter Leakage Current	$V_{CE}=0\text{ V}, V_{GE}=15\text{ V}, T_{vj}=25\text{ }^\circ\text{C}$			410	nA	
$t_{d(on)}$	Turn-on Delay Time, Inductive Load	$I_C=35\text{ A}, V_{CE}=600\text{ V}$ $V_{GE}=\pm 15\text{ V}$ $R_G=15\Omega$ $T_{vj}=25\text{ }^\circ\text{C}$		170		ns	
$t_r$	Rise Time, Inductive Load			160		ns	
$t_{d(off)}$	Turn-on Delay Time, Inductive Load			310		ns	
$t_f$	Fall Time, Inductive Load			100		ns	
$E_{on}$	Turn-on Energy Loss per Pulse			4.6		mJ	
$E_{off}$	Energy Loss per Pulse			2.2		mJ	
$t_{d(on)}$	Turn-on Delay Time, Inductive Load		$I_C=35\text{ A}, V_{CE}=600\text{ V}$ $V_{GE}=\pm 15\text{ V}$ $R_G=15\Omega$ $T_{vj}=150\text{ }^\circ\text{C}$		210		ns
$t_r$	Rise Time, Inductive Load				180		ns
$t_{d(off)}$	Turn-on Delay Time, Inductive Load				350		ns
$t_f$	Fall Time, Inductive Load				180		ns
$E_{on}$	Turn-on Energy Loss per Pulse			4.9		mJ	
$E_{off}$	Energy Loss per Pulse			3.0		mJ	
$R_{thJC}$	Thermal resistance, junction to case	per IGBT				0.75	K/W
$T_{vj\ op}$	Temperature under switching conditions		-40		150	$^\circ\text{C}$	
$I_{sc}$	SC	$V_{GE} \leq 15\text{ V}, V_{CE}=600\text{ V},$ $t_p \leq 10\ \mu\text{s}, T_{vj}=150\text{ }^\circ\text{C},$ $V_{CEmax}=V_{CES}-L_{sCE} \cdot di/dt$		170		A	

**Maximum Rated Values (Diode Inverter)**

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
$V_{RRM}$	Repetitive Peak Reverse Voltage	$T_{vj}= 25\text{ }^{\circ}\text{C}$		1200		V
$I_F$	Continuous DC Forward Current	$T_C= 100\text{ }^{\circ}\text{C}$		35		A
$I_{FRM}$	Repetitive Peak Forward Current	$t_p= 1\text{ ms}$		70		A
$I^2t$	$I^2t$ Value	$V_R= 0\text{ V}$ , $t_p= 10\text{ ms}$ , $T_{vj}= 125\text{ }^{\circ}\text{C}$		220		A <sup>2</sup> s

**Characteristic Values (Diode Inverter)**

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
$V_F$	Forward Voltage	$I_F= 35\text{ A}$ , $V_{CE}= 0\text{ V}$ , $T_{vj}= 25\text{ }^{\circ}\text{C}$		2.38		V
		$I_F= 35\text{ A}$ , $V_{CE}= 0\text{ V}$ , $T_{vj}= 150\text{ }^{\circ}\text{C}$		2.7		V
$t_{rr}$	Reverse Recovery time	$I_F= 35\text{ A}$ , $V_R= 600\text{ V}$ $-di/dt= 100\text{ A/us}$		140		ns
$Q_r$	Recovered Charge			1.1		uC
$E_{rec}$	Reverse Recovery Energy		$T_{vj}= 25\text{ }^{\circ}\text{C}$		6.7	
$t_{rr}$	Reverse Recovery time	$I_F= 35\text{ A}$ , $V_R= 600\text{ V}$ $-di/dt= 100\text{ A/us}$		290		ns
$Q_r$	Recovered Charge			2.5		uC
$E_{rec}$	Reverse Recovery Energy		$T_{vj}= 150\text{ }^{\circ}\text{C}$		0.5	
$R_{thJC}$	Thermal resistance, junction to case	per Diode			1.03	K/W
$T_{vj\text{op}}$	Temperature under switching conditions		-40		150	$^{\circ}\text{C}$

**Maximum Rated Values (IGBT Brake-Chopper)**

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
$V_{CES}$	Collector-emitter voltage	$T_{vj}=25^{\circ}C$		1200		V
$I_C$	Continuous Collector Current	$TC=100^{\circ}C, T_{vj} \max=175^{\circ}C$		25		A
$I_{CRM}$	Peak Collector Current	$I_{CRM}=2I_C$		50		A
$V_{GES}$	Gate-Emitter Voltage	$T_{vj}=25^{\circ}C$	-20		20	V

**Characteristic Values (IGBT Brake-Chopper)**

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit	
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage	$I_C=25A, V_{GE}=15V, T_{vj}=25^{\circ}C$		2.01		V	
		$I_C=25A, V_{GE}=15V, T_{vj}=150^{\circ}C$		2.53		V	
$V_{GE(th)}$	Gate Threshold Voltage	$I_C=5.0mA, V_{CE}=V_{GE}, T_{vj}=25^{\circ}C$		5.8		V	
$I_{CES}$	Collector-Emitter Cut-off Current	$V_{CE}=1200V, V_{GE}=0V, T_{vj}=25^{\circ}C$			1.2	mA	
$I_{GES}$	Gate-Emitter Leakage Current	$V_{CE}=0V, V_{GE}=15V, T_{vj}=25^{\circ}C$			410	nA	
$t_{d(on)}$	Turn-on Delay Time, Inductive Load	$I_C=25A, V_{CE}=600V$ $V_{GE}=\pm 15V$ $R_G=20\Omega$ $T_{vj}=25^{\circ}C$		170		ns	
$t_r$	Rise Time, Inductive Load			160		ns	
$t_{d(off)}$	Turn-off Delay Time, Inductive Load			170		ns	
$t_f$	Fall Time, Inductive Load			150		ns	
$E_{on}$	Turn-on Energy Loss per Pulse				3.7		mJ
$E_{off}$	Energy Loss per Pulse				1.4		mJ
$t_{d(on)}$	Turn-on Delay Time, Inductive Load		$I_C=25A, V_{CE}=600V$ $V_{GE}=\pm 15V$ $R_G=20\Omega$ $T_{vj}=150^{\circ}C$		130		ns
$t_r$	Rise Time, Inductive Load				180		ns
$t_{d(off)}$	Turn-off Delay Time, Inductive Load				250		ns
$t_f$	Fall Time, Inductive Load				180		ns
$E_{on}$	Turn-on Energy Loss per Pulse				3.9		mJ
$E_{off}$	Energy Loss per Pulse				1.8		mJ
$R_{thJC}$	Thermal resistance, junction to case	per IGBT			0.89	K/W	
$T_{vj op}$	Temperature under switching conditions		-40		150	$^{\circ}C$	

**Maximum Rated Values (Diode Rectifier)**

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
$V_{RRM}$	Repetitive peak reverse voltage	$T_{vj}= 25\text{ }^{\circ}\text{C}$		1800		V
$I_{FRMSM}$	Maximum RMS forward current per chip	$T_c= 80\text{ }^{\circ}\text{C}$		70		A
$I_{RMSM}$	Maximum RMS current at rectifier chip	$T_c= 80\text{ }^{\circ}\text{C}$		70		A
$I_{FSM}$	Surge forward current	$t_p= 10\text{ms}$ $T_{vj}= 25\text{ }^{\circ}\text{C}$		420		A
$I^2t$	$I^2t$ -value	$t_p= 10\text{ms}$ $T_{vj}= 150\text{ }^{\circ}\text{C}$		880		A <sup>2</sup> S
$I_{FSM}$	Surge forward current	$t_p= 10\text{ms}$ $T_{vj}= 25\text{ }^{\circ}\text{C}$		360		A
$I^2t$	$I^2t$ -value	$t_p= 10\text{ms}$ $T_{vj}= 150\text{ }^{\circ}\text{C}$		600		A <sup>2</sup> S

**Characteristic Values (Diode Rectifier)**

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
$V_F$	Forward voltage	$T_c= 25\text{ }^{\circ}\text{C}$		0.9		V
$I_R$	Reverse current	$T_{vj}= 150\text{ }^{\circ}\text{C}$ $V_R= 1800\text{V}$		1.1		mA
$R_{thjc}$	Thermal resistance junction to case	$T_c= 25\text{ }^{\circ}\text{C}$		0.76		K/W
$T_{vjop}$	Temperature under switching conditions	per diode	-40		150	$^{\circ}\text{C}$

**Maximum Rated Values (Diode Brake-Chopper)**

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
$V_{RRM}$	Repetitive Peak Reverse Voltage	$T_{vj} = 25\text{ }^{\circ}\text{C}$		1200		V
$I_F$	Continuous DC Forward Current	$T_C = 100\text{ }^{\circ}\text{C}$		25		A
$I_{FRM}$	Repetitive Peak Forward Current	$t_p = 1\text{ ms}$		50		A
$I^2t$	$I^2t$ Value	$V_R = 0\text{ V}$ , $t_p = 10\text{ ms}$ , $T_{vj} = 150\text{ }^{\circ}\text{C}$		100		$\text{A}^2\text{s}$

**Characteristics (Diode Brake-Chopper)**

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
$V_F$	Forward Voltage	$T_{vj} = 25\text{ }^{\circ}\text{C}$		2.03		V
		$T_{vj} = 150\text{ }^{\circ}\text{C}$		2.05		V
$t_{rr}$	Reverse Recovery time	$I_F = 25\text{ A}$ , $V_R = 600\text{ V}$ $-di/dt = 250\text{ A/us}$		220		ns
$Q_r$	Recovered Charge			0.8		$\mu\text{C}$
$E_{rec}$	Reverse Recovery Energy		$T_{vj} = 25\text{ }^{\circ}\text{C}$		0.2	
$t_{rr}$	Reverse Recovery time	$I_F = 25\text{ A}$ , $V_R = 600\text{ V}$ $-di/dt = 250\text{ A/us}$		340		ns
			$Q_r$	Recovered Charge		1.6
$E_{rec}$	Reverse Recovery Energy		$T_{vj} = 150\text{ }^{\circ}\text{C}$		0.5	
$R_{thJC}$	Thermal resistance, junction to case	$I_F = 25\text{ A}$ , $V_{CE} = 0\text{ V}$ , $T_{vj} = 25\text{ }^{\circ}\text{C}$			1.24	K/W
$T_{vj\text{ op}}$	Temperature under switching conditions		-40		150	$^{\circ}\text{C}$

**NTC-Thermistor (Characteristic Values)**

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
R <sub>25</sub>	Rated resistance	T <sub>c</sub> = 25 °C		5		KΩ
ΔR/R	Deviation of R100	T <sub>c</sub> = 100 °C	-5		5	%
P <sub>25</sub>	Power dissipation	T <sub>c</sub> = 25 °C		20		mW
B <sub>25/50</sub>	B-value	$R_2 = R_{25} \exp[B_{25/50}(1/T_2 - 1/(298,15K))]$		3380		K
B <sub>25/100</sub>	B-value	$R_2 = R_{25} \exp[B_{25/100}(1/T_2 - 1/(298,15K))]$		3450		K


**Module Characteristics**

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
V <sub>isol</sub>	Isolation voltage	t = 1 min, f = 50 Hz	2500			V
T <sub>stg</sub>	Storage Temperature		-40		150	°C
M <sub>s</sub>	Module-to-Sink Torque	Recommended(M5)	3.0		6.0	N·m
G	Weight of Module			180		g

**Output characteristic of IGBT, Inverter (typical)**


$$I_c = f(V_{CE})$$

$$V_{GE} = 15V$$


**Switching time of IGBT, Inverter (typical)**


$$E_{on} = f(I_c), E_{off} = f(I_c)$$

$$V_{GE} = \pm 15V, R_G = 15\Omega, V_{CE} = 600V$$


**Switching loss of IGBT, Inverter (typical)**


$$E_{on} = f(R_G), E_{off} = f(R_G)$$

$$V_{GE} = \pm 15V, I_c = 35A, V_{CE} = 600V$$


**RBSOA IGBT, Inverter (typical)**

$$I_c = f(V_{CE})$$


$$V_{GE} = \pm 15V, R_G = 15\Omega, T_{vj} = 150^\circ\text{C}$$





Forward characteristic of Diode, Inverter (typical)


$$I_F = f(V_F)$$



Switching losses of Diode, Inverter (typical)

$$E_{rec} = f(R_G)$$


$$I_F = 35 \text{ A}, V_{CE} = 600 \text{ V}$$



Switching losses of Diode, Inverter (typical)

$$E_{rec} = f(I_F)$$


$$R_{Gon} = 15 \Omega, V_{CE} = 600 \text{ V}$$



Output characteristic of IGBT, Brake-Chopper, (typical)


$$I_c = f(V_{CE})$$

$$V_{GE} = 15 \text{ V}$$




Forward characteristic of Diode, Brake-Chopper (typical)

$$I_F = f(V_F)$$




Forward characteristic of Diode, Rectifier (typical)

$$I_F = f(V_F)$$




NTC-thermistor-temperature characteristic (typical)

$$R = f(T_{NTC}),$$




**Circuit Diagram**



**Package Dimensions**

(Dimensions in Millimeters)



**DISCLAIMER**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE