

PESDNC2FD8VB

Bi-directional 8V Normal Capacitance ESD Protector

Description

The PESDNC2FD8VB protects sensitive semiconductor components from damage or upset due to electrostatic discharge (ESD) and other voltage induced transient events. They feature large cross-sectional area junctions for conducting high transient currents, offer desirable electrical characteristics for board level protection, such as fast response time, low operating voltage. It gives designer the flexibility to protect one bi-directional line in applications where arrays are not practical.

Feature


- 30W peak pulse power per line (t_P = 8/20µs)
- DFN1006-2L package
- Replacement for MLV(0402)
- Bidirectional configurations
- Response time is typically < 1ns</p>
- Low clamping voltage
- RoHS compliant
- Transient protection for data lines to IEC61000-4-2(ESD) ±15KV(air), ±10KV(contact);
 IEC61000-4-4 (EFT) 40A (5/50ns)

Applications


- Cellular phones
- Portable devices
- Digital cameras
- Power supplies

Mechanical Characteristics


- Mounting position: Any
- Qualified max reflow temperature:260°C
- Device meets MSL 1 requirements
- DFN1006-2L without plating



DFN1006-2L(Bottom View)




Marking (Top View)



PESDNC2FD8VB

Electronics Parameter

Symbol	Parameter	
V _{RWM}	Peak Reverse Working Voltage	
IR	Reverse Leakage Current @ VRWM	
VBR	Breakdown Voltage @ I⊤	
Iτ	Test Current	
IPP	Maximum Reverse Peak Pulse Current	
Vc	Clamping Voltage @ IPP	
P _{PP}	Peak Pulse Power	
CJ	Junction Capacitance	
IF	Forward Current	
VF	Forward Voltage @ I _F	



Electrical characteristics per line@25°C (unless otherwise specified)


Parameter	Symbol	Conditions	Min.	Тур.	Max.	Units
Peak Reverse Working Voltage	Vrwm				8.0	V
Breakdown Voltage	Vbr	lt = 1mA	8.5		13.0	V
Reverse Leakage Current	lr	V _{RWM} = 8V T=25°С			1.0	μA
Clamping Voltage	Vcl	I _{PP} =16A t _p =100ns		37.0		V
Clamping Voltage	Vc	I _{PP} =1Α t _P = 8/20μs			14.0	V
Clamping Voltage	Vc	I₽₽=2A t₽ = 8/20µs			16.0	V
Junction Capacitance	Cj	V _R =0V f = 1MHz		13.0	15.0	pF


Absolute maximum rating@25°C

Rating	Symbol	Value	Units
Peak Pulse Power (t _p =8/20µs)	P _{pp}	30	W
Maximum Reverse Peak Pulse Current	PP	2	А
Operating Temperature	TJ	-55 to 150	°C
Storage Temperature	T _{STG}	-55 to 150	°C

PESDNC2FD8VB

Typical Characteristics








Fig 3. Clamping voltage vs. Peak pulse current






Fig 5.Typical Leakage Current vs. Temperature








Fig 4. Non-Repetitive Peak Pulse Power vs. Pulse time






Fig 6. TLP Measurement

PESDNC2FD8VB



Solder Reflow Recommendation




PCB Design

For TVS diodes a low-ohmic and low-inductive path to chassis earth is absolutely mandatory in order to achieve good ESD protection. Novices in the area of ESD protection should take following suggestions to heart:


- > Do not use stubs, but place the cathode of the TVS diode directly on the signal trace.
- Do not make false economies and save copper for the ground connection.
- Place via holes to ground as close as possible to the anode of the TVS diode.
- Use as many via holes as possible for the ground connection.
- > Keep the length of via holes in mind! The longer the more inductance they will have.

PESDNC2FD8VB

Product dimension (DFN1006-2L)



Dim	Inches		Millimeters		
Dim	MIN	МАХ	MIN	МАХ	
А	0.013	0.020	0.34	0.498	
В	0.000	0.002	0.00	0.05	
С	0.037	0.043	0.95	1.080	
D	0.022	0.027	0.55	0.680	
E	0.016	0.024	0.40	0.60	
F	0.008	0.012	0.20	0.30	
н	0.015Typ.		0.40Тур.		
R	0.001	0.005	0.05	0.15	



Suggested PCB Layout


Ordering information

Device	Package	Reel	Shipping
PESDNC2FD8VB	DFN1006-2L (Pb-Free)	7"	10000 / Tape & Reel

PESDNC2FD8VB

ESD Protector

Load with information



IMPORTANT NOTICE

Q and **Prisemi** are registered trademarks of **Prisemi Electronics Co., Ltd** (Prisemi), Prisemi reserves the right to make changes without further notice to any products herein. Prisemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Prisemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in Prisemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. Prisemi does not convey any license under its patent rights nor the rights of others. The products listed in this document are designed to be used with ordinary electronic equipment or devices, Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of with would directly endanger human life (such as medical instruments, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

Website: http://www.prisemi.com For additional information, please contact your local Sales Representative. ©Copyright 2009, Prisemi Electronics @Prisemi[®] is a registered trademark of Prisemi Electronics.

All rights are reserved.