

DT12T High Temperature TRIACs

DT12T High Temperature TRIACs SILICON BIDIRECTIONAL THYRISTORS

General description


These products of 12A TRAIC are packages for third quadrant, DT12T TRIACs are high commutation performance without snubber circuit. It can be controlled by phase angle trigger or on/off trigger.

FEATURES

- Passivated die for reliability and uniformity
- Three-quadrant triggering.
- Over 800V V_{DRM}/V_{RRM}
- 150 Degree C operation temperature.
- Without snubber circuit.
- "Green" molding compound,
UL flammability classification 94V-0, (No Br. Sb. Cl)
- Lead free in RoHS II 2015/863/EU compliant
- Moisture sensitivity meets industry standard
IPC/JEDEC J-STD-02

APPLICATIONS

- General purpose AC switch control
- Control loads in Motor, Fan, and Pump.
- Solenoid drivers
- LED Dimming
- Inrush current limiting circuits



PIN ASSIGNMENT	
1	Main Terminal 1 (A1)
2	Main Terminal 2 (A2)
3	Gate

DT12T High Temperature TRIACs

ELECTRICAL CHARACTERISTICS (T_j = 25°C, unless otherwise specified.)

Absolute Ratings

PARAMETER	SYMBOL	VALUE	UNIT
Peak repetitive off-state voltage (T _j = -40 to 150°C, Full sine wave, 50 to 60 Hz; Gate open) (Note 1)	V _{DRM} V _{RRM}	800	V
On-stage RMS current (Full sine wave, T _c = 100°C)	I _{T(RMS)}	12	A
Peak non-repetitive surge current (one full cycle 60 Hz, T _j = 25°C)	I _{TSM}	100	A
Circuit fusing consideration (t = 8.3ms)	I ² T	41.5	A ² S
Operating junction temperature range	T _j	-40 to +150	°C
Storage temperature range	T _{STG}	-40 to +150	°C

Note :

(1) V_{DRM} and V_{RRM} for all types can be applied on a continuous basis.

Blocking voltages shall not be tested with a constant current source such that the voltage ratings of the devices are exceeded.

Version 04, Oct-2020

DT12T High Temperature TRIACs

CHARACTERISTIC & CURVES ($T_j = 25^\circ\text{C}$, unless otherwise specified.)



Thermal Characteristics

PARAMETER	SYMBOL	VALUE		UNIT
Thermal resistance from junction to case, without heatsink, (1)	$R_{th(j-c)}$	Max	12	$^\circ\text{C}/\text{W}$
Junction to ambient, without heatsink, (1)	$R_{th(j-a)}$	Typ	35	
Maximum lead temperature for soldering purposes (1/8" form case for 10 seconds)	T_L	Max	260	$^\circ\text{C}$

Note1: unidirectional, continuous & full cycle.

Static Characteristics

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT
Threshold Voltage ($T_j = 150^\circ\text{C}$)	V_{to}	--	--	1	V
Dynamic resistors ($T_j = 150^\circ\text{C}$)	R_d	--	--	35	$\text{m}\Omega$
Peak repetitive forward or reverse blocking current (V_{AK} = rated V_{DRM} and V_{RRM} , gate open)	$T_j = 25^\circ\text{C}$	--	--	5	μA
	$T_j = 125^\circ\text{C}$	--	--	700	μA
	$T_j = 150^\circ\text{C}$			1.9	mA

ON Characteristics


PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT
Peak forward on-state voltage ($I_{TM} = 12 \text{ A}$ @ $T_j = 25^\circ\text{C}$)	V_{TM}	--	--	1.5	V
$V_D = V_{DRM}$, $R_L=100\Omega$, $T_j=150^\circ\text{C}$	V_{GD}	0.25	--	--	V
Gate trigger current ($V_{AK} = 12\text{V}$, $R_L=100\Omega$)	I_{GT1} I_{GT2} I_{GT3}	--	--	35 35 35	mA
Gate trigger voltage ($V_{AK} = 12\text{V}$, $R_L=100\Omega$)	V_{GT1} V_{GT2} V_{GT3}	--	--	1	V
Holding current ($V_{AK} = 12\text{V}$, $R_L=100\Omega$)	I_{H1} I_{H3}	--	--	50	mA
Latching current ($V_{AK} = 12\text{V}$, $R_L=100\Omega$)	I_{L1} I_{L2} I_{L3}	--	--	50 80 50	mA
Critical rate of rise of on-state current, $T_j = 150^\circ\text{C}$	$dI/dt(s)$	--	--	50	A/us
$V_D = 67\% V_{DRM}$, gate open, $T_j = 150^\circ\text{C}$	dV/dt	--	--	2000	V/us
Without snubber, $T_j = 150^\circ\text{C}$	$dI/dt(c)$	--	--	6.5	A/ms
$T_j=150^\circ\text{C}$, $10\text{V}/dt$	$dI/dt(c)$	--	--	35	A/ms

DT12T High Temperature TRIACs


CHARACTERISTIC & CURVES ($T_j = 25^\circ\text{C}$, unless otherwise specified.)




Typical gate trigger current V.S. juction temperature




Typical gate trigger voltage V.S. juction temperature




Typical holding current V.S. juction temperature




Typical latch current V.S. juction temperature



Power dissipation V.S. IT



VTM - IT



DT12T High Temperature TRIACs

CHARACTERISTIC & CURVES ($T_j = 25^\circ\text{C}$, unless otherwise specified.)



Ordering information scheme

D T 16 T 35 F -B H X Δ

Type Code _____

Product Code _____

IT Amp Code _____

Quadrantal Code _____

IGT&VCEsat Code _____

Package Code _____

Voltage Code _____

Operation Temp. Code _____

Internal Code1 _____

Internal Code2 _____

Type Code:

Doeshare Standar products

Product Code:

T for Triac series

IT Amp Code:

16 for 16A, 1 for 1A

Quadrantal Code:

T for 3Q, F for 4Q

IGT&VCEsat Code:

35 means Igt 35mA, 5 means Igt 5mA

Package Code:

A=>TO-92, C=>TO-126, D=> DPAK, E=>D2PAK, F=> TO-220F, G=>SOT-223
M=>ITO-3P, P=>TO-3P, T=> TO-220, Y=>TO251

Voltage Code:

A=> 600V, B=> 800V, C=> 1000V


Operation Temp Code:

None=>125°C, H=>150°C

DT12T High Temperature TRIACs
 CHARACTERISTIC & CURVES ($T_j = 25^\circ\text{C}$, unless otherwise specified.)




ITO-220 Plastic Package



DIM	Millimeters		DIM	Millimeters		DIM	Millimeters	
	Min	Max		Min	Max		Min	Max
A	9.8	10.4	E	3.75	3.95	I	4.38	4.61
B	2.65	3.1	F	14.8	16.1	J	1.15	1.36
C	2.8	4.2	G	13.05	13.6	K	5.85	6.82
D	0.7	0.92	H	2.4	2.7	L	2.35	2.75
M	0.35	0.65	N	1.18	1.42			

TO-220F Plastic Package




DIM	Millimeters		DIM	Millimeters		DIM	Millimeters	
	Min	Max		Min	Max		Min	Max
C	4.3	4.7	R	3.0	3.4	E1	2.29	2.79
A	9.7	10.3	b	12.5	13.5	C1	2.5	2.9
B	14.7	15.3	b1	2.9	3.9	C2	2.5	2.7
B1	3.8	4.0	a	0.55	0.75	c	0.5	0.7
B2	2.9	3.1	E	2.29	2.79			

DT12T High Temperature TRIACs
 CHARACTERISTIC & CURVES ($T_j = 25^\circ\text{C}$, unless otherwise specified.)



ITO-220 Plastic Package




DIM	Millimeters		DIM	Millimeters		DIM	Millimeters	
	Min	Max		Min	Max		Min	Max
A	9.8	10.4	E	3.75	3.95	I	4.38	4.61
B	2.65	3.1	F	14.8	16.1	J	1.15	1.36
C	2.8	4.2	G	13.05	13.6	K	5.85	6.82
D	0.7	0.92	H	2.4	2.7	L	2.35	2.75
M	0.35	0.65	N	1.18	1.42			

DT12T High Temperature TRIACs

CHARACTERISTIC & CURVES ($T_j = 25^\circ\text{C}$, unless otherwise specified.)



DPAK(TO-252) Plastic Package




DIM	Millimeters		DIM	Millimeters		DIM	Millimeters	
	Min	Max		Min	Max		Min	Max
A	6.50	6.70	C1	0.967	1.087	θ1	$0^\circ \sim 8^\circ$	
A1	0.71	0.81	C2	0.498	0.518	θ2	8.5° TYP4	
A2	2.236	2.336	D	0.70	0.90	θ3	25° TYP	
A3	5.284	5.384	D1	1.40	1.60	θ4	10° TYP	
A4	0.75	0.85	D2	0.81	0.91	θ5	10° TYP	
B	6.00	6.20	D3	0.05 TYP		θ6	70° TYP	
B1	9.80	10.10	H	0.00	0.10			
C	2.20	2.40	R	0.40 TYP				

DT12T High Temperature TRIACs

CHARACTERISTIC & CURVES ($T_j = 25^\circ\text{C}$, unless otherwise specified.)



TO-262 Plastic Package



Item	Unit: mm		
	Type	Min	Max
A	10	9.95	10.2
B	23.35	23.25	23.45
C	9	8.9	9.1
D	2.54	2.5	2.6
E	1.27	1.2	1.35
F	0.8	0.75	0.85
G	3.5	3.3	3.6
H	4.5	4.45	4.55
I	1.27	1.25	1.29
J	2.6	2.5	2.7
K	0.4	0.38	0.42

Important Notice and Disclaimer

DOESHARE has used reasonable care in preparing the information included in this document, but DOESHARE does not warrant that such information is error free. DOESHARE assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.

DOESHARE makes no warranty, representation or guarantee regarding the documents, circuits and products specification, DOESHARE reserves the right to make changes for any documents, products, circuits and specifications at any time without notice.

Purchasers are solely responsible for the choice, selection and use of the DOESHARE products and services described herein, and DOESHARE assumes no liability whatsoever relating to the choice, selection or use of the products and services described herein.

No license, express or implied, by implication or otherwise under any intellectual property rights of DOESHARE.

Resale of DOESHARE products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by DOESHARE for the DOESHARE product or service described herein and shall not create or extend in any manner whatsoever, any liability of DOESHARE.