HIGH POWERED TVS ARRAY



DESCRIPTION

The PSDxx and PSDxxC Series are transient voltage suppressor arrays designed for ESD protection of SMART phones, laptop computers and other portable electronics. These silicon based diodes offer superior clamping voltage and performance compared to other technologies such as MLVs.

The PSDxx and PSDxxC Series can be utilized as a single line protector in either a unidirectional or bidirectional configuration. The SOD-323 small package configuration offers designers the flexibility of placement on the printed circuit board for each I/O port or voltage bus. The PSDxx and PSDxxC Series meets the IEC 61000-4-2 (ESD), 61000-4-4 (EFT) and 61000-4-5 requirements.

FEATURES

- Compatible with IEC 61000-4-2 (ESD): Air 15kV, Contact 8kV
- Compatible with IEC 61000-4-4 (EFT): 40A 5/50ns
- Compatible with IEC 61000-4-5 (Surge): 24A, 8/20μs Level 2(Line-Gnd) & Level 3 (Line-Line)
- Unidirectional: 500 Watts Peak Pulse Power per Line (tp = 8/20µs)
- Bidirectional: 400 Watts Peak Pulse Power per Line (tp = 8/20μs)
- · Replacement for MLV (0805)
- Unidirectional & Bidirectional Configurations
- Protects One Power or I/O Port
- ESD Protection > 25kV
- Low Clamping Voltage
- Available in Multiple Voltages Ranging From 3V to 36V
- RoHS Compliant
- REACH Compliant


MECHANICAL CHARACTERISTICS


- Molded JEDEC SOD-323 Package
- Approximate Weight: 5 milligrams
- Lead-Free Pure-Tin Plating (Annealed)
- Solder Reflow Temperature:
 - Pure-Tin Sn, 100: 260-270°C
- 8mm Tape and Reel Per EIA Standard 481
 Flammability Rating UL 94V-0

APPLICATIONS

- Laptop Computers
- SMART Phones
- Portable Electronics

PIN CONFIGURATIONS





05118.R15 11/13 Page 1 ISO 9001: 2015 CERTIFIED





MAXIMUM RATINGS @ 25°C Unless Otherwise Specified								
PARAMETER SYMBOL VALUE UNI								
Unidirectional: Peak Pulse Power (tp = 8/20μs) - See Figure 1	P _{pp}	500	Watts					
Bidirectional: Peak Pulse Power (tp = 8/20μs) - See Figure 1	P _{pp}	400	Watts					
Operating Temperature	T _L	-55 to 150	°C					
Storage Temperature	T _{stg}	-55 to 150	°C					


ELECTRICAL CHARACTERISTICS PER LINE @ 25°C Unless Otherwise Specified								
PART NUMBER (Note 1)	DEVICE MARKING	RATED STAND-OFF VOLTAGE V _{WM} VOLTS	MINIMUM BREAKDOWN VOLTAGE @ 1mA V _(BR) VOLTS	MAXIMUM CLAMPING VOLTAGE (Fig. 2) @ IP = 1A V _C VOLTS	MAXIMUM LEAKAGE CURRENT @V _{wM} Ι _D μΑ	TYPICAL CAPACITANCE @0V, 1MHz C pF		
PSD03	А	3.3	4.0	6.5	125	500		
PSD03C	G	3.3	4.0	7.0	125	200		
PSD05	В	5.0	6.0	9.8	10	350		
PSD05C	Н	5.0	6.0	9.8	10	175		
PSD08	С	8.0	8.5	13.4	10	250		
PSD08C	J	8.0	8.5	13.4	10	150		
PSD12	D	12.0	13.3	19.0	1	150		
PSD12C	К	12.0	13.3	19.0	1	50		
PSD15	E	15.0	16.7	24.0	1	100		
PSD15C	L	15.0	16.7	24.0	1	40		
PSD18	18	18.0	20.0	29.0	1	90		
PSD18C	N	18.0	20.0	29.0	1	40		
PSD24	F	24.0	26.7	43.0	1	88		
PSD24C	М	24.0	26.7	43.0	1	40		
PSD36	R	36.0	40.0	60.0	1	75		
PSD36C	Т	36.0	40.0	60.0	1	35		


NOTES


^{1.} Part numbers with an additional "C" suffix are bidirectional devices, i.e., PSD05<u>C</u>.











PSD03 FORWARD TLP Leakage Current @ Pulse (I) - μA Leakage Test Voltage = 0.5V 1E-5 1E-2 1E-6 1E-4 30-27.5 25-22.5 20-Current (I) - Amps 17.5 15 12.5 10-7.5 2.5


0-

FIGURE 6

FIGURE 7
PSD03 REVERSE TLP
Leakage Current @ Pulse (I) - μA
Leakage Test Voltage = 0.5V


Voltage (V) - Volts

3 3.25



Note: Indicative TLP performance- for reference only


FIGURE 8 PSD36 FORWARD TLP Leakage Current @ Pulse (I) - μA Leakage Test Voltage = 0.5V 1E-6 1E-7 29.9-28 26 24-22-20-Current (I) - Amps 18 16-14-12-10-8-6-4-0.5 Voltage (V) - Volts



Note: Indicative TLP performance- for reference only

SPICE MODEL

FIGURE 1 SPICE MODEL FOR



ABD - Avalanche Breakdown Diode (TVS) Lg - Lead Inductance

TABLE 1 - SPICE PARAMETERS							
PARAMETER	PARAMETER UNIT						
BV	V	See Table 2					
IBV	μΑ	1					
C _{jo}	pF See Table 2						
I _s	А	See Table 2					
Vj	V	0.6					
М	-	0.33					
N	-	1					
R_s	Ohms	See Table 2					
TT	S	1E-8					
EG	eV	1.11					

TABLE 2 - ABD SPECIFIC SPICE PARAMETERS									
PART NUMBER	B _v (VOLTS)	C _{io} (pF)	I _s (AMPS)	Rs(OHMS)					
PSD03	4.0	438	1E-11	0.21					
PSD05	6.0	284	1E-11	0.14					
PSD08	8.5	146	1E-11	0.28					
PSD12	13.3	123	1E-13	0.40					
PSD15	16.7	102	1E-13	0.52					
PSD24	26.7	61	1E-13	1.54					
PSD03C	4.5	219	1E-11	0.21					
PSD05C	6.0	142	1E-11	0.14					
PSD08C	8.5	73	1E-11	0.28					
PSD12C	13.3	62	1E-13	0.40					
PSD15C	16.7	51	1E-13	0.52					
PSD24C	26.7	30	1E-13	1.54					







SOD-323 PACKAGE INFORMATION


OUTLINE DIMENSIONS								
DIM	MILLIN	METERS	INCHES					
	MIN	MAX	MIN	MAX				
А	1.60	1.90	0.063	0.075				
В	1.15	1.45	0.045	0.057				
С	2.39	2.70	0.094	0.106				
D	0.80	1.10	0.031	0.043				
Е	0.25	0.40	0.010	0.016				
F	0.10	0.20	0.004	0.008				
Н	-	0.10	-	0.004				
L	0.20	-	0.008	-				

NOTES

- 1. Controlling dimension: millimeters.
- 2. Dimensioning and tolerances per ANSI Y14.5M, 1985.
- 3. Dimensions are exclusive of mold flash and metal burrs.









PAD LAYOUT DIMENSIONS								
DINA	MILLIM	IETERS	INCHES					
DIM	MIN	MAX	MIN	MAX				
Α	2.87	3.12	0.113	0.123				
В	0.66	0.91	0.026	0.036				
С	0.66	0.91	0.026	0.036				

NOTES

1. Controlling dimension: millimeters.



TAPE AND REEL



SPECIFICATIONS												
REEL DIA.	TAPE WIDTH	Α0	В0	КО	D	E	F	W	P0	P2	Р	tmax
178mm (7")	8mm	1.55 ± 0.10	2.90 ± 0.10	1.35 ± 0.10	1.50 ± 0.10	1.75 ± 0.10	3.50 ± 0.05	8.00 ± 0.30	4.00 ± 0.10	2.00 ± 0.05	4.00 ± 0.10	0.25

NOTES

- 1. Dimensions are in millimeters.
- 2. Surface mount product is taped and reeled in accordance with EIA-481.
- 3. Suffix T7 = 7" Reel 3,000 pieces per 8mm tape.
- 4. Marking on Part marking code (see page 2), polarity band (Unidirectional Only).

ORDERING INFORMATION									
BASE PART NUMBER (xx = Voltage)	I I FADEREF SIJEFIX I TAPE SIJEFIX I OTV/REFI I REFI SIZE I TIJRE OTV								
PSDxx/PSDxxC	-LF	-T7	3,000	7"	n/a				
This device is only available in a Lead-Free configuration.									

05118.R15 11/13 Page 9 ISO 9001: 2015 CERTIFIED



COMPANY INFORMATION

COMPANY PROFILE

In business more than 25 years, ProTek Devices™ is a privately held semiconductor company. The company offers a product line of overvoltage protection and overcurrent protection components. These include transient voltage suppressor array (TVS arrays) avalanche breakdown diode, steering diode TVS array and electronics SMD chip fuses. These components deliver circuit protection in electronic systems from numerous overvoltage and overcurrent events. They include lightning; electrostatic discharge (ESD); nuclear electromagnetic pulses (NEMP); inductive switching; and electromagnetic interference (EMI) / radio frequency interference (RFI). ProTek Devices also offers LED wafer die for ESD protection and related high frequency products. ProTek Devices is ISO 9001:2015 certified.

CONTACT US

Corporate Headquarters

2929 South Fair Lane Tempe, Arizona 85282 USA

By Telephone

General: 602-431-8101

Sales: & Marketing: 602-414-5109 Customer Service: 602-414-5114

Product Technical Support: 602-414-5107

By Fax

General: 602-431-2288

By E-mail:

Asia Sales: <u>asiasales@protekdevices.com</u>
Europe Sales: <u>europesales@protekdevices.com</u>
U.S. Sales: <u>ussales@protekdevices.com</u>
Distributor Sales: <u>distysales@protekdevices.com</u>
Customer Service: <u>service@protekdevices.com</u>
Technical Support: <u>support@protekdevices.com</u>

ProTek Devices (Asia Pacific) Pte. Ltd.

8 Ubi Road 2, #06-19

Zervex

Singapore - 408538 Tel: +65-67488312 Fax: +65-67488313

Web

www.protekdevices.com

COPYRIGHT © ProTek Devices 2000 - This literature is subject to all applicable copyright laws and is not for resale in any manner.

SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance. ProTek assumes no responsibility with respect to the selection or specifications of such products. ProTek makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ProTek assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability without limitation special, consequential or incidental damages.

LIFE SUPPORT POLICY: ProTek Devices products are not authorized for use in life support systems without written consent from the factory.

05118.R15 11/13 Page 10 ISO 9001: 2015 CERTIFIED