FUZETEC TECHNOLOGY CO., LTD.

NO.

**Product Specification and Approval Sheet** Version Page

3

1/3

# Axial Leaded PTC Resettable Fuse: FLR600F

#### 1. Summary

- (a) RoHS Compliant (Lead Free) Product
- (b) Applications: Rechargeable battery packs, Lithium cell and battery packs
- (c) Product Features: Low profile, Low resistance, High hold current, Solid state
- (d) Operation Current: 6.0A
- (e) Maximum Voltage: 20V
- (f) Temperature Range :  $-40^{\circ}$ C to  $85^{\circ}$ C

#### 2. Agency Recognition

- UL: File No. E211981
- TÜV: File No. R50004084

### 3. Electrical Characteristics (23°C)

Part Number	Hold	Trip	Max.Time	Rated	Maximum	Typical	I	9	
	Current	Current	to Trip	Voltage	Current	Power	RMIN	Rмах	R1max
	Ін, А	Ιт, А	at 5xIH,s	VMAX, VDC	Імах, А	Pd, W	Ohms	Ohms	Ohms
FLR600F	6.0	11.7	5.0	20	100	2.8	0.007	0.014	0.019

 $I_{H}$ =Hold current-maximum current at which the device will not trip at 23°C still air.

IT=Trip current-minimum current at which the device will always trip at 23  $^\circ\!C$  still air.

V<sub>MAX</sub>=Maximum voltage device can withstand without damage at its rated current.

I MAX= Maximum fault current device can withstand without damage at rated voltage (V MAX).


Pd=Maximum power dissipated from device when in tripped state in 23°C still air environment.

RMIN=Minimum device resistance at 23°C. R1MAX=Maximum device resistance at 23C, 1 hour after tripping.

Physical specifications:

Lead material:0.13mm nominal thickness, quarter-hard nickel. Insulating material: Polyester tape.


## 4. Production Dimensions (millimeter)




Part		Α		В		С		D		F	
Numbe	ər	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max
FLR60	)F	24.0	26.0	13.9	14.5	0.6	1.0	4.1	5.5	5.9	6.1

<b>FUZETEC</b> TECHNOLOGY CO., LTD.	NO.	PQ07-109E		9E
Product Specification and Approval Sheet	Version	3	Page	2/3

# 5. Thermal Derating Curve



6. Typical Time-To-Trip at 23  $^\circ\!\mathrm{C}$ 




<b>FUZETEC</b> TECHNOLOGY CO., LTD.	NO.	PC	207-10	)7-109E	
Product Specification and Approval Sheet	Version	3	Page	3/3	

## 7. Material Specification

Lead material: 0.13 mm nominal thickness, quarter-hard nickel Insulating material:Polyester tape

## 8. Part Numbering and Marking System



**Warning:** -Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.



- -PPTC device are intended for occasional overcurrent protection. Application for repeated overcurrent condition and/or prolonged trip are not anticipated.
- Avoid contact of PPTC device with chemical solvent. Prolonged contact will damage the device performance.